


Sub-base VABS-K1-7B-12-U14-P

Part number: 8047063

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Nominal width | 1.2 mm |
| Valve size | 7 mm |
| Fluid connector | Internal thread 1/4-28 UNF-2B |
| Mounting position | Any |
| Structural design | Connection direction underneath |
| Flow direction | Reversible |
| Operating medium | Liquid media Gaseous media |
| Information on operating and pilot media | Observe resistance of materials that come into contact with media |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364 Zone III |
| Storage temperature | -20 °C ... 70 °C |
| For use in the food industry | See supplementary material information |
| Temperature of medium | 0 °C ... 50 °C |
| Ambient temperature | 0 °C ... 50 °C |
| Max. tightening torque for valve mounting | 0.15 Nm |
| Max. tightening torque of pneumatic fitting | 0.6 Nm |
| Product weight | 3 g |
| Sub-base mounting type | With through-hole |
| Pneumatic valve mounting type | With internal thread |
| Note on materials | RoHS compliant |
| Material of sub-base | PEEK |
| Threaded sleeve material | high-alloy stainless steel |