

Quick coupling socket NPHS-D6-P-G12

Part number: 8059269

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal width	11 mm
Operating pressure for entire temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Operating pressure for entire temperature range	-13.775 psi ... 174 psi
Normal nominal flow rate (normalized to DIN 1343)	1233 l/min ... 2016 l/min
Nominal flow rate standardized according to ISO 8778	1336.6 l/min ... 2185.3 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque	14 Nm
Tolerance for nominal tightening torque	±20%
Product weight	113 g
Pneumatic connection 1	External thread G1/2
Note on materials	RoHS compliant
Seals material	NBR
Material of spring	high-alloy stainless steel
Housing material	Brass, nickel-plated
Material of threaded seal	PA66-GF30 / TPE-U
Threaded coupling material	Brass, nickel-plated
Inner raceway material	POM
Ball material	high-alloy stainless steel
Material of pins	high-alloy stainless steel
Valve body material	Brass
Material releasing sleeve	POM PP high-alloy stainless steel