

# Air solenoid valve VSCS-B-M32-MH-WA-1AC1-8

Part number: 8040566

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Valve function	3/2, closed, monostable
Actuation type	Electrical
Width	15 mm
Normal nominal flow rate (normalized to DIN 1343)	13.5 l/min
Pneumatic working port	Sub-base, size 15 mm according to ISO 15218
Operating voltage	24V AC
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Operating pressure	21.75 psi ... 116 psi
Reset method	Mechanical spring
Degree of protection	IP65
Sealing principle	Soft
Mounting position	Any
Conforms to standard	ISO 15218
Manual override	Non-detenting
Type of control	Direct
Flow direction	Non-reversible
Symbol	00991308
Lap	Underlap
Note on forced dynamization	Switching frequency at least once a week
Switching time off	30 ms
On switching time	9 ms
Duty cycle	100%
Coil characteristics	24 V AC: 50/60 Hz, initial power 2.1 VA, holding power 1.6 VA
Permissible voltage fluctuations	+/- 10 %
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Vibration resistance	Transport application test with severity level 1 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 as per FN 942017-5 and EN 60068-2-27
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Temperature of medium	-5 °C ... 50 °C
Ambient temperature	-5 °C ... 50 °C
Electrical connection	Form C as per DIN EN 175301-803

<b>Feature</b>	<b>Value</b>
Pneumatic connection 1	Sub-base
Pneumatic connection 2	Sub-base
Pneumatic connection 3	Sub-base
Note on materials	RoHS-compliant
Seals material	NBR