

# Position transmitter SDAP-MHS-M160-1L-A-E-0.3-M8

Part number: 8050122

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Design	for T-slot
Symbol	00995389
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Note on materials	RoHS-compliant Halogen-free
Measured variable	Position
Measuring principle	Magnetic Hall
Sensing range	0 μm ... 160000 μm
Ambient temperature	-25 °C ... 70 °C
Typical sampling interval	1 ms
Max. travel speed	3 m/s
Displacement resolution	0.05 mm
Analog output	4 - 20 mA
Sensitivity	0.1 mA/mm
Typical linearity error	±0.25 mm
Max. load resistance of current output	500 Ohm
Short-circuit protection	yes
Overload protection	Available
DC operating voltage range	15 V ... 30 V
Residual ripple	10 %
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Cable with plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00991171
Connection outlet orientation	Longitudinal
Material of pin contacts	Copper alloy, gold-plated
Connector cable test conditions	Flexural strength: as per Festo standard Torsion resistance: > 300,000 cycles, ±270°/0.1 m Energy chain: > 5 million cycles, bending radius 28 mm
Cable length	0.3 m
Cable characteristic	suitable for energy chains/robot applications

Feature	Value
Color cable sheath	Gray
Material of cable sheath	TPE-U(PUR)
Type of mounting	Screwed tightly Can be inserted in slot from above
Mounting position	Any
Product weight	35 g
Housing material	Polyester High-alloy stainless steel
Material of union nut	Brass, nickel-plated
Film material	Polyester
Ready status indication	LED green
Status indicator	LED red
Ambient temperature with flexible cable installation	-20 °C ... 70 °C
Degree of protection	IP65 IP68
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 4 according to ISO 14644-1