

Retro-reflective sensor SOOE-RS-L-PNLK-T

Part number: 8075672

FESTO



 General operating condition

Data sheet

Feature	Value
Design	Block design
Conforms to standard	EN 60947-5-2
Symbol	00995956
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Certificate issuing authority	UL E232949
Note on materials	RoHS compliant
Measuring principle	Optoelectronic
Detection method	Reflection light barrier
Type of light	Laser Red
Max. light spot	30 mm at 12000 mm
Working range	0 mm ... 12000 mm
Distance sensor Reflector	Ø 300 ... 12000 SARA-R-Q50-S Ø 250 ... 10000 SARA-R-Q50-MC Ø 300 ... 2000 SARA-RF-Q100-S Ø 250 ... 10000 SARA-RF-Q100-MC Ø 300 ... 10000 SARA-R-Q20-S Ø 250 ... 10000 SARA-R-Q20-MC Ø 250 ... 8000 SARA-R-Q14-M Ø 300 ... 7500 SARA-R-D20-M
Ambient temperature	-40 °C ... 60 °C
Reference material	Reference reflector: SARA-R-Q50-S
Switching output	Push-pull
Switching element function	Switchable PNP, dark-switching NPN, light-switching
Max. switching frequency	2000 Hz
Max. output current	100 mA
Voltage drop	0 V ... 1.5 V
Timer function	Via IO-Link®
Short-circuit protection	Pulsed
Protocol	IO-Link®
IO-Link®, protocol version	Device V 1.1
IO-Link®, communication mode	COM2 (38,4 kBd)
IO-Link®, SIO mode support	Yes

Feature	Value
IO-Link®, port class	A
IO-Link®, process data width OUT	2 bit
IO-Link®, process data content OUT	1 bit (emitter disable) 1 bit (hold)
IO-Link®, process data width IN	2 bit
IO-Link®, process data content IN	1 bit (stability alarm) 1 bit SSC (switching signal)
IO-Link®, minimum cycle time	2.3 ms
IO-Link®, data memory required	2000 byte
DC operating voltage range	10 V ... 30 V
Residual ripple	10%
Idle current	25 mA
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00991155
Material of pin contacts	Gold-plated brass
Type of mounting	With through-hole for M3 screw
Tightening torque	0.8 Nm
Mounting position	Any
Product weight	10 g
Housing material	PC PMMA
Ready status indication	Green LED
Switching status indication	Yellow LED
Function reserve indication	Yellow LED, flashing
Setting options	IO-Link® Potentiometer Teach-in
Degree of protection	IP65 IP67 IP69K
Insulation voltage	500 V
Surge resistance	1 kV
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Laser safety class	1
Contamination level	3