

Guide axis ELFC-KF-32-400

Part number: 8062799

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Working stroke | 400 mm |
| Size | 32 |
| Mounting position | Any |
| Guide | Recirculating ball bearing guide |
| Structural design | Guide |
| Symbol | 00992984 |
| Position sensing | For proximity sensor For inductive proximity sensors |
| Max. acceleration | 15 m/s ² |
| Max. speed | 1.5 m/s |
| Duty cycle | 100% |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 7 according to ISO 14644-1 |
| Degree of protection | IP40 |
| Ambient temperature | 0 °C ... 50 °C |
| 2nd moment of area Iy | 38000 mm ⁴ |
| 2nd moment of area Iz | 45000 mm ⁴ |
| Max. force Fy | 356 N |
| Max. force Fz | 356 N |
| Max. torque Mx | 1.3 Nm |
| Max. torque My | 1.1 Nm |
| Max. torque Mz | 1.1 Nm |
| Max. force Fy total axis | 150 N |
| Max. force Fz total axis | 300 N |
| Max. moment Mx total axis | 1.3 Nm |
| Max. moment My total axis | 1.1 Nm |
| Max. moment Mz total axis | 1.1 Nm |
| Torsion moment of inertia It | 1770 mm ⁴ |
| Displacement force | 2 N |
| Reference service life | 5000 km |
| Maintenance interval | Life-time lubrication |
| Fy with theoretical service life of 100 km (from a guide perspective only) | 1310 N |
| Fz with theoretical service life of 100 km (from a guide perspective only) | 1310 N |

| Feature | Value |
|--|--------------------------------------|
| Mx with theoretical service life of 100 km (from a guide perspective only) | 5 Nm |
| My with theoretical service life of 100 km (from a guide perspective only) | 4 Nm |
| Mz with theoretical service life of 100 km (from a guide perspective only) | 4 Nm |
| Moving mass | 61 g |
| Basic weight with 0 mm stroke | 168 g |
| Additional weight per 10 mm stroke | 11 g |
| Dynamic deflection (load moved) | 0.05% of axis length, maximum 0.5 mm |
| Static deflection (load at standstill) | 0.1 % of axis length |
| Material of end caps | Die cast aluminum, painted |
| Profile material | Wrought aluminum alloy, anodized |
| Note on materials | RoHS-compliant |
| Cover strip material | High-alloy stainless steel |
| Slide carriage material | Steel |
| Guide rail material | Steel |
| Slide material | Die-cast aluminum |