

Axial kit EAMM-A-M80-90GB

Part number: 8063567

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------|-----------------------|
| Nominal length | 27 mm |
| Mounting position | Any |
| Max. rotational speed | 5500 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Mass moment of inertia | 151 kgmm ² |
| Transferable torque | 60 Nm |
| Product weight | 1279 g |
| Interface code, actuator | M80 |
| Interface code, motor in | 90GB |
| Note on materials | RoHS-compliant |