


Axial kit EAMM-A-M80-115GA

Part number: 8063569

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal length	67 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	151 kgmm ²
Transferable torque	60 Nm
Product weight	1873 g
Interface code, actuator	M80
Interface code, motor in	115GA
Note on materials	RoHS-compliant