


Light barrier SOOE-TB-L-PNLK-T

Part number: 8075671

FESTO



General operating condition

Data sheet

Feature	Value
Design	Block design
Conforms to standard	EN 60947-5-2
Symbol	00995973
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Certificate issuing authority	UL E232949
Note on materials	RoHS-compliant
Measuring principle	Optoelectronic
Detection method	Through-beam sensor Transmitter Receiver
Type of light	Laser Red
Max. light spot	50 mm at 20000 mm
Working range	0 mm ... 20000 mm
Ambient temperature	-40 °C ... 60 °C
Switching output	Push-pull
Switching element function	Switchable PNP, dark-switching NPN, bright-switching
Max. switching frequency	1250 Hz
Max. output current	100 mA
Voltage drop	0 V ... 1.5 V
Timer function	Via IO-Link®
Short-circuit protection	Pulsed
Protocol	IO-Link®
IO-Link®, protocol version	Device V 1.1
IO-Link®, communication mode	COM2 (38,4 kBd)
IO-Link®, SIO mode support	Yes
IO-Link®, port class	A
IO-Link®, process data width OUT	1 bit (emitter) 2 bit (receiver)

Feature	Value
IO-Link®, process data content OUT	1 bit (emitter disable) 1 bit (hold)
IO-Link®, process data width IN	2 bit (receiver)
IO-Link®, process data content IN	1 bit (stability alarm) 1 bit SSC (switching signal)
IO-Link®, minimum cycle time	2.3 ms
IO-Link®, data memory required	2000 byte
DC operating voltage range	10 V ... 30 V
Residual ripple	10 %
Idle current	14 mA
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00991155
Material of pin contacts	Brass, gold-plated
Type of mounting	With through-hole for M3 screw
Tightening torque	0.8 Nm
Mounting position	Any
Product weight	20 g
Housing material	PC PMMA
Ready status indication	LED green
Switching status indication	LED yellow
Function reserve indication	LED yellow, flashing
Setting options	IO-Link® Potentiometer Teach-in
Degree of protection	IP65 IP67 IP69K
Insulation voltage	500 V
Surge resistance	1 kV
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Laser safety class	1
Contamination level	3