

# Push-in fitting NPQR-DK-G12-Q14

Part number: 8085670

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	Standard
Nominal width	11.6 mm
Tubing insertion depth	21.5 mm
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Design	Straight design
Pack size	1
Structural design	Push-pull principle
Symbol	00997424
Operating pressure for entire temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Operating pressure for entire temperature range	-13.775 psi ... 174 psi
Information on operating pressure	Water: max. 0.7 MPa at 0 - 80 °C
Certificate issuing authority	NSF C0556009
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 4 according to ISO 14644-1
For use in the food industry	See declaration of conformity NSF/ANSI 169
Ambient temperature	-5 °C ... 150 °C
Note on ambient temperature	With PUN-H: -20 °C - 60 °C
Nominal tightening torque	9 Nm
Tolerance for nominal tightening torque	±20%
Product weight	39 g
Type of mounting	Hexagon socket SW10
Pneumatic connection 1	External thread G1/2
Pneumatic connection 2	for pneumatic tubing outside diameter 14 mm
Releasing ring color	Silver
Note on materials	RoHS compliant
Housing material	high-alloy stainless steel
Material of threaded seal	FPM
Guard ring material	high-alloy stainless steel

<b>Feature</b>	<b>Value</b>
Releasing ring material	high-alloy stainless steel
Material of tubing seal	FPM
Material of tube retaining claw	high-alloy stainless steel
Thrust ring material	PPSU