


# Axial kit EAMM-A-V32-60PA

Part number: 8091053

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal length	55 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	1.03 kgmm <sup>2</sup>
Transferable torque	1.5 Nm
Product weight	243 g
Interface code, actuator	V32
Interface code, motor in	60PA
Note on materials	RoHS-compliant