

Mini slide DGST-6-40-PA

Part number: 8085108

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Stroke	40 mm
Adjustable end-position range/front length	13.1 mm
Adjustable end-position range/rear length	11.6 mm
Piston diameter	6 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Recirculating ball bearing
Structural design	Yoke Piston rod Slide
Position sensing	Via proximity switch
Symbol	00991249
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Operating pressure	21.75 psi ... 116 psi
Max. speed	0.5 m/s
Repetition accuracy	≤ 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C ... 60 °C
Impact energy in the end positions	0.018 J
Cushioning length	0.9 mm
Max. force F _y	260 N
Max. force F _z	260 N
Max. torque M _x	1.2 Nm
Max. torque M _y	1.2 Nm
Max. torque M _z	1.2 Nm
Theoretical force at 6 bar, retracting	25 N
Theoretical force at 6 bar, advancing	34 N

Feature	Value
Moving mass	78 g
Product weight	150 g
Type of mounting	With through-hole
Pneumatic connection	M3
Note on materials	RoHS compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Guide material	POM TPE-E High-alloy steel
Housing material	Wrought aluminum alloy
Piston rod material	high-alloy stainless steel