

Compact cylinder ADN-S-25-30-A-P

Part number: 8092099

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Stroke	30 mm
Piston diameter	25 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Piston rod end	External thread
Structural design	Piston Piston rod
Symbol	00991227
Variants	Piston rod at one end
Operating pressure	0.06 MPa ... 1 MPa
Operating pressure	0.6 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	0 °C ... 80 °C
Impact energy in the end positions	0.18 J
Theoretical force at 6 bar, retracting	247 N
Theoretical force at 6 bar, advancing	295 N
Moving mass at 0 mm stroke	17 g
Additional moving mass per 10 mm stroke	6 g
Basic weight with 0 mm stroke	70 g
Additional weight per 10 mm stroke	30 g
Type of mounting	With through-hole With internal thread With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy, anodized
Material of dynamic seals	NBR
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel