

Mini slide DGST-20-50-Y12A

Part number: 8085185

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Stroke	50 mm
Adjustable end-position range/front length	27.7 mm
Adjustable end-position range/rear length	25.9 mm
Piston diameter	20 mm
Drive unit operating mode	Yoke
Cushioning	External hydraulic cushioning
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Yoke Piston rod Slide
Position sensing	For proximity sensor
Symbol	00991249
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Operating pressure	14.5 psi ... 116 psi
Max. speed	0.8 m/s
Repetition accuracy	≤ 0.02 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C ... 60 °C
Impact energy in the end positions	3 J
Cushioning length	8 mm
Max. force F _y	1080 N
Max. force F _z	1080 N
Max. torque M _x	9 Nm
Max. torque M _y	10 Nm
Max. torque M _z	10 Nm
Theoretical force at 6 bar, retracting	317 N
Theoretical force at 6 bar, advancing	377 N

Feature	Value
Moving mass	606 g
Product weight	1310 g
Type of mounting	With through-hole
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Guide material	POM TPE-E High-alloy steel
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel