

Parallel kit EAMM-U-30-V20-28AA-44

Part number: 8093176

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	30
Center-to-center distance	44 mm
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	3000 rpm
LABS (PWIS) conformity	VDMA24364 Zone III
Storage temperature	-20 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	0 °C ... 50 °C
Mass moment of inertia	2.11 kgmm ²
No-load driving torque	0.015 Nm
Transferable torque	0.05 Nm
Product weight	94 g
Interface code, actuator	V20
Interface code, motor in	28AA
Note on materials	RoHS compliant