

# Parallel kit EAMM-U-45-V32-42AB-63

Part number: 8095613

FESTO



 [General operating condition](#)

## Data sheet

| Feature                   | Value                  |
|---------------------------|------------------------|
| Size                      | 45                     |
| Center-to-center distance | 63 mm                  |
| Mounting position         | Any                    |
| Gear ratio                | 1:1                    |
| Max. rotational speed     | 3600 rpm               |
| LABS (PWIS) conformity    | VDMA24364 zone III     |
| Storage temperature       | -20 °C ... 60 °C       |
| Relative air humidity     | 0 - 95 %               |
| Degree of protection      | IP40                   |
| Ambient temperature       | 0 °C ... 50 °C         |
| Mass moment of inertia    | 4.35 kgmm <sup>2</sup> |
| No-load driving torque    | 0.05 Nm                |
| Transferable torque       | 1 Nm                   |
| Product weight            | 242 g                  |
| Interface code, actuator  | V32                    |
| Interface code, motor in  | 42AB                   |
| Note on materials         | RoHS-compliant         |