

Compact cylinder ADN-S-20-15-A-P

Part number: 8091447

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Stroke | 15 mm |
| Piston diameter | 20 mm |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Mode of operation | Double-acting |
| Piston rod end | External thread |
| Structural design | Piston Piston rod |
| Symbol | 00991227 |
| Variants | Piston rod at one end |
| Operating pressure | 0.06 MPa ... 1 MPa |
| Operating pressure | 0.6 bar ... 10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 5 according to ISO 14644-1 |
| Ambient temperature | 0 °C ... 80 °C |
| Impact energy in the end positions | 0.14 J |
| Theoretical force at 6 bar, retracting | 141 N |
| Theoretical force at 6 bar, advancing | 188 N |
| Moving mass at 0 mm stroke | 11 g |
| Additional moving mass per 10 mm stroke | 6 g |
| Basic weight with 0 mm stroke | 51 g |
| Additional weight per 10 mm stroke | 26 g |
| Type of mounting | With through-hole With internal thread With accessories |
| Pneumatic connection | M5 |
| Note on materials | RoHS compliant |
| Cover material | Wrought aluminum alloy, anodized |
| Material of dynamic seals | NBR |
| Housing material | Wrought aluminum alloy, anodized |
| Piston rod material | high-alloy stainless steel |