

Filter regulator MS4-LFR-1/4-D6-E-P-M-A8-B

Part number: 8098255

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	4
Series	MS
Actuator lock	Rotary knob with detent
Mounting position	Vertical $\pm 5^\circ$
Grade of filtration	40 μm
Condensate drain	Manual, rotating
Structural design	Directly controlled piston regulator
Max. condensate volume	16.5 ml
Controller function	Constant output pressure With secondary exhausting With return flow characteristic
Degree of condensate separation	$>75\%$
Symbol	00991590
Pressure gauge	Set up for G1/8
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Pressure regulation range	0.3 bar ... 7 bar
Max. pressure hysteresis	0.05 MPa
Max. pressure hysteresis	0.5 bar
Max. pressure hysteresis	7.25 psi
Normal nominal flow rate (normalized to DIN 1343)	1700 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 7 according to ISO 14644-1
Storage temperature	-5 $^\circ\text{C}$... 50 $^\circ\text{C}$
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:4:4]
Temperature of medium	-5 $^\circ\text{C}$... 50 $^\circ\text{C}$
Ambient temperature	-5 $^\circ\text{C}$... 50 $^\circ\text{C}$
Pore size	$<40\ \mu\text{m}$
Product weight	204 g
Type of mounting	With accessories
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4

Feature	Value
Note on materials	RoHS compliant
Seals material	NBR
Rotary knob material	POM
Material of spring	High-alloy steel Galvanized steel
Compressed air filter material	Protective grounding
Housing material	PA-reinforced
Material of bowl	PC
Valve tappet material	POM