

# Filter regulator MS4-LFR-1/4-D6-E-P-VC-A8-B

Part number: 8098262

FESTO



General operating condition

## Data sheet

Feature	Value
Size	4
Series	MS
Actuator lock	Rotary knob with detent
Mounting position	Vertical $\pm 5^\circ$
Grade of filtration	40 $\mu\text{m}$
Condensate drain	Manual, non-detenting
Structural design	Directly controlled piston regulator
Max. condensate volume	16.5 ml
Controller function	Constant output pressure With secondary exhausting With return flow characteristic
Degree of condensate separation	$>75\%$
Symbol	00991588
Pressure gauge	Set up for G1/8
Operating pressure	0.2 MPa ... 1 MPa
Operating pressure	2 bar ... 10 bar
Pressure regulation range	0.3 bar ... 7 bar
Max. pressure hysteresis	0.05 MPa
Max. pressure hysteresis	0.5 bar
Max. pressure hysteresis	7.25 psi
Normal nominal flow rate (normalized to DIN 1343)	1700 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 7 according to ISO 14644-1
Storage temperature	-5 °C ... 50 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:4:4]
Temperature of medium	5 °C ... 50 °C
Ambient temperature	5 °C ... 50 °C
Pore size	$<40\ \mu\text{m}$
Product weight	213 g
Type of mounting	With accessories
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4

<b>Feature</b>	<b>Value</b>
Note on materials	RoHS compliant
Seals material	NBR
Rotary knob material	POM
Material of spring	High-alloy steel Galvanized steel
Compressed air filter material	Protective grounding
Housing material	PA-reinforced
Material of bowl	PC
Valve tappet material	POM