

One-way flow control valve NEBM-SF1W31-EH-10-Q15N-LE14

Part number: 8113310

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Conforms to standard | DIN 47100 |
| Cable designation | Without label holder |
| Contact durability | 30 |
| Product weight | 2960 g |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | Square |
| Electrical connection 1, connection type | Plug |
| Electrical connection 1, cable outlet | Angled |
| Electrical connection 1, information on cable outlet | 90° |
| Electrical connection 1, connection technology | Connection pattern F1 |
| Electrical connection 1, number of pins/wires | 31 |
| Electrical connection 1, occupied pins/wires | 31 |
| Electrical connection 1, type of mounting | Snap-locking |
| Electrical connection for input 1, connection pattern | 00995929 |
| Electrical connection 2, function | Control side |
| Electrical connection 2, connection type | Cable |
| Electrical connection 2, connection technology | Open end |
| Electrical connection 2, number of pins/wires | 14 |
| Electrical connection 2, occupied pins/wires | 14 |
| DC operating voltage range | 0 V ... 50 V |
| Nominal operating voltage DC | 24 V |
| Current rating at 40° C | 0.5 A |
| Surge resistance | 0.25 kV |
| Cable length | 10 m |
| Cable characteristic | Suitable for energy chains |
| Connector cable test conditions | Test conditions on request |
| Bending radius, fixed cable installation | ≥49.5 mm |
| Bending radius, flexible cable installation | ≥74.25 mm |
| Cable diameter | 9.9 mm |
| Cable diameter tolerance | ± 0.2 mm |
| Cable design | 1 x (6 x 0.35 mm ²) + 2 x (4 x 0.15 mm ²) |
| Nominal conductor cross section | 0.35 mm ² |
| Wire ends | Wire ferrule |
| Degree of protection | IP20 |
| Note on degree of protection | In mounted state |
| Ambient temperature | -20 °C ... 75 °C |

| Feature | Value |
|--|------------------------------|
| Ambient temperature with flexible cable installation | -5 °C ... 70 °C |
| Storage temperature | -25 °C ... 55 °C |
| CE marking (see declaration of conformity) | As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| LABS (PWIS) conformity | VDMA24364 Zone III |
| Note on materials | RoHS compliant |
| Contamination level | 1 |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Material of cable sheath | TPE-U(PUR) |
| Color cable sheath | Black |
| Housing material | PA |
| Housing colour | Black |
| Material of pin contacts | Tin-plated, high-alloy steel |