

Ball valve

VZBE-11/4-T-63-T-2-F0405-M-V15V15

Part number: 8096668

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|--|
| Structural design | 2-way ball valve |
| Actuation type | Mechanical |
| Sealing principle | Soft |
| Mounting position | Any |
| Type of mounting | In-line installation |
| Fitting connection | 1 1/4 NPT |
| Switching position indication | Slot direction = flow direction |
| Flange hole pattern | F0405 |
| Inside diameter | 32 mm |
| Nominal width DN | 32 |
| Valve function | 2/2 |
| Flow direction | Reversible |
| Nominal pressure of fitting PN | 63 |
| Breakaway torque at differential pressure, nominal pressure, fitting PN | 18 Nm |
| Based on norm | ISO 5211 |
| Symbol | 00991458 |
| Medium | Vapor Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water Neutral liquids |
| Temperature of medium | -20 °C ... 200 °C |
| Flow rate Kv | 42.6 m ³ /h |
| Note on materials | RoHS compliant |
| LABS (PWIS) conformity | VDMA24364 Zone III |
| Housing material | Cast stainless steel |
| Material number of housing | 1,4408 |
| Seat seal material | PTFE, modified |
| Seals material | FPM PTFE |

| Feature | Value |
|--|--|
| Ball material | Cast stainless steel |
| Material number for ball | 1,4408 |
| Shaft material | high-alloy stainless steel |
| Material number for shaft | 1,4401 |
| Product weight | 1700 g |
| Certification | CRN |
| CE marking (see declaration of conformity) | as per EU pressure equipment directive |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |