

Pressure sensor SPAN-B-B11R-M5FAL-PN-L1+2.5S

Part number: 8114771

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Symbol	00997331
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Note on materials	RoHS compliant
Measured variable	Relative pressure
Method of measurement	Piezoresistive pressure sensor
Pressure measuring range initial value	-0.1 MPa
Pressure measuring range initial value	-1 bar
Pressure measuring range initial value	-14.5 psi
Pressure measuring range end value	1 MPa
Pressure measuring range end value	10 bar
Pressure measuring range end value	145 psi
Max. overload pressure	15 bar
Overload pressure	1.5 MPa
Overload pressure	15 bar
Overload pressure	217.5 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases
Information on operating and pilot media	Lubricated operation possible
Temperature of medium	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Accuracy in ± % FS	1.5 %FS
Repetition accuracy in ± %FS	0.3 %FS
Temperature co-efficient in ± %FS/K	0.1 %FS/K
Switching output	PNP/NPN switchable
Switching function	Window comparator Threshold value comparator
Switching element function	N/C contact/N/O contact, switchable
Max. output current	80 mA
Short-circuit protection	Yes
DC operating voltage range	10.8 V ... 30 V
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Plug

Feature	Value
Electrical connection 1, connection technology	Connection pattern L1]
Electrical connection 1, number of pins/wires	4
Electrical connection for input 1, connection pattern	00995428
Type of mounting	Front panel mounting With wall/surface bracket
Mounting position	Any
Pneumatic connection	Internal thread M5
Product weight	21 g
Housing material	PA-reinforced
Materials in contact with the media	Wrought aluminum alloy, anodized FPM PA-reinforced
Display type	Illuminated LCD
Displayable unit(s)	MPa bar In Hg KPa mmHg psi
Setting options	Teach-in Via display and keys
Protection against tampering	PIN code
Setting range threshold value	0 % ... 100 %
Setting range hysteresis	0 % ... 90 %
Degree of protection	IP40
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 4 according to ISO 14644-1