


Air Solenoid valve VSNC-FT-B52-H-N14-F19A

FESTO

Part number: 8116384



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|--|
| Valve function | 5/2-way, bistable |
| Actuation type | Electrical |
| Width | 32 mm |
| Normal nominal flow rate (normalized to DIN 1343) | 1000 l/min |
| Pneumatic working port | NAMUR connection pattern |
| Operating voltage | Via solenoid coil, to be ordered separately |
| Operating pressure | 0.15 MPa ... 0.8 MPa |
| Operating pressure | 1.5 bar ... 8 bar |
| Structural design | Plate seat |
| Exhaust air function | Adjustable |
| Sealing principle | Soft |
| Mounting position | Any |
| Conforms to standard | VDI/VDE 3845 (NAMUR) |
| Manual override | Non-detenting |
| Type of control | Piloted |
| Pilot air supply port | Internal |
| Flow direction | Non-reversible |
| Symbol | 00991005 |
| Lap | Negative overlap |
| Changeover time | 435 ms |
| Duty cycle | 100% |
| Coil characteristics | See solenoid coil, to be ordered separately |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Temperature of medium | -20 °C ... 60 °C |
| Ambient temperature | -20 °C ... 60 °C |
| Product weight | 613 g |
| Type of mounting | With through-hole |
| Venting hole connection | Not ducted |
| Pneumatic connection 1 | 1/4 NPT |
| Pneumatic connection 2 | NAMUR connection pattern |
| Pneumatic connection 3 | 1/4 NPT |
| Pneumatic connection 4 | NAMUR connection pattern |
| Pneumatic connection 5 | 1/4 NPT |

| Feature | Value |
|--------------------|------------------------|
| Note on materials | RoHS compliant |
| Seals material | NBR |
| Housing material | Wrought aluminum alloy |
| Material of screws | Galvanized steel |