


# Standards-based cylinder DSNA-N-2"- -

Part number: 8117044

FESTO



[PDF](#) General operating condition

## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	6.35 mm ... 1219.2 mm
Piston diameter	2"
Piston rod thread	7/16-20 UNF-2B 7/16-20 UNF-2A 5/8-18 UNF-2A 1/2-20 UNF-2A
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Conforms to standard	NFPA/T3.6.7
Piston rod end	External thread Internal thread
Structural design	Piston Piston rod Tie rod Cylinder barrel
Position sensing	For proximity sensor
Symbol	00991235 00991237
Variants	Internal thread on piston rod Special thread on piston rod Swiveling rod eye mounting on the end cap Through piston rod Screwed-on swivel mounting position Swivel mounting on end cap Swivel clevis on end cap Spacer bolt on end cap end Spacer bolt on bearing cap end Temperature range -5 - 80°C Piston rod at one end
Operating pressure	0.089 MPa ... 0.965 MPa
Operating pressure	0.89 bar ... 9.65 bar
Operating pressure	12.905 psi ... 139.925 psi
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-5 °C ... 80 °C
Theoretical force at 6 bar, retracting	238 N

<b>Feature</b>	<b>Value</b>
Theoretical force at 6 bar, advancing	264 N
Type of mounting	With accessories
Pneumatic connection	3/8 NPT
Note on materials	RoHS-compliant
Cover material	Die-cast aluminum, coated
Seals material	FPM NBR
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized