


# Axial kit EAMM-A-D60-80PB

Part number: 8105937

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal length	75 mm
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	21 Nm
Product weight	1070 g
Interface code, actuator	D60
Interface code, motor in	80PB 80R
Note on materials	RoHS compliant