


# Sub-base VABS-K2-10S-16-M6-P

Part number: 8122827

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	10
Nominal width	1.6 mm
Fluid connector	Internal thread M6
Mounting position	Any
Structural design	Lateral connection direction
Max. no. of valve positions	1
Flow direction	Non-reversible
Operating medium	Liquid media Gaseous media
Information on operating and pilot media	Observe resistance of materials that come into contact with media
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Storage temperature	-20 °C ... 70 °C
Temperature of medium	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Max. tightening torque for valve mounting	0.2 Nm
Max. tightening torque	0.6 Nm
Product weight	7 g
Sub-base mounting type	With through-hole
Pneumatic valve mounting type	With internal thread
Note on materials	RoHS compliant
Material of sub-base	PEEK