

System supply CPX-AP-A-S-1-M18-4P

Part number: 8129254

FESTO



 General operating condition

Data sheet

Feature	Value
Dimensions W x L x H	50.1 mm x 124 mm x 35 mm
Width dimension	50.1 mm
Type of mounting	On H-rail with accessories with through-hole for M5 screw with accessories with through-hole for M6 screw with accessories
Product weight	111 g
Mounting position	Arbitrary, on H-rail: horizontal
Ambient temperature	-20 °C ... 50 °C
Note on ambient temperature	Observe ambient temperature derating according to IEC 61131-2:2017
Storage temperature	-20 °C ... 70 °C
Relative air humidity	5 - 95 % Non-condensing
Nominal altitude of use above sea level	≤ 2000 m ASL (≥ 79.5 kPa)
Max. installation height	3500 m
Information on max. installation height	Observe ambient temperature derating according to IEC 61131-2:2017
Corrosion resistance class (CRC)	1 - Low corrosion stress
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Note on vibration resistance	SG1 on H-rail SG2 on direct mounting Transport application test with severity level 1 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Note on shock resistance	30 g/11 ms as per EN 60068-2-27 SG1 on H-rail SG2 on direct mounting Shock test with severity level 1 as per FN 942017-5 and EN 60068-2-27
Protection class	III
Overvoltage category	II
LABS (PWIS) conformity	VDMA24364-B2-L
Material fire test	UL94 V-0 (housing)
Note on materials	RoHS-compliant Halogen-free Free of phosphoric acid ester
Housing material	PA-reinforced
Material of screws	Steel, nickel-plated
Seals material	PU foam
Power supply, function	Incoming electronics/sensors and load and functional earth
Power supply, type of connection	Plug

Feature	Value
Power supply, connection technology	M18x1
Power supply, connection pattern	00995991
Power supply, number of pins/wires	4
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Note on nominal operating voltage DC	2x24 V [XD1,PS,PL] Protected Extra-Low-Voltage as per IEC 60204-1
Nominal operating voltage DC load	24 V
Nominal operating voltage DC for electronics/sensors	24 V
Power supply, conductor diameter	2.5 mm ²
Nominal current	8 A
Max. power supply	2 x 8 A (external fuse required)
Potential separation between the supply voltages electronics/sensor technology and load/valves	no