

# Limit switch box SRBC-CA5-YR90-N-1-P-C2

Part number: 8137106

FESTO



 General operating condition

## Data sheet

Feature	Value
Certification	RCM compliance mark c CSA us (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
KC characters	KC-EMV
Certificate issuing authority	Eurocert. SIL202587141
Note on materials	RoHS compliant
Safety integrity level (SIL)	SIL 3
Measuring principle	Inductive
Ambient temperature	-20 °C ... 80 °C
Switching output	PNP
Switching element function	N.O. contact
Max. switching frequency	1000 Hz
Max. output current DC	100 mA
Voltage drop	≤3 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V ... 30 V
Idle current	≤15 mA
Reverse polarity protection	for all electrical connections
Microswitch type	Switch type P&F NBB2-V3-E2
Electrical connection	Screw terminal
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	Spring-loaded terminal
Electrical connection 1, number of pins/wires	10
Closable nominal conductor cross-section	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Approved cable diameter	5 mm ... 13 mm
Dimensions W x L x H	114 mm x 98 mm x 122 mm
Type of mounting	on flange according to ISO 5211
Mounting position	Any
Product weight	800 g
Housing colour	Gray
Housing material	Die-cast aluminum
Seals material	NBR
Shaft material	high-alloy stainless steel

Feature	Value
Material of screws	high-alloy stainless steel
Material of mounting bracket	high-alloy stainless steel
Circlip material	high-alloy stainless steel
Disc material	high-alloy stainless steel
Cover cap material	PC
Position indicator	Yellow/red
Angle detection setting range	0 deg ... 90 deg
Storage temperature	-20 °C ... 50 °C
Degree of protection	IP66 IP67 NEMA 4/4X
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Contamination level	3