


Parallel gripper DHPC-6-A-NO-S-1

Part number: 8116742

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Size | 6 |
| Stroke per gripper jaw | 2 mm |
| Max. interchangeability | 0.2 mm |
| Max. gripper jaw angular play ax, ay | 0 deg |
| Max. gripper jaw backlash Sz | 0 mm |
| Rotational symmetry | ≤0.2 mm |
| Pneumatic gripper repetition accuracy | ≤0.02 mm |
| Number of gripper jaws | 2 |
| Actuator system | Pneumatic |
| Mounting position | Any |
| Mode of operation | Single-acting Open |
| Gripper function | Parallel |
| Gripping force backup | On opening |
| Structural design | Connection direction at side Lever Side mounting type for gripper fingers Positively driven motion sequence |
| Guide | Ball guide |
| Position sensing | For proximity sensor |
| Symbol | 00997349 |
| Variants | Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils. |
| Operating pressure | 0.35 MPa ... 0.8 MPa |
| Operating pressure | 3.5 bar ... 8 bar |
| Operating pressure | 50.75 psi ... 116 psi |
| Max. operating frequency of pneumatic gripper | 3 Hz |
| Min. opening time at 6 bar | 8 ms |
| Min. closing time at 6 bar | 6 ms |
| Max. mass per external gripper finger | 6 g |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |

| Feature | Value |
|--|--|
| Ambient temperature | -10 °C ... 60 °C |
| Gripping force per gripper jaw at 6 bar, closing | 7.8 N |
| Gripping force per gripper jaw at 6 bar, closing | 3.9 N |
| Mass moment of inertia | 0.012 kgcm ² |
| Maximum force on gripper jaw Fz, static | 22 N |
| Maximum torque on gripper jaw, Mx static | 0.24 Nm |
| Maximum torque on gripper jaw, My static | 0.11 Nm |
| Maximum torque on gripper jaw, Mz static | 0.11 Nm |
| Product weight | 27 g |
| Type of mounting | Optionally: Direct mounting via through-hole Direct fastening via thread |
| Pneumatic connection | M3 |
| Note on materials | RoHS-compliant |
| Housing material | Aluminum, anodized |
| Gripper jaw material | High-alloy stainless steel |