


# Media separated solenoid valve VYKB-F12-M32-20-PE-5HPS

Part number: 8140317

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Structural design	Rocker valve with diaphragm seal
Sealing principle	Soft
Materials in contact with the media	PEEK
Valve function	3/2, open/closed, monostable
Nominal width	2 mm
Flow direction	Non-reversible
Actuation type	Electrical
Type of control	directly
Reset method	Mechanical spring
Manual override	None
Mounting position	Any
Type of mounting	With through-hole for M3 screw
Electrical connection 1, connection type	Cable with plug
Electrical connection 1, connection technology	Connection pattern HP
Size	12
Fluid connector	Flange
Medium	Liquid media Gaseous media
Information on medium	Observe resistance of materials that come into contact with media Maximum particle size 5 µm
Internal volume	60 µl
Temperature of medium	0 °C ... 50 °C
Temperature of liquid media	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Medium pressure	-0.075 MPa ... 0.3 MPa
Medium pressure	-0.75 bar ... 3 bar
Medium pressure	-10.875 psi ... 43.5 psi
Overload pressure	0.45 MPa
Overload pressure	4.5 bar
Overload pressure	65.25 psi
DC operating voltage range	12 V
Permissible voltage fluctuations	-5% / +10%
Coil characteristics	12 V DC: low-current phase 1 W, high-current phase 5.2 W
Duty cycle	100%
Max. switching frequency	2 Hz

Feature	Value
Note on switching frequency	Dependent on the ambient temperature and installation state
On switching time	≤15 ms
Switching time on gaseous media	≤15 ms
Switching time off	≤15 ms
Switching time off gaseous media	≤15 ms
Flow rate Kv	0.056 m <sup>3</sup> /h
Flow rate Kv	0.93 l/min
Note on flow rate Kv	For the medium water Pressure difference 1 bar
Symbol	00997353
Housing material	PEEK
Diaphragm material	EPDM
Seals material	EPDM
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 Zone III
Product weight	40 g
Degree of protection	IP40
Corrosion resistance class (CRC)	0 - No corrosion stress
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions