

Compact cylinder ADN-S-16-5-I-P-A-F1A

Part number: 8142728

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	16 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Piston rod end	Internal thread
Structural design	Piston Piston rod
Position sensing	Via proximity switch
Symbol	00991217
Variants	Piston rod at one end
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Operating pressure	14.5 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	0 °C ... 80 °C
Impact energy in the end positions	0.15 J
Theoretical force at 6 bar, retracting	90 N
Theoretical force at 6 bar, advancing	121 N
Moving mass at 0 mm stroke	11 g
Additional moving mass per 10 mm stroke	4 g
Basic weight with 0 mm stroke	42 g
Additional weight per 10 mm stroke	18 g
Type of mounting	With through-hole With internal thread
Pneumatic connection	M5
Note on materials	RoHS compliant
Cover material	Wrought aluminum alloy, anodized
Material of dynamic seals	NBR TPE-U(PU)
Housing material	Wrought aluminum alloy, anodized

Feature	Value
Piston rod material	high-alloy stainless steel