

# Guided drive DFM-50-125-P-A-KF-F1A

Part number: 8118938

FESTO



 [General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Distance of centre of gravity of payload to yoke plate xs | 50 mm  |
| Stroke  | 125 mm   |
| Piston diameter   | 50 mm  |
| Drive unit operating mode                                 | Yoke   |
| Cushioning  | Elastic cushioning rings/pads at both ends   |
| Mounting position   | Any  |
| Guide   | Recirculating ball bearing guide   |
| Structural design   | Guide  |
| Position sensing  | For proximity sensor   |
| Symbol  | 00991737   |
| Variants  | Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils. |
| Operating pressure  | 0.1 MPa ... 1 MPa  |
| Operating pressure  | 1 bar ... 10 bar   |
| Max. speed  | 0.6 m/s  |
| Mode of operation   | Double-acting  |
| Operating medium  | Compressed air as per ISO 8573-1:2010 [7:4:4]  |
| Information on operating and pilot media                  | Operation with oil lubrication possible (required for further use)   |
| Corrosion resistance class (CRC)                          | 0 - No corrosion stress  |
| LABS (PWIS) conformity                                    | VDMA24364-B1/B2-L  |
| Suitability for the production of Li-ion batteries        | Suitable for battery production with reduced Cu/Zn/Ni values (F1a)   |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1   |
| Ambient temperature                                       | -5 °C ... 60 °C  |
| Impact energy in the end positions                        | 1 J  |
| Max. force Fy   | 1487 N   |
| Max. force Fy static                                      | 1600 N   |
| Max. force Fz   | 1487 N   |
| Max. force Fz static                                      | 1600 N   |
| Max. torque Mx  | 81.79 Nm   |
| Max. static moment Mx                                     | 88 Nm  |
| Max. torque My  | 62.46 Nm   |
| Max. static moment My                                     | 67.2 Nm  |
| Max. torque Mz  | 62.46 Nm   |
| Max. static moment Mz                                     | 67.2 Nm  |

| <b>Feature</b>   | <b>Value</b>               |
|--|----------------------------|
| Max. permissible torque load Mx as a function of the stroke      | 15.77 Nm                   |
| Max. payload as a function of the stroke at defined distance xs  | 238 N                      |
| Theoretical force at 6 bar, retracting                           | 1057 N                     |
| Theoretical force at 6 bar, advancing                            | 1178 N                     |
| Moving mass  | 2703 g                     |
| Product weight   | 5758 g                     |
| Center of gravity of the moving mass as a function of the stroke | 82.8 mm                    |
| Alternative connections  | See product drawing        |
| Pneumatic connection   | G1/4                       |
| Note on materials  | RoHS-compliant             |
| Cover material   | Wrought aluminum alloy     |
| Seals material   | NBR                        |
| Housing material   | Wrought aluminum alloy     |
| Piston rod material  | High-alloy stainless steel |