

Servo motor EMMT-AS-150-LKR-HS-R3SB

Part number: 8148363

FESTO



 General operating condition

Data sheet

Feature	Value
Ambient temperature	-15 °C ... 40 °C
Note on ambient temperature	Up to 80 °C with derating of -1.5% per degree Celsius
Max. installation height	4000 m
Information on max. installation height	with 1,000 m and longer only with derating of -1.0% per 100 m
Storage temperature	-20 °C ... 70 °C
Relative air humidity	0 - 90%
Conforms to standard	IEC 60034
Thermal class according to EN 60034-1	F
Max. winding temperature	155 °C
Rating class according to EN 60034-1	S1
Temperature monitoring	Digital motor temperature transmission via EnDat® 2.2
Motor type as per EN 60034-7	IM V1 IM V3
Mounting position	Any
Degree of protection	IP21
Note on degree of protection	IP67 for motor housing, incl. connection technology
Concentricity, coaxiality, axial runout according to DIN SPEC 42955	N
Balancing quality	G 2.5
Detent torque	<1.0% of peak torque
Bearing lifetime, under nominal conditions	20000 h
Featherkey shaft design	DIN 6885 A 8 x 7 x 36
Interface code, motor out	150A
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connection technology	M40x1
Electrical connection 1, number of pins/wires	15
Electrical connection for input 1, connection pattern	00997380
Contamination level	2
Note on materials	RoHS compliant
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Vibration resistance	as per EN 60068-2-6
Shock resistance	as per EN 60068-2-29 15 g/11 ms as per EN 60068-2-27
Certification	RCM compliance mark c UL us - recognized (OL)

Feature	Value
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK instructions for electrical equipment
Certificate issuing authority	UL E342973
Nominal operating voltage DC	680 V
Type of winding switch	Star inside
Number of pole pairs	5
Stall torque	45.5 Nm
Nominal torque	29 Nm
Peak torque	87 Nm
Nominal rotary speed	2100 rpm
Max. rotational speed	3495 rpm
Max. mechanical speed	8000 rpm
Angular acceleration	$\leq 100000 \text{ rad/s}^2$
Motor nominal power	6377 W
Continuous stall current	23.6 A
Motor nominal current	15.4 A
Peak current	49.5 A
Motor constants	1.88 Nm/A
Standstill torque constant	2.23 Nm/A
Voltage constant, phase-to-phase	135.1 mVmin
Phase-phase winding resistance	0.25 Ohm
Winding inductance phase-phase	4.4 mH
Winding longitudinal inductivity Ld (phase)	2.15 mH
Cross inductivity Lq (phase)	2.2 mH
Electric time constant	17.1 ms
Thermal time constant	55 min
Thermal resistance	0.39 K/W
Measuring flange	450 x 450 x 30 mm, steel
Total output inertia moment	70.1 kgcm ²
Product weight	29700 g
Permissible axial shaft load	274 N
Permissible radial shaft load	1370 N
Rotor position sensor	Absolute single-turn encoder
Rotor position sensor for manufacturer designation	ECl 1319
Rotor position encoder for absolutely detectable revolutions	1
Rotor position sensor interface	EnDat 22
Rotor position sensor measuring principle	Inductive
Rotor position encoder for DC operating voltage	5 V
Rotor position encoder for DC operating voltage range	3.6 V ... 14 V
Rotor position encoder for positional values per revolution	524288
Rotor position sensor resolution	19 bit
Rotor position encoder system accuracy angle measurement	-65 arcsec ... 65 arcsec
Brake holding torque	65 Nm
Brake DC operating voltage	24 V
Brake current consumption	1.08 A
Brake power consumption	26 W
Brake separation time	200 ms
Brake closing time	40 ms
DC brake response delay	10 ms
Max. brake no-load speed	8000 rpm
Max. friction work per braking operation	40000 J

Feature	Value
Number of emergency stops per hour	1
Total brake friction work	4500 kJ
Brake mass moment of inertia	12.5 kgcm ²
Switching cycles, holding brake	5 million idle actuations (without friction work!)
MTTF, subcomponent	190 years, rotor position encoder
Energy efficiency	ENEFF (CN) / Class 1