

Angle gripper DHWC-20-A-S-NO

Part number: 8128702

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	20
Max. interchangeability	≤0.2 mm
Max. opening angle	30 deg
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	≤0.1 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mounting position	Any
Mode of operation	Single-acting Open
Gripper function	Bracket
Gripping force backup	On opening
Structural design	Lateral connection direction Positively driven motion sequence
Position sensing	Via proximity switch
Symbol	00997349
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Operating pressure	21.75 psi ... 116 psi
Max. operating frequency of pneumatic gripper	≤2 Hz
Min. opening time at 6 bar	13 ms
Min. closing time at 6 bar	10 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-10 °C ... 60 °C
Total gripping torque at 6 bar, closing	120.9 Ncm
Mass moment of inertia	0.255 kgcm ²
Maximum force on gripper jaw Fz, static	100 N
Maximum torque on gripper jaw, Mx static	1.5 Nm
Maximum torque on gripper jaw, My static	2.2 Nm
Maximum torque on gripper jaw, Mz static	2.2 Nm
Product weight	190.5 g

Feature	Value
Type of mounting	Alternatively: Direct mounting via through-hole Direct fastening via thread With through-hole and dowel pin With internal thread and dowel pin
Pneumatic connection	M5
Note on materials	RoHS compliant
Cover cap material	Wrought aluminum alloy, anodized
Housing material	Wrought aluminum alloy, anodized
Gripper jaw material	High-alloy steel