

# Operator unit CDPX-X-E1-W-15

Part number: 8155218

FESTO



 General operating condition

## Data sheet

Feature	Value
Width	422 mm
Installation depth	56 mm
Height	267 mm
Length	64 mm
Max. front panel thickness	8 mm
Real-time clock	Yes
Supported PLC protocols	CODESYS 3.X ModbusRTU Client Modbus RTU server Modbus TCP Client Modbus TCP server
Real-time clock deviation	<100 ppm at 25°C
Number of colors	16 M
Display	With backlighting
Display type	Color TFT
Display properties	Touchscreen
Display size	15.6"
Backup battery	Rechargeable lithium battery
DC operating voltage range	10 V ... 32 V
Display resolution	1366x768 pixels
Nominal operating voltage DC	24 V
Current consumption at nominal operating voltage	1.2 A
Certification	c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 Zone III
Storage temperature	-20 °C ... 70 °C
Relative air humidity	5 - 85% Non-condensating
Degree of protection	IP20 IP66
Note on degree of protection	IP66 front side
Ambient temperature	-20 °C ... 60 °C
Note on ambient temperature	for vertical mounting
Product weight	4100 g
SD card slot	1
Additional functions	RS232 communication function

<b>Feature</b>	<b>Value</b>
Type of mounting	Front panel mounting
Note on materials	RoHS compliant
Ethernet interface, connection type	Socket
Ethernet interface, connection technology	RJ45
Ethernet interface, number of poles/wires	8
Ethernet interface, transmission rate	10/100 mbps 1000 Mbit/s
Ethernet interface, function	Programming
Ethernet interface 2, type of connection	2x port
Ethernet interface 2, connection technology	RJ45
Ethernet interface 2, number of pins/wires	8
Ethernet interface 2, transmission rate	10/100 mbps
Ethernet interface 2, function	Programming
USB interface, function	File transfer
USB-interface, connection type	2x port
USB interface	USB 2.0, type A
Programming software	Designer Studio
CPU data	2 GB RAM