


Semi-rotary drive DRRS-20-180-FH-PA

Part number: 8163611

FESTO



 General operating condition

Data sheet

Feature	Value
Size	20
Cushioning angle	27.5 deg
Setting range of swivel angle for each end position	+10 /-100 deg
Axial eccentricity of plate	<0.07 mm
Swivel angle	180 deg
Min. swivel angle	45 deg
Max. swivel angle	200 deg
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Structural design	Gear rack/pinion
Position sensing	For proximity sensor
Symbol	00991265
Operating pressure	0.3 MPa ... 0.8 MPa
Operating pressure	3 bar ... 8 bar
Repetition accuracy	0.07 deg
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 9 according to ISO 14644-1
Storage temperature	-20 °C ... 60 °C
Ambient temperature	0 °C ... 60 °C
Theoretical torque at 6 bar	3.3 Nm
Permissible mass moment of inertia	0.0175 kgm ²
Max. bending moment	5 Nm
Max. axial load static	350 N
Product weight	790 g
Type of mounting	With mounting kit With through-hole With internal thread
Pneumatic connection	M5
Note on materials	RoHS-compliant

Feature	Value
Seals material	NBR TPE-U(PU)
Housing material	Aluminum, anodized
Flange shaft material	Wrought aluminum alloy
Pinion material	Tempered steel