



# Filter MS2-LF-QS6-C-P-M-F1A-B

Part number: 8181092

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	2
Series	MS
Mounting position	Vertical $\pm 5^\circ$
Grade of filtration	5 $\mu\text{m}$
Condensate drain	Manual, rotating
Structural design	Sinter filter with centrifugal separator
Symbol	00991519
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Operating pressure	14.5 psi ... 145 psi
Normal nominal flow rate (normalized to DIN 1343)	250 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Storage temperature	-5 $^\circ\text{C}$ ... 50 $^\circ\text{C}$
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [6:4:4]
Temperature of medium	-5 $^\circ\text{C}$ ... 50 $^\circ\text{C}$
Ambient temperature	-5 $^\circ\text{C}$ ... 50 $^\circ\text{C}$
Product weight	42.1 g
Type of mounting	With accessories
Pneumatic connection 1	QS-6
Pneumatic connection 2	QS-6
Note on materials	RoHS compliant
Seals material	NBR
Material of spring	High-alloy steel
Compressed air filter material	Protective grounding
Housing material	PA-reinforced
Diaphragm material	NBR
Material of bowl	PC