

Sub-base VABS-K2-10S-16-G18-P

Part number: 8186874

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	10
Nominal width	1.6 mm
Valve size	10 mm
Fluid connector	Internal thread G1/8
Mounting position	Any
Structural design	Connection direction at side
Max. no. of valve positions	1
Flow direction	Non-reversible
Operating medium	Liquid media Gaseous media
Information on operating and pilot media	Observe resistance of materials that come into contact with media
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 70 °C
For use in the food industry	See supplementary material information
Temperature of medium	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Max. tightening torque for valve mounting	0.2 Nm
Max. tightening torque of pneumatic fitting	7 Nm
Max. tightening torque	0.6 Nm
Product weight	20 g
Sub-base mounting type	With through-hole
Pneumatic valve mounting type	With internal thread
Note on materials	RoHS-compliant
Material of sub-base	PEEK