

# Shock absorber retainer DADP-ES-G8-25

Part number: 8159237

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	25
Mounting position	Any
Structural design	Stop lever
Max. impact velocity	0.8 m/s
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Ambient temperature	0 °C ... 60 °C
Max. stop force	1100 N
Max. tightening torque	8.4 Nm
Tightening torque tolerance	± 20 %
Product weight	503 g
Type of mounting	Via through-hole and centering sleeve
Note on materials	RoHS-compliant
Lever material	Wrought aluminum alloy
Material of screws	Steel, galvanized