

Parallel kit EAMM-U-60-D40-60P-61

Part number: 8164735

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	60
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	26.7 kgmm ²
No-load driving torque	0.07 Nm
Transferable torque	3 Nm
Product weight	926 g
Interface code, actuator	D40B
Interface code, motor in	60P 60PA
Note on materials	RoHS-compliant