

Standards-based cylinder DSBC-32-500-D3-PPSA-N3

Part number: 8165461

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Stroke	500 mm
Piston diameter	32 mm
Piston rod thread	M10x1.25
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Conforms to standard	ISO 15552
Piston rod end	External thread
Structural design	Piston Piston rod Profile barrel
Position sensing	Via proximity switch
Symbol	00992970
Variants	Piston rod at one end
Operating pressure	0.08 MPa ... 1.2 MPa
Operating pressure	0.8 bar ... 12 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	0.4 J
Cushioning length	17 mm
Theoretical force at 6 bar, retracting	415 N
Theoretical force at 6 bar, advancing	483 N
Moving mass	560 g
Moving mass at 0 mm stroke	110 g
Additional moving mass per 10 mm stroke	9 g
Product weight	2029 g
Basic weight with 0 mm stroke	480 g
Additional weight per 10 mm stroke	31 g
Type of mounting	With internal thread With accessories
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Cover material	Die-cast aluminum, coated

Feature	Value
Piston seal material	TPE-U(PU)
Material of piston	Wrought aluminum alloy
Piston rod material	High-alloy steel
Piston rod wiper material	TPE-U(PU)
Buffer seal material	TPE-U(PU)
Cushion piston material	POM
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized
Nut material	Steel, galvanized
Rod wiper material	TPE-E
Material of bearing	Metal polymer compound
Flange screws material	Steel, galvanized