

Forwarding supply CPX-AP-A-W-1-PP-5P

Part number: 8169617

FESTO



 General operating condition

Data sheet

Feature	Value
Dimensions W x L x H	50.1 mm x 153 mm x 45.6 mm
Width dimension	50.1 mm
Type of mounting	On H-rail with accessories with through-hole for M5 screw with accessories with through-hole for M6 screw with accessories
Product weight	182 g
Mounting position	Arbitrary, on H-rail: horizontal
Ambient temperature	-20 °C ... 50 °C
Note on ambient temperature	Observe ambient temperature derating according to IEC 61131-2:2017
Storage temperature	-20 °C ... 70 °C
Relative air humidity	5 - 95 % Non-condensing
Nominal altitude of use above sea level	≤ 2000 m ASL (≥ 79.5 kPa)
Max. installation height	3500 m
Information on max. installation height	Observe ambient temperature derating according to IEC 61131-2:2017
Corrosion resistance class (CRC)	1 - Low corrosion stress
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Note on vibration resistance	SG1 on H-rail SG2 on direct mounting Transport application test with severity level 1 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Note on shock resistance	30 g/11 ms as per EN 60068-2-27 SG1 on H-rail SG2 on direct mounting Shock test with severity level 1 as per FN 942017-5 and EN 60068-2-27
Protection class	III
Overvoltage category	II
LABS (PWIS) conformity	VDMA24364-B2-L
Material fire test	UL94 V-0 (housing)
Note on materials	RoHS-compliant Halogen-free Free of phosphoric acid ester
Housing material	PA-reinforced
Material of flange	Die-cast zinc, nickel-plated
Material of screws	Steel, nickel-plated
Seals material	PU foam
Voltage forwarding, function	Outgoing electronics/sensors and load and functional earth

Feature	Value
Voltage forwarding, connection type	Plug
Voltage forwarding, connection technology	Push-pull as per IEC 61076-3-126
Voltage forwarding, number of pins/wires	5
Voltage forwarding, connection pattern	00997378
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Note on nominal operating voltage DC	2X24 V [XD2,PS,PL] Protected Extra-Low-Voltage as per IEC 60204-1
Nominal operating voltage DC load	24 V
Nominal operating voltage DC for electronics/sensors	24 V
Nominal current	10 A
Max. power supply	2 x 10 A (external fuse required)
Potential separation between the supply voltages electronics/sensor technology and load/valves	yes