

Sub-base kit DADP-SP-G9-20-R

Part number: 8173535

FESTO



 General operating condition

Data sheet

Feature	Value
Size	20
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C ... 60 °C
Max. stop force	300 N
Max. tightening torque	1.5 Nm
Tightening torque tolerance	± 15 %
Product weight	160 g
Type of mounting	Direct fastening via thread
Note on materials	RoHS-compliant
Stops material	High-alloy steel
Seals material	NBR
Plate material	Wrought aluminum alloy, anodized
Material of screws	Steel