


Air solenoid valve JMFDH-5-1/8

Part number: 8821

FESTO



General operating condition

Data sheet

| Feature | Value |
|---|--|
| Valve function | 5/2, bistable, dominant |
| Actuation type | Electrical |
| Width | 26 mm |
| Normal nominal flow rate (normalized to DIN 1343) | 601 l/min |
| Pneumatic working port | G1/8 |
| Operating voltage | Via solenoid coil, to be ordered separately |
| Operating pressure | 0.25 MPa ... 0.8 MPa |
| Operating pressure | 2.5 bar ... 8 bar |
| Structural design | Plate seat |
| Certification | c UL us - Recognized (OL) |
| Degree of protection | IP65 |
| Nominal width | 5 mm |
| Width dimension | 27 mm |
| Exhaust air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Detenting |
| Type of control | Pilot-controlled |
| Flow direction | Non-reversible |
| Symbol | 00995980 |
| Lap | Underlap |
| Max. switching frequency | 16 Hz |
| Changeover time | 16 ms |
| Max. positive test pulse with 0 signal | 2200 µs |
| Max. negative test pulse on 1 signal | 3700 µs |
| Coil characteristics | See solenoid coil, to be ordered separately |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C ... 60 °C |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -5 °C ... 40 °C |
| Product weight | 260 g |
| Electrical connection | Via F coil, to be ordered separately |

| Feature | Value |
|---------------------------|--|
| Type of mounting | On terminal strip With through-hole |
| Pilot exhaust air port 82 | M5 |
| Pilot exhaust air port 84 | M5 |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 2 | G1/8 |
| Pneumatic connection 3 | G1/8 |
| Pneumatic connection 4 | G1/8 |
| Pneumatic connection 5 | G1/8 |
| Note on materials | RoHS-compliant |
| Seals material | NBR TPE-U(PU) |
| Housing material | Die-cast aluminum |