

Air solenoid valve MFH-5/3G-D-3-C

Part number: 151873

FESTO



[PDF General operating condition](#)

Datasheet product reliability

The information in this "Product reliability data sheet" is based on products being used as intended. This includes complying with all specifications in data sheets, catalogues, user documentation and the general operating conditions. The user alone is responsible for determining whether a product is suitable for a particular application.

| Feature | Value |
|---|---|
| Certificate issuing authority | UL MH19482 DNV-TAA000032X |
| Service-life value B_{10} ¹⁾ | 10 Mio cycles |
| Fault exclusion | Automatic change of the normal position of the switching element of the main stage without a control signal. The control signal for pilot-controlled solenoid valves consists of the electrical control signal for the valve coil and the pneumatic signal (pilot air supply) of the pilot valve. Bursting of the valve housing: externally directed failure of the material structure with a sudden release of the medium and associated pressure drop (according to ISO 5598, 3.2.85). |
| Well-tried component ²⁾ | Yes |
| Design characteristics | Mechanical spring return Spring return to mid-position on logic 0 |
| Lap | Overlap |
| Vibration resistance | Transport application test with severity level 1 in accordance with FN942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Max. positive test pulse with 0 signal | 2200 μ s |
| Max. negative test pulse with 1 signal | 3700 μ s |

- 1) The ascertainment of characteristic service life values is based on the ISO 19973 "Pneumatic fluid power - Assessment of component reliability by testing".
- 2) The product is a well-tried product for a safety-related application according to ISO 13849-1. The relevant basic and well- tried safety principles according ISO 13849-2 for this product are fulfilled. The suitability of the product for a precise application must be verified by the user.