


# Air solenoid valve VUVS-LT25-T32U-MD-G14-F8-1B2

Part number: 8035206



 [General operating condition](#)

## Datasheet product reliability

The information in this "Product reliability data sheet" is based on products being used as intended. This includes complying with all specifications in data sheets, catalogues, user documentation and the general operating conditions. The user alone is responsible for determining whether a product is suitable for a particular application.

Feature	Value
Relevant basic safety principles <sup>1)</sup>	Yes
Service-life value B <sub>10</sub> <sup>2)</sup>	10 Mio cycles
Service-life value B10D <sup>3)</sup>	20 Mio cycles
Relevant well-tried safety principles <sup>4)</sup>	Yes
Fault exclusion	Bursting of the valve housing: externally directed failure of the material structure with a sudden release of the medium and associated pressure drop (according to ISO 5598, 3.2.85). Failure of the underlap Standard flow rate 6 to 0 bar (2→1+2→3; 2→1; 2→3; 4→1+4→5; 4→1; 4→5) is equal to or greater than the standard nominal flow rate of the valve at exhausted operating pressure (port 1).
Well-tried component <sup>5)</sup>	Yes
Lap	Underlap
Max. positive test pulse with 0 signal	2000 µs
Max. negative test pulse with 1 signal	3600 µs

- 1) The product-relevant basic safety principles are fulfilled according to the ISO 13849-2.
- 2) The ascertainment of characteristic service life values is based on the ISO 19973 "Pneumatic fluid power - Assessment of component reliability by testing".
- 3) B10D value determined on the basis of ISO 13849-1: e.g. B10D=2\*B10. Whether this value is suitable for a specific application must be checked by the user.
- 4) The product-relevant well-tried safety principles are fulfilled according to the ISO 13849-2.
- 5) The product is a well-tried product for a safety-related application according to ISO 13849-1. The relevant basic and well- tried safety principles according ISO 13849-2 for this product are fulfilled. The suitability of the product for a precise application must be verified by the user.