



# Solenoid valve VUVX-BK10-T32U-MZH-F-1T1L

Part number: 8187063



[PDF General operating condition](#)

## Datasheet product reliability

The information in this "Product reliability data sheet" is based on products being used as intended. This includes complying with all specifications in data sheets, catalogues, user documentation and the general operating conditions. The user alone is responsible for determining whether a product is suitable for a particular application.

Feature	Value
Relevant basic safety principles <sup>1)</sup>	Yes
Service-life value B <sub>10</sub> <sup>2)</sup>	10 Mio cycles
Relevant well-tried safety principles <sup>3)</sup>	Yes
Fault exclusion	Automatic change of the normal position of the switching element of the main stage without a control signal. The redundant switch-off of the applied control signal for pilot-operated solenoid valves is possible by: a) switching off the electrical control signal for the valve coil (channel 1) and the pilot air supply (channel 2) or b) redundant switch-off of the pilot air supply. Bursting of the valve housing: externally directed failure of the material structure with a sudden release of the medium and associated pressure drop (according to ISO 5598, 3.2.85). Failure of the underlap 10%. Standard flow rate 6 to 0 bar (2->1+2->3; 2->1; 2->3; 4->1+4->5; 4->1; 4->5) is at least 10% of the standard nominal flow rate of the valve at exhausted operating pressure (port 1).
Well-tried component <sup>4)</sup>	Yes
Max. switching frequency	3 Hz
Design characteristics	Mechanical spring return Pneumatic spring return Supply air via duct 1
Lap	Underlap
Vibration resistance	Transport application test with severity level 2 in accordance with FN942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27
Max. positive test pulse with 0 signal	1400 µs
Max. negative test pulse with 1 signal	800 µs

- 1) The product-relevant basic safety principles are fulfilled according to the ISO 13849-2.
- 2) The ascertainment of characteristic service life values is based on the ISO 19973 "Pneumatic fluid power - Assessment of component reliability by testing".
- 3) The product-relevant well-tried safety principles are fulfilled according to the ISO 13849-2.
- 4) The product is a well-tried product for a safety-related application according to ISO 13849-1. The relevant basic and well- tried safety principles according ISO 13849-2 for this product are fulfilled. The suitability of the product for a precise application must be verified by the user.