


## Round cylinders DSNU

**FESTO**



## Key features

### At a glance

DSNU-8 ... 63

- Stainless steel piston rod
- Good running performance and long service life
- Piston rod with male and female thread

- Extensive range of accessories makes it possible to install the cylinder virtually anywhere


DSNU-8 ... 25



- The basic versions conform to ISO 6432, variants are based on these standards

### Wide choice of variants

DSNU	DSNU-...-MA	DSNU-...-MQ	DSNU-...-MH
<ul style="list-style-type: none"> <li>• Piston Ø 8 ... 63 mm</li> <li>• Cylinder barrel made of stainless steel</li> <li>• Bearing and end caps made of wrought aluminium alloy</li> </ul>	<ul style="list-style-type: none"> <li>• Piston Ø 8 ... 63 mm</li> <li>• Cylinder barrel made of stainless steel</li> <li>• Bearing cap with threaded flange</li> <li>• Short end cap with axial supply port</li> </ul>	<ul style="list-style-type: none"> <li>• Piston Ø 8 ... 63 mm</li> <li>• Cylinder barrel made of stainless steel</li> <li>• Bearing cap with threaded flange</li> <li>• Short end cap with lateral supply port</li> </ul>	<ul style="list-style-type: none"> <li>• Piston Ø 8 ... 63 mm</li> <li>• Cylinder barrel made of stainless steel</li> <li>• Direct mounting on bearing cap</li> <li>• Short end cap with lateral supply port</li> </ul>



DSNU-...-KP


- Piston Ø 8 ... 63 mm
- Cylinder barrel made of stainless steel
- With clamping unit

DSNU-...-Q

- Piston Ø 12 ... 63 mm
- Cylinder barrel made of stainless steel
- With square piston rod

DSNU-...-KE















- Piston Ø 8 ... 63 mm
- Through piston rod with stroke adjustment
- Adjustment range of the extended end position



### Cushioning types

	Cushioning P	Cushioning PPS	Cushioning PPV
<b>Operating mode</b>	<ul style="list-style-type: none"> <li>• The drive is fitted with polymer elastic end-position cushioning</li> </ul>	<ul style="list-style-type: none"> <li>• The drive is fitted with self-adjusting end-position cushioning</li> </ul>	<ul style="list-style-type: none"> <li>• The drive is fitted with adjustable end-position cushioning</li> </ul>
<b>Application</b>	<ul style="list-style-type: none"> <li>• Small loads</li> <li>• Low speeds</li> <li>• Low impact energies</li> </ul>	<ul style="list-style-type: none"> <li>• Small to medium loads</li> <li>• Low to medium speeds</li> <li>• Medium impact energies</li> </ul>	<ul style="list-style-type: none"> <li>• Medium to large loads</li> <li>• High speeds</li> <li>• High impact energies</li> </ul>
<b>Advantages</b>	<ul style="list-style-type: none"> <li>• No adjustment required</li> <li>• Saves time</li> </ul>	<ul style="list-style-type: none"> <li>• No adjustment required</li> <li>• Saves time</li> <li>• Powerful</li> </ul>	<ul style="list-style-type: none"> <li>• Very powerful</li> </ul>

## Key features

Variants from the modular product system		
Symbol	Key features	Description
	S2 Through piston rod	For working at both ends with the same force in the forward and return stroke, for attaching external stops
	KE Stroke adjustment, extending	Through piston rod with adjustment element mounted on one side. For limiting the extended end position and setting an exact stroke position.
	S6 Heat-resistant seals	Temperature resistance up to max. 120°C
	S10 Constant motion (slow speed) at low piston speeds	<ul style="list-style-type: none"> <li>• Break-away pressure: very low</li> <li>• Dynamic response: suitable for very slow, constant and stick-slip-free movements</li> </ul> Application example: slow, constant feed motion
	L Low friction	<ul style="list-style-type: none"> <li>• Break-away pressure: low</li> <li>• Dynamic response: suitable for very fast movements, especially at low operating pressures</li> </ul> Application example: very dynamic movements with no standstill
	...K2 Extended male piston rod thread	–
	K3 Female piston rod thread	–
	...K5 – Special piston rod thread	Metric standard thread to ISO
	...K6 – Shortened male piston rod thread	–
	...K8 – Extended piston rod	–
	R3 High corrosion protection	All external cylinder surfaces comply with corrosion resistance class CRC 3 to Festo standard 940070. The piston rod is made from corrosion- and acid-resistant steel
	R8 Dust protection (wiper) (32 ... 63 mm)	The cylinder has a hard-chrome-plated piston rod and a hard wiper, which protects against dry, dusty media
	A1 Wiper variant (12 ... 63 mm)	Increased chemical resistance: For longer service life, e.g. when using cooling lubricants.
	A6 Metal wiper (32 ... 63 mm)	The cylinder has a hard-chrome-plated piston rod and metal wiper, which scrapes off hard particles (e.g. welding spatter) that stick to the piston rod. For use in welding systems, for example
	F1A Recommended for production plants for manufacturing lithium-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)

### Longer service life with bellows kit DADB



The bellows protects the piston rod, the seal and the bearing from the effects of a wide range of media, which has a positive impact on the service life of these components.


The bellows kit is a leak-free system. To prevent unwanted media from being drawn in, the supply and exhaust air for the kit must be ducted via a pressure compensation hole in the connection part [1].

The kit protects the piston rod, seal and bearing against a wide variety of media, for example:

- Dust
- Grease
- Chippings
- Fuel
- Oil


Peripherals overview

DSNU-...



## Peripherals overview

Mounting attachments and accessories		Piston Ø	DSNU				DSNU-Q		→ Page/Internet
			MA	MQ	MH	KP			
[1]	Round cylinder DSNU								
[2]	Hex nut MSK	16 ... 25	■	■	■	■	■	■	64
[3]	Bellows kit <sup>2)</sup> DADB	12 ... 63	■	■	■	–	–	–	66
[4]	One-way flow control valve GRLA/GRLZ	8 ... 63	■	■	■	■	■	■	75
[5]	Push-in fitting QS	8 ... 63	■	■	■	■	■	■	95
[6]	Clevis foot LBN/CRLBN	8 ... 63	■	–	–	–	■	■	63
[7]	Foot mounting HBN/CRHBN/CRH	8 ... 63	■	■	■	–	■	■	58
[8]	Flange mounting FBN/CRFBN/CRFV	8 ... 63	■	■	■	–	■	■	60
[9]	Swivel mounting <sup>1)</sup> WBN	8 ... 63	■	■	■	–	■	■	62
[10]	Swivel mounting <sup>1)</sup> SBN	20 ... 63	■	■	■	–	■ Ø 20 ... 50	■	62
[11]	Mounting kit SMBR	8 ... 63	■	■	■	■	■	■	72
[12]	Mounting kit SMBR-...S6	8 ... 63	■	■	■	■	■	■	72
[13]	Proximity switch SMT/CRSMT/SDBT	8 ... 63	■	■	■	■	■	■	72
	Position transmitter SDAS/SDAT/SMAT	8 ... 63	■	■	■	■	■	■	74
[14]	Self-aligning rod coupler FK/CRFK/DARP	8 ... 63	■	■	■	■	■	■	<?>
[15]	Rod clevis SG/CRSG	8 ... 63	■	■	■	■	■	■	<?>
[16]	Coupling piece KSG/KSZ	12 ... 63	■	■	■	■	■	■	64
[17]	Rod eye SGS/CRSGS	8 ... 63	■	■	■	■	■	■	64
[18]	Right-angle clevis foot LQG	32 ... 63	■	■	■	■	■	■	63
[19]	Rod clevis SGA	32 ... 63	■	■	■	■	■	■	<?>
[20]	Clevis foot LBG	32 ... 63	■	■	■	■	■	■	65
[21]	Guide unit FEN	8 ... 25	■	■	■	–	–	–	65

 **Note**

- 1) Cannot be used on the bearing cap in combination with protective bellows kit DADB.
- 2) The bellows kit protects the cylinder (piston rod, seal and bearings) against a wide range of media and thus prevents premature wear. It can only be used in combination with an extended piston rod (K8)

Type codes

DSNU-...

<b>001</b>	<b>Series</b>
<b>DSNU</b>	Round cylinder, double-acting, based on ISO 6432

<b>002</b>	<b>Piston diameter [mm]</b>
<b>8</b>	8
<b>10</b>	10
<b>12</b>	12
<b>16</b>	16
<b>20</b>	20
<b>25</b>	25
<b>32</b>	32
<b>40</b>	40
<b>50</b>	50
<b>63</b>	63

<b>003</b>	<b>Stroke range [mm]</b>
<b>...</b>	1 ... 500

<b>004</b>	<b>Cushioning</b>
<b>P</b>	Elastic cushioning rings/plates on both sides
<b>PPS</b>	Pneumatic cushioning, self-adjusting at both ends
<b>PPV</b>	Pneumatic cushioning, adjustable at both ends

<b>005</b>	<b>Position sensing</b>
<b>A</b>	For proximity sensor

<b>006</b>	<b>Special material properties</b>
	None
<b>F1A</b>	Recommended for production plants for manufacturing lithium-ion batteries, F1A

<b>007</b>	<b>Cylinder end cap</b>
	Standard
<b>MA</b>	Axial air connection, end cap
<b>MH</b>	Direct mounting, bearing cap
<b>MQ</b>	Transverse supply port, end cap

<b>008</b>	<b>Protection against rotation</b>
<b>Q</b>	Square piston rod
	None

<b>009</b>	<b>Piston rod type</b>
	At one end
<b>S2</b>	Through piston rod

<b>010</b>	<b>Stroke adjustment</b>
	Without
<b>15KE</b>	15 mm, advancing
<b>25KE</b>	25 mm, advancing
<b>50KE</b>	50 mm, advancing

<b>011</b>	<b>Piston rod thread extension</b>
	None
<b>...K2</b>	1 ... 70 mm

<b>012</b>	<b>K6 - Shortened male piston rod thread</b>
	None
<b>K6</b>	1 ... 10 mm

<b>013</b>	<b>Piston rod thread type</b>
	Male thread
<b>K3</b>	Female thread

<b>014</b>	<b>Custom thread</b>
<b>"M10"K5</b>	M10
<b>"M12"K5</b>	M12
<b>"M16"K5</b>	M16

<b>015</b>	<b>Piston rod extension</b>
	None
<b>...K8</b>	1 ... 500 mm

<b>016</b>	<b>Clamping unit</b>
	None
<b>KP</b>	attached

<b>017</b>	<b>Temperature range</b>
	Standard
<b>S6</b>	Heat-resistant seals max. 120 °C

<b>018</b>	<b>Constant motion</b>
	Standard
<b>S10</b>	Uniform, slow movement

<b>019</b>	<b>Running characteristic</b>
	None
<b>L</b>	Low friction


<b>020</b>	<b>Corrosion protection</b>
	Standard
<b>R3</b>	High corrosion protection

<b>021</b>	<b>Scraper variant</b>
	Standard
<b>A1</b>	Increased chemical resistance (FKM seal)
<b>A6</b>	Metal scraper
<b>R8</b>	Dust protection


<b>022</b>	<b>EX certification EU</b>
	None
<b>EX4</b>	II 2GD

## Datasheet


## P cushioning





## PPV cushioning




## PPS cushioning



-  - Diameter  
 8 ... 25 mm  
 ISO 6432

-  - Diameter  
 32 ... 63 mm

-  - Stroke length  
 1 ... 500 mm,  
 longer strokes on request


**General technical data**

Piston Ø	8	10	12	16	20	25	32	40	50	63	
Conforms to standard	ISO 6432						-				
Pneumatic connection	M5	M5	M5	M5	G1/8	G1/8	G1/8	G1/4	G1/4	G3/8	
Piston rod thread	M4	M4	M6	M6	M8	M10x1.25	M10x1.25	M12x1.25	M16x1.5	M16x1.5	
Stroke <sup>1)</sup> [mm]	1 ... 100		1 ... 200		1 ... 320	1 ... 500					
Design	Piston/piston rod/cylinder barrel										
Cushioning											
DSNU-...-P	Elastic cushioning rings/plates at both ends										
DSNU-...-PPV	-		Cushioning, adjustable at both ends								
DSNU-...-PPS	-		Cushioning, self-adjusting at both ends								
Cushioning length											
DSNU-...-PPV [mm]	-		9	12	15	17	14	18	20	21	
DSNU-...-PPS [mm]	-		12	15	17	14	18	20	21		
Position sensing	Via proximity switch										
Type of mounting	Direct mounting (variant MH only)										
	With accessories										
Mounting position	Any										

1) Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.  
 Longer strokes on request.

Datasheet

Operating and environmental conditions												
Piston Ø		8	10	12	16	20	25	32	40	50	63	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]										
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)										
Operating pressure <sup>1)</sup>												
DSNU-...	[MPa]	0.15 ... 1 <sup>3)</sup>			0.1 ... 1							
	[bar]	1.5 ... 10 <sup>3)</sup>			1 ... 10							
DSNU-...-S10	[MPa]	-		0.05 ... 1	0.03 ... 1			0.02 ... 1				
	[bar]	-		0.5 ... 10	0.3 ... 10			0.2 ... 10				
DSNU-...-L <sup>2)</sup>	[MPa]	0.06 ... 1			0.05 ... 1		0.04 ... 1		0.02 ... 1			
	[bar]	0.6 ... 10			0.5 ... 10		0.4 ... 10		0.2 ... 10			
DSNU-...-A6	[MPa]	-							0.2 ... 1			
	[bar]	-							2 ... 10			
Ambient temperature <sup>4)</sup>												
DSNU-...	[°C]	-20 ... +80										
DSNU-...-S6	[°C]	0 ... +120										
DSNU-...-S10/L	[°C]	+5 ... +80										
DSNU-...-R3	[°C]	-20 ... +80										
DSNU-...-A1	[°C]	0 ... +80										
DSNU-...-S6-A6	[°C]	-							0 ... +120			
Corrosion resistance class CRC <sup>5)</sup>												
DSNU-...		2 - Moderate corrosion stress										
DSNU-...-R3		3 - High corrosion stress										
DSNU-...-F1A		0 - no corrosion stress										
DSNU-...-P/PPV		See certificate								-		

- 1) With variant S2 (through piston rod) or variant KE (stroke adjustment), the minimum operating pressure may increase slightly after an idle period of > 24 hours.
- 2) Values apply only for strokes ≤ 500 mm and after 10 double strokes. In combination with cushioning PPV/PPS, the specifications only apply outside the cushioning range.
- 3) For DSNU-12... PPV (pneumatic cushioning, adjustable at both ends): 0.2 ... 1 MPa (2 ... 10 bar)
- 4) Note operating range of proximity switches.
- 5) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

ATEX <sup>1)</sup>	
ATEX category for gas	II 2G
Type of (ignition) protection for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T120°C Db
Explosion-proof ambient temperature	-20 °C ≤ Ta ≤ +60 °C
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)	To UK explosion regulations
Explosion protection certification outside the EU	EPL Db (GB)
	EPL Gb (GB)

- 1) Note the ATEX certification of the accessories.

Weight [g]											
Piston Ø		8	10	12	16	20	25	32	40	50	63
<b>DSNU-...</b>											
Product weight with 0 mm stroke		34.6	37.3	75	89.9	186.8	238	370.5	661	1087	1445
Additional weight per 10 mm stroke		2.4	2.7	4	4.6	7.2	11	15.5	24	40	44
Moving mass with 0 mm stroke		7.5	8.5	18.5	23	44	71	121	230	413	459
Moving mass per 10 mm stroke		1	1	2	2	4	6	9	16	25	25
<b>DSNU-...-S2</b>											
Moving mass with 0 mm stroke		12	12.5	30	34.5	70	113	182	363	638	701
Moving mass per 10 mm stroke		2	2	4	4	8	12	18	32	50	50
<b>DSNU-...-KE</b>											
Moving mass with 0 mm stroke	[15KE]	17	17.5	-	-	-	-	-	-	-	-
	[25KE]	-	-	46	50.5	99	142	251	469	839	902
	[50KE]	-	-	-	-	-	-	-	491	918	981
Moving mass per 10 mm stroke		2	2	4	4	8	12	18	32	50	50

# Datasheet

Speed [mm/s] <sup>1)</sup>							
Piston Ø	16	20	25	32	40	50	63
Speed with stick-slip-free operation, horizontal, without load, at 0.6 MPa (6 bar)	10 ... 100			8 ... 100			5 ... 100

1) Measurements of less than 1 mm/s were not conducted

Forces [N] and impact energy [J]										
Piston Ø	8	10	12	16	20	25	32	40	50	63
Theoretical force at 0.6 MPa (6 bar), advancing	30	47	68	121	189	295	483	753	1178	1870
Theoretical force at 0.6 MPa (6 bar), retracting	23	40	51	104	158	247	415	633	990	1682
Impact energy in the end positions for P cushioning <sup>1)</sup>										
DSNU-...	0.03	0.05	0.07	0.15	0.2	0.3	0.4	0.7	1	1.3
DSNU-...-S6	0.015	0.025	0.035	0.075	0.1	0.15	0.2	0.35	0.5	0.65
DSNU-...-KE	0.025	0.025	0.055	0.12	0.16	0.24	0.32	0.56	0.8	1


1) The values are reduced by approx. 50% at an ambient temperature of 80 °C

Permissible impact velocity: 
$$V = \sqrt{\frac{2 \times E}{m_1 + m_2}}$$

Maximum permissible mass: 
$$m_2 = \frac{2 \times E}{V^2} - m_1$$

V Perm. impact velocity  
 E Max. impact energy  
 m1 Moving mass (drive)  
 m2 Moving payload


## Average piston speed v as a function of payload m in combination with cushioning PPS



Datasheet


Average piston speed  $v$  as a function of payload  $m$  in combination with cushioning PPS

Piston  $\varnothing$  40




- DSNU-40-50
- ⋯ DSNU-40-100
- - - DSNU-40-200

Piston  $\varnothing$  50



- DSNU-50-50
- ⋯ DSNU-50-100
- - - DSNU-50-200

Piston  $\varnothing$  63



- DSNU-63-50
- ⋯ DSNU-63-100
- - - DSNU-63-200


Note:

Engineering software for  
 P cushioning  
 PPV cushioning  
 PPS cushioning  
 → <https://www.festo.com/x/pneumatic-sizing>



Average piston speed = Stroke/  
 movement time

Datasheet

Max. transverse force  $F_q$  as a function of projection  $l$





DSNU-...



- DSNU-8/10
- · - · - DSNU-12/16
- - - DSNU-20
- · · · · DSNU-25

- · - · - DSNU-32
- - - DSNU-40
- - - DSNU-50/63

DSNU-...-S2 – Through piston rod




- DSNU-8/10
- · - · - DSNU-12/16
- - - DSNU-20
- · · · · DSNU-25

- · - · - DSNU-32
- - - DSNU-40
- - - DSNU-50/63

Datasheet

Materials

Sectional view



Round cylinder	8 ... 25	32 ... 63
[1] Piston rod		
DSNU-...	High-alloy steel	
DSNU-...-R3	High-alloy stainless steel	
DSNU-...-A6	-	Hard-chrome-plated tempered steel
[2] Piston rod bearing	Sintered bronze	
[3] Bearing cap	Wrought aluminium alloy, colourless anodised	
[4] Cylinder barrel	High-alloy stainless steel	
[5] End cap	Wrought aluminium alloy, colourless anodised	
[6] Swivel bearing	Polymer	
- Piston rod wiper seal		
DSNU-...	TPE-U(PU)	
DSNU-...-S6/-S10/-L/-A1	FPM	
DSNU-...-R3	TPE-U (PU) media seal (modified for resistance to hydrolysis and cleaning)	
Piston rod scraper		
DSNU-...-A6	-	CuZn
Stroke adjustment DSNU-...-KE		
Stop element	PE-UHMW	
Threaded coupling	Anodised aluminium	
LABS (PWIS) conformity	VDMA24364-B1/B2-L <sup>1)</sup>	
Cleanroom class	Class 6 to ISO 14644-1	
Note on materials		
DSNU-...	RoHs-compliant	
DSNU-...-S10	Contains paint-wetting impairment substances	
DSNU-...-F1A	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)	


1) Applies to all variants except S10

Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-8 ... 25



∅ [mm]	AM	B ∅ h8	BE	BF	CD ∅ H9	D ∅	D4 ∅	E	EE	EW	G
8	12	12	M12x1.25	12	4	16	9.3	14	M5	8	10
10							11.3				
12	16	16	M16x1.5	17	6	20	13.3	18	G1/8	12	16
16							17.3				
20	20	22	M22x1.5	20	8	30	21.3	26	16	16	
25	22			22			22				26.5

∅ [mm]	KK	KV	KW	MM ∅	L	L2	PL	VD	WF ±1.2	XC ±1	ZJ	∅1
8	M4	19	6	4	6	46	6	2	16	64	62	-
10						50						
12	M6	24	8	6	9	56	6	2	22	75	72	5
16						68						
20	M8	32	11	8	12	68	8.2	2	24	95	92	7
25	M10x1.25			10		69.5						


Datasheet

Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-8 ... 25



MQ – Lateral supply port, short end cap



MA – Axial supply port, short end cap



MH – With direct mounting



## Datasheet

ø [mm]	B ø h8	D2 ø	D3 ø	E	EE	F	FB ø	G	L2		
									DSNU-...		
									-MQ	-MA	-MH
8	12	10.5	6	24	M5	3	3.4	10	46	43.6	53.5
10		12.5								43.1	53.8
12	16	14.5	8	30			4.5		50	47.7	62
16		17.5							56	53.7	67.8
20	22	21.7	10	40	G1/8	5.5	16	68	66.5	81.5	
25		26.7	11			6.6		69.5	68.5	86.2	

ø [mm]	L3	L4	L5	R	RT	TG	T1	U0	WF	ZJ		
										DSNU-...		
										-MQ	-MA	-MH
8	7.6	5	14	12	M3	18	3.4	16	8	62	59.6	61.5
10	7.1										59.1	61.8
12	7.7	6	18.1	16	M4	23	4.5	22	10	72	69.7	72
16										78	75.7	77.8
20	14.5	7.5	22.4	22	M5	31	5.5	28		92	90.5	91.5
25	14		25.2	25			6.6	32		11	97.5	96.5


Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-8 ... 25

S2 – Through piston rod




Note

The thread types at both piston rod ends are identical. In combination with variant Q, the left piston rod end is square, the right piston rod end round.


- + = plus stroke length
- ++ = plus 2x stroke length

KE – Stroke adjustment




- + = plus stroke length
- ++ = plus 2x stroke length


K2 – Extended male piston rod thread




K6 – Shortened male piston rod thread




K3 – Female piston rod thread



K5 – Special piston rod thread



K8 – Extended piston rod



Note

If variant K8 is required in combination with S2, the piston rod will only be extended at one end.

## Datasheet

∅ [mm]	A1 max.	A2 max.	A3 max.	A5		AF	AM	D8 ∅	KF	KK	
				DSNU-...						Basic thread	Special thread <sup>1)</sup>
				-15KE	-25KE						
8	15	50	4	27.5	-	-	12	12	-	M4	-
10						-			-		
12	20	100		-	43	-	16	15	-	M6	-
16						-			-		
20	25	110	8	-	47	12	20	20	M4	M8	-
25	35	150				22	M6		M10x1.25	M10	

1) The special threads are only available as male threads. The scope of delivery does not include a hex nut for the piston rod thread


∅ [mm]	L13 +1	T4	WF ±1.2	ZJ			ZM	⊖ 2	⊖ 3
				DSNU-...					
				-MQ	-MA	-MH			
8	78	-	16	62	59.6	61.5	78.4	7	10
10		-			59.1	61.8			
12	94	-	22	72	69.7	72	94	10	13
16	100	-		78	75.7	77.8			
20	116	2	24	92	90.5	91.5	116	13	17
25	125.5	2.6	28	97.5	96.5	97.2	125.5		

Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-32 ... 63



∅ [mm]	AM	B ∅ h8	BE	BF	B4	CD ∅ H9	D ∅	D1 ∅	D4 ∅	E	EE	EW
32	22	30	M30x1.5	26	5	10	41	42	33.6	38	G1/8	16
40	24	38	M38x1.5	30	6	12	49	50	41.6	45	G1/4	18
50	32	45	M45x1.5	33	8	16	57	60	52.4	-		G3/8
63							70				65.4	

∅ [mm]	G	KK	KW	MM ∅	L	L2	PL	VD	WF ±1.2	XC ±1	ZJ	∅C1	∅C2
32	19	M10x1.25	8	12	13	69.5	9	2	34	117.5	103.5	10	16
40	25	M12x1.25	10	16	15	84.6	12	3	39	139.6	123.6	13	18
50		M16x1.5		20	16	86.2			44	147.2	130.2	17	24
63	28					94.2	13	45	156.2	139.2			


Datasheet

Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-32 ... 63


MQ – Lateral supply port, short end cap




MA – Axial supply port, short end cap



MH – With direct mounting



[1] Centring holes  
(2 centring sleeves included in the scope of delivery)  
+ = plus stroke length



∅ [mm]	B ∅ h8	B2	E	EE	G	F	FB ∅	D2 ∅	D3 ∅	D5 ∅	D6 ∅	L1	L2		
													DSNU-...		
													-MQ	-MA	-MH
32	30	1	48	G1/8	19	4	6.6	34	11	9	30	3	69.5	65.5	85.5
40	38		54	G1/4	25		9	42	14	12	38	4	84.6	77.6	104.6
50	45	64	11			53	18	15					45	86.2	86.2
63		2	72	G3/8	28	11	66	18	15	45	4	94.2	94.2	117.2	


∅ [mm]	L3	L4	L5	R	RT	T0	T1	T2	TG	U0	WF	ZJ		
												DSNU-...		
												-MQ	-MA	-MH
32	15	12	25	30	M5	19	6.6	2.1	38	40	12	103.5	99.5	97.5
40	18	15	32	38		24	9	2.6	42	48		123.6	116.6	116.6
50	25		35	42	M6	32	32	50	58	15	130.2	130.2	124.2	
63	28	36	44	M8	36	36	11	3.1	52	72	15	139.2	139.2	132.2

Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-32 ... 63  
S2 – Through piston rod




Note

The thread types at both piston rod ends are identical. In combination with variant Q, the left piston rod end is square, the right piston rod end round.


+ = plus stroke length  
++ = plus 2x stroke length

KE – Stroke adjustment




+ = plus stroke length  
++ = plus 2x stroke length


K2 – Extended male piston rod thread




K6 – Shortened male piston rod thread




K3 – Female piston rod thread



K5 – Special piston rod thread



K8 – Extended piston rod



Note

If variant K8 is required in combination with S2, the piston rod will only be extended at one end.

## Datasheet

∅ [mm]	A1 max.	A2 max.	A3 max.	A5		AF	AM	D8 ∅	KF	KK	
				DSNU-...						Basic thread	Special thread <sup>1)</sup>
				-25KE	-50KE						
32	35	500	8	52	-	12	22	30	M6	M10x1.25	M10
40				56	81		24	35	M8	M12x1.25	M12
50	70		10	67	92	16	32	45	M10	M16x1.5	M16
63											

1) The special threads are only available as male threads. The scope of delivery does not include a hex nut for the piston rod thread

∅ [mm]	L13 +1	T4	WF ±1.2	ZJ			ZM	⊖ 2	⊖ 3
				DSNU-...					
				-MQ	-MA	-MH			
32	137.5	2.6	34	103.5	99.5	97.5	137.5	17	24
40	162.6	3.3	39	123.6	111.6	116.6	162.6	19	30
50	174.2	4.7	44	130.2	130.2	124.2	174.2	24	
63	184.2		45	139.2	139.2	132.2	184.2		

Datasheet

Ordering data				PPV – Pneumatic cushioning, adjustable at both ends		PPS – Pneumatic cushioning, self-adjusting at both ends	
Piston Ø	Stroke	P – Elastic cushioning rings/plates at both ends	A – With position sensing	A – With position sensing		A – With position sensing	
[mm]	[mm]	Part no.	Type	Part no.	Type	Part no.	Type
8	10	19177	DSNU-8-10-P-A	-		-	
	15	1908247	DSNU-8-15-P-A				
	20	1908248	DSNU-8-20-P-A				
	25	19178	DSNU-8-25-P-A				
	30	1908249	DSNU-8-30-P-A				
	40	19179	DSNU-8-40-P-A				
	50	19180	DSNU-8-50-P-A				
	60	1908250	DSNU-8-60-P-A				
	80	19181	DSNU-8-80-P-A				
100	19182	DSNU-8-100-P-A					
10	10	19183	DSNU-10-10-P-A	-		-	
	15	1908251	DSNU-10-15-P-A				
	20	1908252	DSNU-10-20-P-A				
	25	19184	DSNU-10-25-P-A				
	30	1908253	DSNU-10-30-P-A				
	40	19185	DSNU-10-40-P-A				
	50	19186	DSNU-10-50-P-A				
	60	1908254	DSNU-10-60-P-A				
	80	19187	DSNU-10-80-P-A				
100	19188	DSNU-10-100-P-A					
12	10	19189	DSNU-12-10-P-A	-		-	
	15	1908255	DSNU-12-15-P-A				
	20	1908256	DSNU-12-20-P-A				
	25	19190	DSNU-12-25-P-A				
	30	1908257	DSNU-12-30-P-A				
	40	19191	DSNU-12-40-P-A				
	50	19192	DSNU-12-50-P-A				
	60	1908258	DSNU-12-60-P-A				
	70	5249943	DSNU-12-70-P-A				
	80	19193	DSNU-12-80-P-A				
	100	19194	DSNU-12-100-P-A				
	125	19195	DSNU-12-125-P-A				
	150	5249947	DSNU-12-150-P-A				
	160	19196	DSNU-12-160-P-A				
200	19197	DSNU-12-200-P-A					
16	10	19198	DSNU-16-10-P-A	1908266	DSNU-16-10-PPV-A	1908274	DSNU-16-10-PPS-A
	15	1908259	DSNU-16-15-P-A	1908267	DSNU-16-15-PPV-A	1908275	DSNU-16-15-PPS-A
	20	1908260	DSNU-16-20-P-A	1908268	DSNU-16-20-PPV-A	1908276	DSNU-16-20-PPS-A
	25	19199	DSNU-16-25-P-A	33973	DSNU-16-25-PPV-A	559263	DSNU-16-25-PPS-A
	30	1908261	DSNU-16-30-P-A	1908269	DSNU-16-30-PPV-A	1908277	DSNU-16-30-PPS-A
	35	1908262	DSNU-16-35-P-A	1908270	DSNU-16-35-PPV-A	1908278	DSNU-16-35-PPS-A
	40	19200	DSNU-16-40-P-A	19229	DSNU-16-40-PPV-A	559264	DSNU-16-40-PPS-A
	50	19201	DSNU-16-50-P-A	19230	DSNU-16-50-PPV-A	559265	DSNU-16-50-PPS-A
	60	1908263	DSNU-16-60-P-A	1908271	DSNU-16-60-PPV-A	1908279	DSNU-16-60-PPS-A
	70	1908264	DSNU-16-70-P-A	1908272	DSNU-16-70-PPV-A	1908280	DSNU-16-70-PPS-A
	80	19202	DSNU-16-80-P-A	19231	DSNU-16-80-PPV-A	559266	DSNU-16-80-PPS-A
	100	19203	DSNU-16-100-P-A	19232	DSNU-16-100-PPV-A	559267	DSNU-16-100-PPS-A
	125	19204	DSNU-16-125-P-A	19233	DSNU-16-125-PPV-A	559268	DSNU-16-125-PPS-A
	150	1908265	DSNU-16-150-P-A	1908273	DSNU-16-150-PPV-A	1908281	DSNU-16-150-PPS-A
	160	19205	DSNU-16-160-P-A	19234	DSNU-16-160-PPV-A	559269	DSNU-16-160-PPS-A
	200	19206	DSNU-16-200-P-A	19235	DSNU-16-200-PPV-A	559270	DSNU-16-200-PPS-A

## Datasheet

Ordering data											
Piston Ø	Stroke	P – Elastic cushioning rings/plates at both ends		PPV – Pneumatic cushioning, adjustable at both ends		PPS – Pneumatic cushioning, self-adjusting at both ends					
[mm]	[mm]	A – With position sensing		A – With position sensing		A – With position sensing					
		Part no.	Type	Part no.	Type	Part no.	Type				
20	10	19207	DSNU-20-10-P-A	1908289	DSNU-20-10-PPV-A	1908297	DSNU-20-10-PPS-A				
	15	1908282	DSNU-20-15-P-A	1908290	DSNU-20-15-PPV-A	1908298	DSNU-20-15-PPS-A				
	20	1908283	DSNU-20-20-P-A	1908291	DSNU-20-20-PPV-A	1908299	DSNU-20-20-PPS-A				
	25	19208	DSNU-20-25-P-A	33974	DSNU-20-25-PPV-A	559271	DSNU-20-25-PPS-A				
	30	1908284	DSNU-20-30-P-A	1908292	DSNU-20-30-PPV-A	1908300	DSNU-20-30-PPS-A				
	35	1908285	DSNU-20-35-P-A	1908293	DSNU-20-35-PPV-A	1908301	DSNU-20-35-PPS-A				
	40	19209	DSNU-20-40-P-A	19236	DSNU-20-40-PPV-A	559272	DSNU-20-40-PPS-A				
	50	19210	DSNU-20-50-P-A	19237	DSNU-20-50-PPV-A	559273	DSNU-20-50-PPS-A				
	60	1908286	DSNU-20-60-P-A	1908294	DSNU-20-60-PPV-A	1908302	DSNU-20-60-PPS-A				
	70	1908287	DSNU-20-70-P-A	1908295	DSNU-20-70-PPV-A	1908303	DSNU-20-70-PPS-A				
	80	19211	DSNU-20-80-P-A	19238	DSNU-20-80-PPV-A	559274	DSNU-20-80-PPS-A				
	100	19212	DSNU-20-100-P-A	19239	DSNU-20-100-PPV-A	559275	DSNU-20-100-PPS-A				
	125	19213	DSNU-20-125-P-A	19240	DSNU-20-125-PPV-A	559276	DSNU-20-125-PPS-A				
	150	1908288	DSNU-20-150-P-A	1908296	DSNU-20-150-PPV-A	1908304	DSNU-20-150-PPS-A				
	160	19214	DSNU-20-160-P-A	19241	DSNU-20-160-PPV-A	559277	DSNU-20-160-PPS-A				
	200	19215	DSNU-20-200-P-A	19242	DSNU-20-200-PPV-A	559278	DSNU-20-200-PPS-A				
	250	19216	DSNU-20-250-P-A	19243	DSNU-20-250-PPV-A	559279	DSNU-20-250-PPS-A				
	300	19217	DSNU-20-300-P-A	19244	DSNU-20-300-PPV-A	559280	DSNU-20-300-PPS-A				
320	34718	DSNU-20-320-P-A	34720	DSNU-20-320-PPV-A	559281	DSNU-20-320-PPS-A					
25	10	19218	DSNU-25-10-P-A	1908312	DSNU-25-10-PPV-A	1908320	DSNU-25-10-PPS-A				
	15	1908305	DSNU-25-15-P-A	1908313	DSNU-25-15-PPV-A	1908321	DSNU-25-15-PPS-A				
	20	1908306	DSNU-25-20-P-A	1908314	DSNU-25-20-PPV-A	1908322	DSNU-25-20-PPS-A				
	25	19219	DSNU-25-25-P-A	33975	DSNU-25-25-PPV-A	559282	DSNU-25-25-PPS-A				
	30	1908307	DSNU-25-30-P-A	1908315	DSNU-25-30-PPV-A	1908323	DSNU-25-30-PPS-A				
	35	1908308	DSNU-25-35-P-A	1908316	DSNU-25-35-PPV-A	1908324	DSNU-25-35-PPS-A				
	40	19220	DSNU-25-40-P-A	19245	DSNU-25-40-PPV-A	559283	DSNU-25-40-PPS-A				
	50	19221	DSNU-25-50-P-A	19246	DSNU-25-50-PPV-A	559284	DSNU-25-50-PPS-A				
	60	1908309	DSNU-25-60-P-A	1908317	DSNU-25-60-PPV-A	1908325	DSNU-25-60-PPS-A				
	70	1908310	DSNU-25-70-P-A	1908318	DSNU-25-70-PPV-A	1908326	DSNU-25-70-PPS-A				
	80	19222	DSNU-25-80-P-A	19247	DSNU-25-80-PPV-A	559285	DSNU-25-80-PPS-A				
	100	19223	DSNU-25-100-P-A	19248	DSNU-25-100-PPV-A	559286	DSNU-25-100-PPS-A				
	125	19224	DSNU-25-125-P-A	19249	DSNU-25-125-PPV-A	559287	DSNU-25-125-PPS-A				
	150	1908311	DSNU-25-150-P-A	1908319	DSNU-25-150-PPV-A	1908327	DSNU-25-150-PPS-A				
	160	19225	DSNU-25-160-P-A	19250	DSNU-25-160-PPV-A	559288	DSNU-25-160-PPS-A				
	200	19226	DSNU-25-200-P-A	19251	DSNU-25-200-PPV-A	559289	DSNU-25-200-PPS-A				
	250	19227	DSNU-25-250-P-A	19252	DSNU-25-250-PPV-A	559290	DSNU-25-250-PPS-A				
	300	19228	DSNU-25-300-P-A	19253	DSNU-25-300-PPV-A	559291	DSNU-25-300-PPS-A				
320	34719	DSNU-25-320-P-A	34721	DSNU-25-320-PPV-A	559292	DSNU-25-320-PPS-A					
400	35191	DSNU-25-400-P-A	35193	DSNU-25-400-PPV-A	559293	DSNU-25-400-PPS-A					
500	35192	DSNU-25-500-P-A	35194	DSNU-25-500-PPV-A	559294	DSNU-25-500-PPS-A					

Datasheet

Ordering data				PPV – Pneumatic cushioning, adjustable at both ends		PPS – Pneumatic cushioning, self-adjusting at both ends	
Piston Ø	Stroke	P – Elastic cushioning rings/plates at both ends	A – With position sensing	A – With position sensing		A – With position sensing	
[mm]	[mm]	Part no.	Type	Part no.	Type	Part no.	Type
32	10	5249365	DSNU-32-10-P-A	–		–	
	15	5249366	DSNU-32-15-P-A	–		–	
	20	5249367	DSNU-32-20-P-A	–		–	
	25	195980	DSNU-32-25-P-A	196020	DSNU-32-25-PPV-A	559295	DSNU-32-25-PPS-A
	30	5249368	DSNU-32-30-P-A	5249851	DSNU-32-30-PPV-A	5249968	DSNU-32-30-PPS-A
	40	195981	DSNU-32-40-P-A	196021	DSNU-32-40-PPV-A	559296	DSNU-32-40-PPS-A
	50	195982	DSNU-32-50-P-A	196022	DSNU-32-50-PPV-A	559297	DSNU-32-50-PPS-A
	60	5249369	DSNU-32-60-P-A	5249853	DSNU-32-60-PPV-A	5249970	DSNU-32-60-PPS-A
	70	5249370	DSNU-32-70-P-A	5249854	DSNU-32-70-PPV-A	5249971	DSNU-32-70-PPS-A
	80	195983	DSNU-32-80-P-A	196023	DSNU-32-80-PPV-A	559298	DSNU-32-80-PPS-A
	100	195984	DSNU-32-100-P-A	196024	DSNU-32-100-PPV-A	559299	DSNU-32-100-PPS-A
	125	195985	DSNU-32-125-P-A	196025	DSNU-32-125-PPV-A	559300	DSNU-32-125-PPS-A
	150	5249371	DSNU-32-150-P-A	5249855	DSNU-32-150-PPV-A	5249972	DSNU-32-150-PPS-A
	160	195986	DSNU-32-160-P-A	196026	DSNU-32-160-PPV-A	559301	DSNU-32-160-PPS-A
	200	195987	DSNU-32-200-P-A	196027	DSNU-32-200-PPV-A	559302	DSNU-32-200-PPS-A
	250	195988	DSNU-32-250-P-A	196028	DSNU-32-250-PPV-A	559303	DSNU-32-250-PPS-A
	300	5249372	DSNU-32-300-P-A	5249856	DSNU-32-300-PPV-A	5249973	DSNU-32-300-PPS-A
320	195989	DSNU-32-320-P-A	196029	DSNU-32-320-PPV-A	559304	DSNU-32-320-PPS-A	
40	10	5262529	DSNU-40-10-P-A	–		–	
	15	5262530	DSNU-40-15-P-A	–		–	
	20	5262531	DSNU-40-20-P-A	–		–	
	25	195990	DSNU-40-25-P-A	196030	DSNU-40-25-PPV-A	559305	DSNU-40-25-PPS-A
	30	5262532	DSNU-40-30-P-A	5262705	DSNU-40-30-PPV-A	5262768	DSNU-40-30-PPS-A
	40	195991	DSNU-40-40-P-A	196031	DSNU-40-40-PPV-A	559306	DSNU-40-40-PPS-A
	50	195992	DSNU-40-50-P-A	196032	DSNU-40-50-PPV-A	559307	DSNU-40-50-PPS-A
	60	5262534	DSNU-40-60-P-A	5262706	DSNU-40-60-PPV-A	5262769	DSNU-40-60-PPS-A
	70	5262535	DSNU-40-70-P-A	5262707	DSNU-40-70-PPV-A	5262771	DSNU-40-70-PPS-A
	80	195993	DSNU-40-80-P-A	196033	DSNU-40-80-PPV-A	559308	DSNU-40-80-PPS-A
	100	195994	DSNU-40-100-P-A	196034	DSNU-40-100-PPV-A	559309	DSNU-40-100-PPS-A
	125	195995	DSNU-40-125-P-A	196035	DSNU-40-125-PPV-A	559310	DSNU-40-125-PPS-A
	150	5262536	DSNU-40-150-P-A	5262708	DSNU-40-150-PPV-A	5262772	DSNU-40-150-PPS-A
	160	195996	DSNU-40-160-P-A	196036	DSNU-40-160-PPV-A	559311	DSNU-40-160-PPS-A
	200	195997	DSNU-40-200-P-A	196037	DSNU-40-200-PPV-A	559312	DSNU-40-200-PPS-A
	250	195998	DSNU-40-250-P-A	196038	DSNU-40-250-PPV-A	559313	DSNU-40-250-PPS-A
	300	5262537	DSNU-40-300-P-A	5262709	DSNU-40-300-PPV-A	5262773	DSNU-40-300-PPS-A
320	195999	DSNU-40-320-P-A	196039	DSNU-40-320-PPV-A	559314	DSNU-40-320-PPS-A	

## Datasheet


Ordering data							
Piston Ø [mm]	Stroke [mm]	P – Elastic cushioning rings/plates at both ends A – With position sensing		PPV – Pneumatic cushioning, adjustable at both ends A – With position sensing		PPS – Pneumatic cushioning, self-adjusting at both ends A – With position sensing	
		Part no.	Type	Part no.	Type	Part no.	Type
50	25	196000	DSNU-50-25-P-A	196040	DSNU-50-25-PPV-A	559315	DSNU-50-25-PPS-A
	40	196001	DSNU-50-40-P-A	196041	DSNU-50-40-PPV-A	559316	DSNU-50-40-PPS-A
	50	196002	DSNU-50-50-P-A	196042	DSNU-50-50-PPV-A	559317	DSNU-50-50-PPS-A
	80	196003	DSNU-50-80-P-A	196043	DSNU-50-80-PPV-A	559318	DSNU-50-80-PPS-A
	100	196004	DSNU-50-100-P-A	196044	DSNU-50-100-PPV-A	559319	DSNU-50-100-PPS-A
	125	196005	DSNU-50-125-P-A	196045	DSNU-50-125-PPV-A	559320	DSNU-50-125-PPS-A
	160	196006	DSNU-50-160-P-A	196046	DSNU-50-160-PPV-A	559321	DSNU-50-160-PPS-A
	200	196007	DSNU-50-200-P-A	196047	DSNU-50-200-PPV-A	559322	DSNU-50-200-PPS-A
	250	196008	DSNU-50-250-P-A	196048	DSNU-50-250-PPV-A	559323	DSNU-50-250-PPS-A
320	196009	DSNU-50-320-P-A	196049	DSNU-50-320-PPV-A	559324	DSNU-50-320-PPS-A	
63	25	196010	DSNU-63-25-P-A	196050	DSNU-63-25-PPV-A	559325	DSNU-63-25-PPS-A
	40	196011	DSNU-63-40-P-A	196051	DSNU-63-40-PPV-A	559326	DSNU-63-40-PPS-A
	50	196012	DSNU-63-50-P-A	196052	DSNU-63-50-PPV-A	559327	DSNU-63-50-PPS-A
	80	196013	DSNU-63-80-P-A	196053	DSNU-63-80-PPV-A	559328	DSNU-63-80-PPS-A
	100	196014	DSNU-63-100-P-A	196054	DSNU-63-100-PPV-A	559329	DSNU-63-100-PPS-A
	125	196015	DSNU-63-125-P-A	196055	DSNU-63-125-PPV-A	559330	DSNU-63-125-PPS-A
	160	196016	DSNU-63-160-P-A	196056	DSNU-63-160-PPV-A	559331	DSNU-63-160-PPS-A
	200	196017	DSNU-63-200-P-A	196057	DSNU-63-200-PPV-A	559332	DSNU-63-200-PPS-A
	250	196018	DSNU-63-250-P-A	196058	DSNU-63-250-PPV-A	559333	DSNU-63-250-PPS-A
320	196019	DSNU-63-320-P-A	196059	DSNU-63-320-PPV-A	559334	DSNU-63-320-PPS-A	

Ordering data for variable strokes							
Piston Ø [mm]	Stroke [mm]	P – Elastic cushioning rings/plates at both ends A – With position sensing		PPV – Pneumatic cushioning, adjustable at both ends A – With position sensing			
		Part no.	Type	Part no.	Type		
8	1 ... 100	14326	DSNU-8-...-P-A				
10	1 ... 100	14325	DSNU-10-...-P-A				
12	1 ... 200	14324	DSNU-12-...-P-A				
16	1 ... 200	14323	DSNU-16-...-P-A				
20	1 ... 320	14328	DSNU-20-...-P-A				
25	1 ... 500	14327	DSNU-25-...-P-A				
				14320	DSNU-16-...-PPV-A		
				14321	DSNU-20-...-PPV-A		
				14322	DSNU-25-...-PPV-A		

## Ordering data – Modular product system


Ordering table									
Size	8	10	12	16	20	25	Conditions	Code	Enter code
Module no.	<b>193986</b>	<b>193987</b>	<b>193988</b>	<b>193989</b>	<b>193990</b>	<b>193991</b>			
Function	Round cylinder, double-acting, based on ISO 6432							<b>DSNU</b>	DSNU
Piston Ø [mm]	8	10	12	16	20	25		-...	
Stroke [mm]	1 ... 100		1 ... 200		1 ... 320	1 ... 500	[1]	-...	
Cushioning	Elastic cushioning rings/plates at both ends							<b>-P</b>	
	-		-		Pneumatic cushioning, adjustable at both ends		[2]	<b>-PPV</b>	
	-		-		Pneumatic cushioning, self-adjusting at both ends		[3]	<b>-PPS</b>	
Position sensing	Via proximity switch						[4]	<b>-A</b>	-A
Cylinder end cap	Lateral supply port, short end cap						[5]	<b>-MQ</b>	
	Axial supply port, short end cap						[5]	<b>-MA</b>	
	With mounting flange at front (direct mounting), bearing cap						[6]	<b>-MH</b>	
Piston rod type	Through piston rod						[7]	<b>-S2</b>	
Stroke adjustment, [mm]	0 ... 15		-				[8]	<b>-15KE</b>	
extending [mm]	-		0 ... 25				[9]	<b>-25KE</b>	

- [1] -... Longer strokes on request
- [2] PPV Not with MA. In combination with S6, S10, L, A1 not with piston diameter 12 mm
- [3] PPS Not with MA, MH, S6, S10 and not with combination MQ-R3
- [4] A Minimum stroke > 10 mm required for reliable sensing
- [5] MQ, MA Not with S2, S10
- [6] MH Not with combination S6-R3.  
Not with S10
- [7] S2 Not with S10
- [8] 15KE Not with MQ, MA, S2, S6, S10, L, A1, EX4
- [9] 25KE Not with MQ, MA, S2, S6, S10, L, A1, EX4  
With piston Ø 20, 25: stroke only up to 250 mm

 - **Note**

The bellows kit DADB must not be used in combination with the variant MH.

The running characteristics change slightly when the bellows kit DADB is combined with the variant S10 or L

 - **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.

Longer strokes on request

## Ordering data – Modular product system


Ordering table		8	10	12	16	20	25	Conditions	Code	Enter code	
Extended male thread		Extended male piston rod thread									
	[mm]	1 ... 15		1 ... 20		1 ... 25	1 ... 35	[10]	-...K2		
Shortened male thread		Shortened male piston rod thread									
	[mm]	1 ... 4				1 ... 8	1 ... 10	[11]	-...K6		
Female thread		Piston rod with female thread									
		-	-	-	-	(M4)	(M6)	[12]	-K3		
Special thread		Special piston rod thread									
		-	-	-	-	-	M10		-“...”K5		
Extended piston rod at one end		Piston rod extended at one end									
	[mm]	1 ... 50		1 ... 100		1 ... 110	1 ... 150		...K8		
Temperature resistance		Heat-resistant seals max. 120 °C						[13]	-S6		
Constant motion		-	-	Slow speed (constant motion at low piston speeds)			[14]	-S10			
Running characteristic		Low friction						[15]	-L		
Corrosion protection		-	-	High corrosion protection				-R3			
Wiper		-	-	Increased chemical resistance			[16]	-A1			
EU certification		II 2GD						[17]	-EX4		

[10]	K2	Not with K3, K6
[11]	K6	Not with K3
[12]	K3	Not with K5
[13]	S6	Not with S10
[14]	S10	Not with R3, L
[15]	L	Not with MQ, MA, MH, S2, S6, S10
[16]	A1	Not with MH, S6, S10, L
[17]	EX4	Not with S6


## Ordering data – Modular product system

Ordering table							
Size	32	40	50	63	Conditions	Code	Enter code
Module no.	<b>193992</b>	<b>193993</b>	<b>193994</b>	<b>193995</b>			
Function	Double-acting round cylinder					<b>DSNU</b>	DSNU
Piston Ø [mm]	32	40	50	63		-...	
Stroke [mm]	1 ... 500				[1]	-...	
Cushioning	Elastic cushioning rings/plates at both ends					<b>-P</b>	
	Pneumatic cushioning, adjustable at both ends				[2]	<b>-PPV</b>	
	Pneumatic cushioning, self-adjusting at both ends				[3]	<b>-PPS</b>	
Position sensing	Via proximity switch				[4]	<b>-A</b>	-A
Cylinder end cap	Lateral supply port, short end cap				[5]	<b>-MQ</b>	
	Axial supply port, short end cap				[6]	<b>-MA</b>	
	Mounting flange at the front (direct mounting), bearing cap				[7]	<b>-MH</b>	
Piston rod type	Through piston rod				[8]	<b>-S2</b>	
Stroke adjustment, extending	[mm]	0 ... 25			[9]	<b>-25KE</b>	
	[mm]	-	0 ... 50			[10]	<b>-50KE</b>

- [1] -... Longer strokes on request
- [2] PPV Not with MA
- [3] PPS Not with MA, MH, S6, S10, combination MQ-R3 and R8
- [4] A Minimum stroke > 10 mm required for reliable sensing
- [5] MQ Not with S2, S10
- [6] MA Not with S2, S10 R8
- [7] MH Not with combination S6-R3.  
Not with S10, R8
- [8] S2 Not with S10
- [9] 25KE Not with MQ, MA, S2, S6, S10, L, R8, A1, A6, EX4
- [10] 50KE Not with MQ, MA, S2, S6, S10, L, R8, A1, A6, EX4

 - **Note**

The bellows kit DADB must not be used in combination with the variant MH.  
The running characteristics change slightly when the bellows kit DADB is combined with the variant S10 or L

 - **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.  
Longer strokes on request

## Ordering data – Modular product system


Ordering table							
Size	32	40	50	63	Conditions	Code	Enter code
Extended male thread	Extended male piston rod thread						
	[mm]	1 ... 35		1 ... 70	[11]	-...K2	
Shortened male thread	Shortened male piston rod thread						
	[mm]	1 ... 8		1 ... 10	[12]	-...K6	
Female thread	Piston rod with female thread						
		(M6)	(M8)	(M10)	[13]	-K3	
Special thread	Special piston rod thread						
		M10	M12	M16		-“...”K5	
Extended piston rod at one end	Piston rod extended at one end						
	[mm]	1 ... 500					...K8
Temperature resistance	Heat-resistant seals max. 120 °C				[14]	-S6	
Constant motion	Slow speed (constant motion at low piston speeds)				[15]	-S10	
Running characteristic	Low friction				[16]	-L	
Corrosion protection	High corrosion protection				[17]	-R3	
Wiper	Dust protection				[18]	-R8	
	Increased chemical resistance				[19]	-A1	
	Metal wiper				[20]	-A6	
EU certification	II 2GD				[21]	-EX4	

- [11] K2 Not with K3, K6  
 [12] K6 Not with K3  
 [13] K3 Not with K5  
 [14] S6 Not with S10, S1  
 [15] S10 Not with R3, R8, L  
 [16] L Not with MQ, MA, MH, S2, S6, S10  
 [17] R8 Not with MA, MH, S10, L, R3, A1, PPS  
 [18] R3 Not with R8  
 [19] A1 Not with MH, S6, S10, L, R8  
 [20] A6 Not with S10, L, MH, P, PPS, S6, R3, EX4  
 [21] EX4 Not with S6, S10

## Ordering data – Modular product system

Ordering table												
Size	8	10	12	16	20	25	32	40	Conditions	Code	Enter code	
Module no.	<b>8150747</b>	<b>8149443</b>	<b>8149444</b>	<b>8149445</b>	<b>8149446</b>	<b>8149447</b>	<b>8149448</b>	<b>8149449</b>				
Function	Standards-based cylinder, double-acting, based on ISO 6432									<b>DSNU</b>	DSNU	
Piston Ø [mm]	8	10	12	16	20	25	32	40		-...		
Stroke [mm]	1 ... 100		1 ... 200		1 ... 320		1 ... 500		[1]	-...		
Cushioning	Elastic cushioning rings/plates at both ends									<b>-P</b>		
	-		-		Pneumatic cushioning, adjustable at both ends					<b>-PPV</b>		
	-		-		Pneumatic cushioning, self-adjusting					<b>-PPS</b>		
Position sensing	Via proximity switch									<b>-A</b>	-A	
Special material properties	Recommended for production facilities for manufacturing lithium-ion batteries									[2]	<b>-F1A</b>	
Cylinder end cap	Standard											
	Lateral supply port, short end cap										<b>-MQ</b>	
	Axial supply port, short end cap									[3]	<b>-MA</b>	
Piston rod type	Piston rod at one end											
	Through piston rod									[4]	<b>-S2</b>	
Stroke adjustment, extending	[mm]	0 ... 15		-						[5]	<b>-15KE</b>	
	[mm]	-		0 ... 25					[6]	<b>-25KE</b>		
	[mm]	-						0 ... 50		[7]	<b>-50KE</b>	

- [1] -... Longer strokes on request
- [2] F1A With A only
- [3] MA Not with PPV, PPS
- [4] S2 Not with MQ, MA
- [5] 15KE Not with MQ, MA, S2
- [6] 25KE Not with MQ, MA, S2
- [7] 50KE Not with MQ, MA, S2

 **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.  
Longer strokes on request


## Ordering data – Modular product system

Ordering table											
Size	8	10	12	16	20	25	32	40	Conditions	Code	Enter code
Extended male thread	Extended male piston rod thread										
	[mm]	1 ... 15		1 ... 20		1 ... 25	1 ... 35		[8]	-...K2	
Shortened male thread	Shortened male piston rod thread										
	[mm]	1 ... 4				1 .. 8			[9]	-...K6	
Female thread	Piston rod with female thread										
	-	-	-	-	(M4)	(M6)	(M8)		-K3		
Special thread	Special piston rod thread										
	-	-	-	-	-	M10	M12	[10]	-“...”K5		
Extended piston rod at one end	Piston rod extended at one end										
	[mm]	1 ... 50		1 ... 100		1 ... 110	1 ... 150	1 ... 500			-...K8

- [8] K2 Not with K3  
 [9] K6 Not with K2, K3  
 [10] K5 Not with K3


## Datasheet


### P cushioning




-  - Diameter  
8 ... 25 mm  
ISO 6432


### PPV cushioning



-  - Diameter  
32 ... 63 mm

### PPS cushioning



-  - Stroke length  
1 ... 500 mm



### Note

Additional measures are required for use in safety-related applications; in Europe, for example, the standards listed under the EC Machinery Directive must be observed.

Without additional measures in accordance with legally specified minimum requirements, the product is not suitable as a safety-oriented component in control systems.

### General technical data

Piston Ø	8	10	12	16	20	25	32	40	50	63	
Based on standard	ISO 6432						-				
Pneumatic connection	M5	M5	M5	M5	G1/8	G1/8	G1/8	G1/4	G1/4	G3/8	
Piston rod thread	M4	M4	M6	M6	M8	M10x1.25	M10x1.25	M12x1.25	M16x1.5	M16x1.5	
Stroke <sup>1)</sup> [mm]	1 ... 100		1 ... 200		1 ... 320		1 ... 500				
Design	Piston/piston rod/cylinder barrel										
Cushioning											
DSNU...-P	Elastic cushioning rings/plates at both ends										
DSNU...-PPV	-		Cushioning, adjustable at both ends								
DSNU...-PPS	-		Cushioning, self-adjusting at both ends								
Cushioning length											
DSNU...-PPV [mm]	-		9	12	15	17	14	18	20	21	
DSNU...-PPS [mm]	-		12	15	17	14	18	20	21		
Position sensing	Via proximity switch										
Type of mounting	With through-hole										
	With accessories										
Mounting position	Any										
Holding force of the clamping unit [N]	80	80	180	180	350	350	600	1000	1400	2000	
Axial backlash under load [mm]	0.2		0.3		0.5			0.8			
Pneumatic connection on clamping unit	M5							G1/8			

1) Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing. Longer strokes on request.

## Datasheet

Operating and environmental conditions	
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/ pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure <sup>1)</sup>	[MPa] 0.3 ... 1
	[bar] 3 ... 10
Ambient temperature	[°C] -10 ... +80
Corrosion resistance class CRC <sup>2)</sup>	
DSNU-...	2 - Moderate corrosion stress
DSNU...-R3	3 - High corrosion stress

1) With variant S2 (through piston rod) or variant KE (stroke adjustment), the minimum operating pressure may increase slightly after an idle period of > 24 hours.

2) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

Forces [N] and impact energy [J]										
Piston Ø	8	10	12	16	20	25	32	40	50	63
Theoretical force at 0.6 MPa (6 bar), advancing	30	47	68	121	189	295	483	753	1178	1870
Theoretical force at 0.6 MPa (6 bar), retracting	23	40	51	104	158	247	415	633	990	1682
Impact energy in the end positions for P cushioning <sup>1)</sup>										
DSNU-...	0.03	0.05	0.07	0.15	0.2	0.3	0.4	0.7	1	1.3
DSNU...-KE	0.025	0.025	0.055	0.12	0.16	0.24	0.32	0.56	0.8	1

1) The values are reduced by approx. 50% at an ambient temperature of 80 °C

Permissible impact velocity: 
$$V = \sqrt{\frac{2 \times E}{m_1 + m_2}}$$

Maximum permissible mass: 
$$m_2 = \frac{2 \times E}{v^2} - m_1$$


V Perm. impact velocity  
 E Max. impact energy  
 m1 Moving mass (drive)  
 m2 Moving payload

Weight [g]											
Piston Ø	8	10	12	16	20	25	32	40	50	63	
<b>DSNU-...</b>											
Product weight with 0 mm stroke	97.6	100.3	193	207.9	393.8	456	711.5	1287	2059	2556	
Additional weight per 10 mm stroke	2.4	2.7	4	4.6	7.2	11	15.5	24	40	44	
Moving mass with 0 mm stroke	7.5	8.5	18.5	23	44	71	121	230	413	459	
Moving mass per 10 mm stroke	1	1	2	2	4	6	9	16	25	25	
<b>DSNU...-S2</b>											
Moving mass with 0 mm stroke	12	12.5	30	34.5	70	113	182	363	638	701	
Moving mass per 10 mm stroke	2	2	4	4	8	12	18	32	50	50	
<b>DSNU...-KE</b>											
Moving mass with 0 mm stroke	[15KE]	17	17.5	-	-	-	-	-	-	-	
	[25KE]	-	-	46	50.5	99	142	251	469	839	902
	[50KE]	-	-	-	-	-	-	-	491	918	981
Moving mass per 10 mm stroke	2	2	4	4	8	12	18	32	50	50	

Datasheet


Average piston speed  $v$  as a function of payload  $m$  in combination with cushioning PPS

Piston  $\varnothing$  16




- DSNU-16-50
- ⋯ DSNU-16-100
- - - DSNU-16-200

Piston  $\varnothing$  20




- DSNU-20-50
- ⋯ DSNU-20-100
- - - DSNU-20-200

Piston  $\varnothing$  25




- DSNU-25-50
- ⋯ DSNU-25-100
- - - DSNU-25-200

Piston  $\varnothing$  32




- DSNU-32-50
- ⋯ DSNU-32-100
- - - DSNU-32-200

Piston  $\varnothing$  40



- DSNU-40-50
- ⋯ DSNU-40-100
- - - DSNU-40-200

Piston  $\varnothing$  50




- DSNU-50-50
- ⋯ DSNU-50-100
- - - DSNU-50-200

## Datasheet

### Average piston speed $v$ as a function of payload $m$ in combination with cushioning PPS

Piston  $\varnothing$  63

Note:




Engineering software for  
 P cushioning  
 PPV cushioning  
 PPS cushioning  
 → <https://www.festo.com/x/pneumatic-sizing>



Average piston speed  
 = Stroke/movement time

- DSNU-63-50
- DSNU-63-100
- - - DSNU-63-200

### Max. transverse force $F_q$ as a function of projection $l$



DSNU-...




- DSNU-8/10
- DSNU-12/16
- - - DSNU-20
- · · · · DSNU-25


- · · · · DSNU-32
- - - DSNU-40
- DSNU-50/63

Datasheet


Max. transverse force  $F_q$  as a function of projection  $l$



DSNU-...S2 – Through piston rod



- DSNU-8/10
- - - - DSNU-12/16
- - - - DSNU-20
- ..... DSNU-25




- · - · - DSNU-32
- - - - DSNU-40
- - - - DSNU-50/63

## Datasheet

## Materials

## Sectional view




Round cylinder	
[1]	Piston rod
	DSNU-...
	High-alloy steel
	DSNU-...-R3
	High-alloy stainless steel
[2]	Bearing cap
	Anodised aluminium
[3]	Piston rod bearing
	Sintered bronze
[4]	Housing, clamping unit
	Wrought aluminium alloy
[5]	Clamping jaws
	Brass
[6]	Cylinder barrel
	High-alloy stainless steel
[7]	End cap
	Anodised aluminium
[8]	Swivel bearing
	Polymer
-	Piston, clamping unit
	POM
	Spring
	Spring steel
	Piston rod wiper seal
	TPE-U(PU)
	Stroke adjustment DSNU-...-KE
	Stop element
	PE-UHMW
	Threaded coupling
	Anodised aluminium
	LABS (PWIS) conformity
	VDMA24364-B1/B2-L
	Cleanroom class
	Class 6 to ISO 14644-1
	Note on materials
	RoHS-compliant

Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-8 ... 25



**Note**  
 Piston rod nut is not included in the scope of delivery for diameter 8 ... 20.  
 + = plus stroke length

$\varnothing$ [mm]	AM	B $\varnothing$ h8	B2	B3	BE	BF	CD $\varnothing$ H9	D $\varnothing$	D4 $\varnothing$	D6 $\varnothing$	D7 $\varnothing$	D8
8	12	12	19.5	27	M12x1.25	12	4	16	9.3	12	4.2	M5
10									11.3			
12	16	16	24	32	M16x1.5	17	6	20	13.3			
16									17.3			
20									21.3			
25	22	22	27	36	M22x1.5	22	8	30	26.5	20		

$\varnothing$ [mm]	E1	EE	EW	G	H1	H2	KK	KV	KW	MM $\varnothing$	L	L2
8	M5	M5	8	10	34.5	13.5	M4	19	6	4	6	46
10			12		41	16	M6	24	8	6	9	50
12			16	16	62.5	18	M8	32	11	8	12	68
16		G1/8	16	16	62.5	18	M10x1.25	32	11	10	12	69.5
20												69.5
25												

$\varnothing$ [mm]	L6	L7	L8	L9	T3	PL	VD	WF $\pm 1.2$	XC $\pm 1$	ZJ	$\approx \text{S}1$
8	29 $\pm 0.65$	8	-	-	11	6	2	16	93	91	-
10			-	-				-	-		
12	38 $\pm 0.75$	10	-	-				113	110	5	
16			-	-				120	116		
20			47 $\pm 0.75$	13				4.5	20	142	139
25	48 $\pm 0.75$	152	145.5		9						


Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-8 ... 25

S2 – Through piston rod



+ = plus stroke length  
++ = plus 2x stroke length

Note


The thread types at both piston rod ends are identical. The clamping unit is mounted at only one end.

In combination with variant Q (→ page 46) the right piston rod is square, the left piston rod round. The clamping unit is mounted on the left round piston rod.

In combination with variant K8 the piston rod extension is on the right piston rod only. The clamping unit is mounted on the left piston rod that is not extended.

In combination with variant K8 and Q, the piston rod extension is on the right, square piston rod only.

KE – Stroke adjustment



+ = plus stroke length  
++ = plus 2x stroke length


ø [mm]	A5		D8 ø	ZJ	ZM	≈ 2	≈ 3
	DSNU-... -15KE	-25KE					
8	27.5	-	12	91	107	7	10
10							
12	-	43	15	110	132	10	13
16							
20							
25		47	20	139	163	13	17
				145.5	173.5		

Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-32 ... 63



∅ [mm]	AM	B ∅ h9	B2	B3	BE	BF	CD ∅ H9	D ∅	D1 ∅	D4 ∅	D6 ∅	D7 ∅
32	22	30	30	46	M30x1.5	26	10	41	42	33.6	20	4.4
40	24	38	36	56	M38x1.5	30	12	49	50	41.6	24	6.8
50	32	45	50	65	M45x1.5	33	16	57	60	52.4	30	8.5
63			54	72	M45x1.5			70		65.4	38	

∅ [mm]	D8	E1	EE	EW	G	H1	H2	KK	KW	MM ∅ f8	L	L2
32	M5	M5	G1/8	16	19	67.5	23	M10x1.25	8	12	13	69.5
40	M8	G1/8	G1/4	18	25	89	28	M12x1.25	10	16	15	84.6
50		G1/8		21		107.5	32.5	20		16	86.2	
63	M10	G1/8	G3/8	28	121.5	36	M16x1.5	16	94.2			

∅ [mm]	L6	L7	L8	L9	T3	PL	VD	WF	XC	ZJ	⊖G1
	±0.75								±1		
32	55	12.5	5	15	12	9	2	34	172.5	158.5	10
40	69	17	7	20	18	12	3	39	208.6	192.6	13
50	78	20		26	20			44	225.2	208.2	17
63	86	24	8	32	21	13		45	242.2	225.2	


Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-32 ... 63

S2 – Through piston rod



+ = plus stroke length  
++ = plus 2x stroke length

Note


The thread types at both piston rod ends are identical. The clamping unit is mounted at only one end.

In combination with variant Q (→ page 46) the right piston rod is square, the left piston rod round. The clamping unit is mounted on the left round piston rod.

In combination with variant K8 the piston rod extension is on the right piston rod only. The clamping unit is mounted on the left piston rod that is not extended.

In combination with variant K8 and Q, the piston rod extension is on the right, square piston rod only.

KE – Stroke adjustment




+ = plus stroke length  
++ = plus 2x stroke length

ø [mm]	A5		D8 ø	ZJ	ZM	Ra 2	Ra 3
	DSNU-... -25KE	-50KE					
32	52	–	30	158.5	192.5	17	24
40	56	81	35	192.6	231.6	19	30
50	67	92	45	208.2	252.2	24	
63				225.2	270.2		

## Ordering data – Modular product system

Ordering table									
Size	8	10	12	16	20	25	Conditions	Code	Enter code
Module no.	<b>193986</b>	<b>193987</b>	<b>193988</b>	<b>193989</b>	<b>193990</b>	<b>193991</b>			
Function	Round cylinder, double-acting, based on ISO 6432							<b>DSNU</b>	DSNU
Piston Ø [mm]	8	10	12	16	20	25		-...	
Stroke [mm]	1 ... 100		1 ... 200		1 ... 320	1 ... 500	[1]	-...	
Cushioning	Elastic cushioning rings/plates at both ends							<b>-P</b>	
	-		-		Pneumatic cushioning, adjustable at both ends		[2]	<b>-PPV</b>	
	-		-		Pneumatic cushioning, self-adjusting at both ends		[3]	<b>-PPS</b>	
Position sensing	Via proximity switch						[4]	<b>-A</b>	-A
Cylinder end cap	Lateral supply port, short end cap						[5]	<b>-MQ</b>	
	Axial supply port, short end cap						[5]	<b>-MA</b>	
Piston rod type	Through piston rod							<b>-S2</b>	
Stroke adjustment, extending [mm]	0 ... 15		-		-		[6]	<b>-15KE</b>	
	-		0 ... 25		-		[7]	<b>-25KE</b>	

- [1] -... Longer strokes on request
- [2] PPV Not with MA
- [3] PPS Not with MA, MH and not with combination MQ-R3
- [4] A Minimum stroke > 10 mm required for reliable sensing
- [5] MQ, MA Not with S2
- [6] 15KE Not with MQ, MA, S2
- [7] 25KE Not with MQ, MA, S2  
With piston Ø 20, 25: stroke only up to 250 mm

 **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.  
Longer strokes on request

## Ordering data – Modular product system

Ordering table									
Size	8	10	12	16	20	25	Conditions	Code	Enter code
Extended male thread	Extended male piston rod thread								
	[mm]	1 ... 15	1 ... 20		1 ... 25	1 ... 35	[8]	-...K2	
Shortened male thread	Shortened male piston rod thread								
	[mm]	1 ... 4			1 ... 8	1 ... 10	[9]	-...K6	
Female thread	Piston rod with female thread								
		-	-	-	-	(M4)	(M6)	[10]	-K3
Special thread	Special piston rod thread								
		-	-	-	-	-	M10		-“...”K5
Extended piston rod at one end	Piston rod extended at one end								
	[mm]	1 ... 50	1 ... 100		1 ... 110	1 ... 150		...K8	
Clamping unit	Attached								
								-KP	-KP

[8] K2 Not with K3, K6


[9] K6 Not with K3

[10] K3 Not with K5

## Ordering data – Modular product system

Ordering table							
Size	32	40	50	63	Conditions	Code	Enter code
Module no.	<b>193992</b>	<b>193993</b>	<b>193994</b>	<b>193995</b>			
Function	Double-acting round cylinder					<b>DSNU</b>	DSNU
Piston Ø [mm]	32	40	50	63		-...	
Stroke [mm]	1 ... 500				[1]	-...	
Cushioning	Elastic cushioning rings/plates at both ends					<b>-P</b>	
	Pneumatic cushioning, adjustable at both ends				[2]	<b>-PPV</b>	
	Pneumatic cushioning, self-adjusting at both ends				[3]	<b>-PPS</b>	
Position sensing	Via proximity switch				[4]	<b>-A</b>	-A
Cylinder end cap	Lateral supply port, short end cap				[5]	<b>-MQ</b>	
	Axial supply port, short end cap				[5]	<b>-MA</b>	
Piston rod type	Through piston rod					<b>-S2</b>	
Stroke adjustment, extending	[mm]	0 ... 25			[6]	<b>-25KE</b>	
	[mm]	-	0 ... 50			[7]	<b>-50KE</b>

- [1] -... Longer strokes on request
- [2] PPV Not with MA
- [3] PPS Not with MA, MH and not with combination MQ-R3
- [4] A Minimum stroke > 10 mm required for reliable sensing
- [5] MQ, MA Not with S2
- [6] 25KE Not with MQ, MA, S2  
With piston Ø 20, 25: stroke only up to 250 mm
- [7] 50KE Not with MQ, MA, S2

 **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.  
Longer strokes on request

## Ordering data – Modular product system

Ordering table							
Size	32	40	50	63	Conditions	Code	Enter code
Extended male thread	Extended male piston rod thread						
	[mm]	1 ... 35		1 ... 70	[8]	-...K2	
Shortened male thread	Shortened male piston rod thread						
	[mm]	1 ... 8		1 ... 10	[9]	-...K6	
Female thread	Piston rod with female thread						
		(M6)	(M8)	(M10)	[10]	-K3	
Special thread	Special piston rod thread						
		M10	M12	M16		-“...”K5	
Extended piston rod at one end	Piston rod extended at one end						
	[mm]	1 ... 500				...K8	
Clamping unit	Attached					-KP	-KP

[8] K2 Not with K3, K6


[9] K6 Not with K3

[10] K3 Not with K5

# Round cylinders DSNU-Q, protected against rotation


## Datasheet



### P cushioning



-  Diameter  
12 ... 25 mm  
ISO 6432

### PPV cushioning



-  Diameter  
32 ... 63 mm
-  Stroke length  
1 ... 500 mm



General technical data		12	16	20	25	32	40	50	63
Piston Ø		12	16	20	25	32	40	50	63
Based on standard		ISO 6432				-			
Pneumatic connection		M5	M5	G1/8	G1/8	G1/8	G1/4	G1/4	G3/8
Piston rod thread		M6	M6	M8	M10x1.25	M10x1.25	M12x1.25	M16x1.5	M16x1.5
Stroke <sup>1)</sup>	[mm]	1 ... 160		1 ... 200	1 ... 250	1 ... 300	1 ... 400		1 ... 500
Design		Piston Protected against rotation with square piston rod							
Max. torque at the piston rod	[Nm]	0.10	0.10	0.20	0.45	0.8	1.1	1.5	1.5
Cushioning									
DSNU-...-P	Elastic cushioning rings/plates at both ends	-				Elastic cushioning rings/plates at both ends			
DSNU-...-PPV		Pneumatic cushioning adjustable at both ends							
Cushioning length (PPV)	[mm]	-	12	15	17	14	18	20	21
Position sensing		Via proximity switch							
Type of mounting		With accessories							
Mounting position		Any							

- 1) Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.  
Longer strokes on request.

Operating and environmental conditions		12	16	20	25	32	40	50	63
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]							
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)							
Operating pressure <sup>1)</sup>									
DSNU-...	[MPa]	0.15 ... 1 <sup>2)</sup>		0.1 ... 1					
	[bar]	1.5 ... 10 <sup>2)</sup>		1 ... 10					
DSNU-Q-...-S6	[MPa]	-				0.1 ... 0.8			
	[bar]	-				1 ... 8			
Ambient temperature <sup>3)</sup>									
DSNU-...	[°C]	-20 ... +80							
DSNU-Q-...-S6	[°C]	-				0 ... +120			
Corrosion resistance class CRC <sup>4)</sup>									
DSNU-...		2 - Moderate corrosion stress							
DSNU-Q-...-R3		3 - High corrosion stress							

- 1) With variant S2 (through piston rod) or variant KE (stroke adjustment), the minimum operating pressure may increase slightly after an idle period of > 24 hours.  
2) For DSNU-12-...-Q-PPV (pneumatic cushioning adjustable at both ends): 0.2 ... 1 MPa (2 ... 10 bar)  
3) Note operating range of proximity switches  
4) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

## Datasheet

ATEX <sup>1)</sup>	
ATEX category for gas	II 2G
Type of (ignition) protection for gas	c T4
ATEX category for dust	II 2D
Type of ignition protection for dust	c 120 °C
Explosion-proof ambient temperature	-20 °C ≤ Ta ≤ +60 °C
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)	To UK explosion regulations
Explosion protection certification outside the EU	EPL Db (GB)
	EPL Gb (GB)

1) Note the ATEX certification of the accessories.

Forces [N] and impact energy [J]								
Piston Ø	12	16	20	25	32	40	50	63
Theoretical force at 0.6 MPa (6 bar), advancing	68	121	189	295	483	753	1178	1870
Theoretical force at 0.6 MPa (6 bar), retracting	51	104	158	247	415	633	990	1682
Impact energy in the end positions for P cushioning <sup>1)</sup>								
DSNU-...	0.07	0.15	0.2	0.3	0.4	0.7	1	1.3
DSNU-...-S6	0.035	0.075	0.1	0.15	0.2	0.35	0.5	0.65
DSNU-...-KE	0.055	0.12	0.16	0.24	0.32	0.56	0.8	1

1) The values are reduced by approx. 50% at an ambient temperature of 80 °C

Permissible impact velocity: 
$$V = \sqrt{\frac{2 \times E}{m_1 + m_2}}$$

Maximum permissible mass: 
$$m_2 = \frac{2 \times E}{v^2} - m_1$$


V Perm. impact velocity  
 E Max. impact energy  
 m1 Moving mass (drive)  
 m2 Moving payload

Weight [g]								
Piston Ø	12	16	20	25	32	40	50	63
<b>DSNU-...</b>								
Product weight with 0 mm stroke	80	110	215	275	370.5	661	1087	1445
Additional weight per 10 mm stroke	4	4.6	7.2	11	15.5	24	40	44
Moving mass with 0 mm stroke	18.5	23	44	71	121	230	413	459
Moving mass per 10 mm stroke	2	2	4	6	9	16	25	25
<b>DSNU-...-S2</b>								
Moving mass with 0 mm stroke	30	34.5	70	113	182	363	638	701
Moving mass per 10 mm stroke	4	4	8	12	18	32	50	50
<b>DSNU-...-KE</b>								
Moving mass with 0 mm stroke	[15KE]	-	-	-	-	-	-	-
	[25KE]	46	50.5	99	142	251	469	839
	[50KE]	-	-	-	-	-	491	918
Moving mass per 10 mm stroke	4	4	8	12	18	32	50	50

## Datasheet

### Materials

Sectional view



## Datasheet


Round cylinder	
[1]	Piston rod
	DSNU-...
	DSNU-...-R3
[2]	Piston rod bearing
[3]	Bearing cap
[4]	Cylinder barrel
[5]	End cap
[6]	Swivel bearing
-	Piston rod wiper seal
	Stroke adjustment DSNU-...-KE
	Stop element
	Threaded coupling
	LABS (PWIS) conformity
	Cleanroom class
	Note on materials

Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-12 ... 25



∅ [mm]	AM	B ∅ h8	B1	BE	BF	CD ∅ H9	D ∅	D4 ∅	E	EE	EW
12	16	16	5.5	M16x1.5	17	6	20	13.3	18	M5	12
16								17.3			
20	20	22	7	M22x1.5	20	8	30	21.3	26	G1/8	16
25	22		9		22			26.5			


∅ [mm]	G	KK	KV	KW	L	L2	PL	VD	WF ±1.2	XC ±1	ZJ			
12	10	M6	24	8	9	50	6	2	22	75	72			
16						56								
20	16	M8	32	11	12	68	8.2					24	95	92
25		M10x1.25				69.5						28		

Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

S2 – Through piston rod




Note

The thread types at both piston rod ends are identical. The clamping unit is mounted at only one end. In combination with variant Q, the right piston rod is square, the left piston rod round. The clamping unit is mounted on the left round piston rod.

+ = plus stroke length  
 ++ = plus 2x stroke length

KE – Stroke adjustment



+ = plus stroke length  
 ++ = plus 2x stroke length


ø [mm]	A5		D8 ø	ZJ	ZM	√Ra 2	√Ra 3
	DSNU-... -15KE	-25KE					
12	-	43	15	110	132	10	13
16				116	138		
20		47	20	139	163		
25	145.5			173.5			

Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

DSNU-32 ... 63



∅	AM	B ∅ h8	B1	BE	BF	CD ∅ H9	D ∅	D1 ∅	D4 ∅	E	EE	EW
32	22	30	10	M30x1.5	26	10	41	42	33.6	38	G1/8	16
40	24	38	12	M38x1.5	30	12	49	50	41.6	45	G1/4	18
50	32	45	16	M45x1.5	33	16	57	60	52.4	–	G1/4	21
63	32	45	16	M45x1.5	33	16	70	60	65.4	–	G3/8	21


∅	G	KK	KW	L	L2	PL	VD	WF ±1.2	XC ±1	ZJ
32	19	M10x1.25	8	13	69.5	9	2	34	117.5	103.5
40	25	M12x1.25	10	15	84.6	12	3	39	139.6	123.6
50	25	M16x1.5	10	16	86.2	12	3	44	147.2	130.2
63	28	M16x1.5	10	16	94.2	13	3	45	156.2	139.2

Datasheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

S2 – Through piston rod




Note

The thread types at both piston rod ends are identical. The clamping unit is mounted at only one end. In combination with variant Q, the right piston rod is square, the left piston rod round. The clamping unit is mounted on the left round piston rod.

+ = plus stroke length  
++ = plus 2x stroke length

KE – Stroke adjustment




+ = plus stroke length  
++ = plus 2x stroke length

ø [mm]	A5		D8 ø	ZJ	ZM	⊖ 2	⊖ 3
	DSNU-... -25KE	-50KE					
32	52	–	30	158.5	192.5	17	24
40	56	81	35	192.6	231.6	19	30
50	67	92	45	208.2	252.2	24	
63				225.2	270.2		

## Ordering data – Modular product system


Ordering table							
Size	12	16	20	25	Conditions	Code	Enter code
Module no.	<b>193988</b>	<b>193989</b>	<b>193990</b>	<b>193991</b>			
Function	Round cylinder, double-acting, based on ISO 6432					<b>DSNU</b>	DSNU
Piston Ø [mm]	12	16	20	25		-...	
Stroke [mm]	1 ... 160		1 ... 200	1 ... 250	[1]	-...	
Cushioning	Elastic cushioning rings/plates at both ends	-	-	-		<b>-P</b>	
	-	Pneumatic cushioning, adjustable at both ends			[2]	<b>-PPV</b>	
Position sensing	Via proximity switch				[3]	<b>-A</b>	-A
Cylinder end cap	Lateral supply port, short end cap				[4]	<b>-MQ</b>	
	Axial supply port, short end cap	-	-	-	[4]	<b>-MA</b>	
	-	With mounting flange at front (direct mounting), bearing cap			[5]	<b>-MH</b>	
Protection against rotation	Square piston rod					<b>-Q</b>	-Q
Piston rod type	Through piston rod					<b>-S2</b>	
Stroke adjustment, extending [mm]	0 ... 25				[6]	<b>-25KE</b>	

- [1] -... Longer strokes on request  
 [2] PPV Not with MA  
 [3] A Minimum stroke > 10 mm required for reliable sensing  
 [4] MQ, MA Not with S2  
 [5] MH Not with combination Q-R3  
 [6] 25KE Not with MQ, MA, S2, EX4  
 With piston Ø 20, 25: stroke only up to 250 mm



**Note**

The bellows kit DADB must not be used in combination with the variant Q.



**Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.  
 Longer strokes on request

## Ordering data – Modular product system

Ordering table							
Size	12	16	20	25	Conditions	Code	Enter code
Extended male thread	Extended male piston rod thread						
	[mm]	1 ... 20	1 ... 25	1 ... 35	[7]	-...K2	
Shortened male thread	Shortened male piston rod thread						
	[mm]	1 ... 4	1 ... 8	1 ... 10	[8]	-...K6	
Female thread	Piston rod with female thread						
			(M4)	(M6)	[9]	-K3	
Special thread	Special piston rod thread						
				M10		-“...”K5	
Extended piston rod at one end	Piston rod extended at one end						
	[mm]	1 ... 100	1 ... 110	1 ... 150		...K8	
Clamping unit	Attached				[10]	-KP	
Corrosion protection	-		High corrosion protection				-R3
EU certification	II 2GD				[11]	-EX4	

[7]	K2	Not with K3, K6
[8]	K6	Not with K3
[9]	K3	Not with K5
[10]	KP	Only with S2. Not with R3
[11]	EX4	Not with KP

## Ordering data – Modular product system

Ordering table							
Size	32	40	50	63	Conditions	Code	Enter code
Module no.	<b>193992</b>	<b>193993</b>	<b>193994</b>	<b>193995</b>			
Function	Double-acting round cylinder					<b>DSNU</b>	DSNU
Piston Ø [mm]	32	40	50	63		-...	
Stroke [mm]	1 ... 300	1 ... 400		1 ... 500	[1]	-...	
Cushioning	Elastic cushioning rings/plates at both ends					<b>-P</b>	
	Pneumatic cushioning adjustable at both ends				[2]	<b>-PPV</b>	
Position sensing	Via proximity switch				[3]	<b>-A</b>	-A
Cylinder end cap	Lateral supply port, short end cap				[4]	<b>-MQ</b>	
	Axial supply port, short end cap				[4]	<b>-MA</b>	
	Mounting flange at the front (direct mounting), bearing cap				[5]	<b>-MH</b>	
Protection against rotation	Square piston rod					<b>-Q</b>	-Q
Piston rod type	Through piston rod					<b>-S2</b>	
Stroke adjustment, extending	[mm]	0 ... 25			[6]	<b>-25KE</b>	
	[mm]	-	0 ... 50		[6]	<b>-50KE</b>	

- [1] -... Longer strokes on request
- [2] PPV Not with MA
- [3] A Minimum stroke > 10 mm required for reliable sensing
- [4] MQ, MA Not with S2
- [5] MH Not with combinations: Q-R3, S6-R3. Not with KP
- [6] KE Not with MQ, MA, S2, S6, EX4



**Note**

The bellows kit DADB must not be used in combination with the variant Q.



**Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.  
Longer strokes on request

## Ordering data – Modular product system

Ordering table							
Size	32	40	50	63	Conditions	Code	Enter code
Extended male thread	Extended male piston rod thread						
	[mm]	1 ... 35		1 ... 70		[7]	-...K2
Shortened male thread	Shortened male piston rod thread						
	[mm]	1 ... 8		1 ... 10		[8]	-...K6
Female thread	Piston rod with female thread						
		(M6)	(M8)	(M10)		[9]	-K3
Special thread	Special piston rod thread						
		M10	M12	M16			-“...”K5
Extended piston rod at one end	Piston rod extended at one end						
	[mm]	1 ... 500					
Clamping unit	Attached					[10]	-KP
Temperature resistance	Heat-resistant seals max. 120 °C						-S6
Corrosion protection	High corrosion protection						-R3
EU certification	II 2GD					[11]	-EX4

- [7] K2 Not with K3, K6  
 [8] K6 Not with K  
 [9] K3 Not with K5  
 [10] KP Only with S2. Not with S6, R3  
 [11] EX4 Not with KP, S6

## Accessories

### Foot mounting HBN/CRHBN

Scope of delivery:

HBN/CRHBN-...x1: 1 foot


HBN/CRHBN-...x2: 2 feet and 1 nut

Material:

HBN: Galvanised steel

CRHBN: High-alloy stainless steel

RoHS-compliant



#### Dimensions and ordering data

For Ø [mm]	AB ∅	AH	AO	AT	AU	R1	SA		TR	US	XA		XS	
								DSNU-KP				DSNU-KP		DSNU-KP
8, 10	4.5	16	5	3	11	10	68	97	25	35	73	102	24	-
12	5.5	20	6	4	14	13	78	116	32	42	86	124	32	-
16	5.5	20	6	4	14	13	84	122	32	42	92	130	32	-
20	6.6	25	8	5	17	20	102	149	40	54	109	156	36	-
25	6.6	25	8	5	17	20	103.5	151.5	40	54	114.5	162.5	40	-


For Ø [mm]	Basic version				High corrosion protection			
	CRC <sup>1)</sup>	Weight [g]	Part no.	Type	CRC <sup>1)</sup>	Weight [g]	Part no.	Type
8, 10	1	22	5123	HBN-8/10x1	-	-	-	
	1	54	5124	HBN-8/10x2	-	-	-	
12, 16	1	43	5125	HBN-12/16x1	4	43	161866	CRHBN-12/16x1
	1	107	5126	HBN-12/16x2	4	107	162999	CRHBN-12/16x2
20, 25	1	95	5127	HBN-20/25x1	4	94	161867	CRHBN-20/25x1
	1	237	5128	HBN-20/25x2	4	236	162998	CRHBN-20/25x2

1) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

## Accessories

### Foot mounting HBN/CRH

Material:  
 HBN: Galvanised steel  
 CRH: High-alloy stainless steel  
 RoHS-compliant



#### Dimensions and ordering data

For Ø [mm]	AB ∅	AH	AO	AT	AU	SA		TR	US	XA		XS	
							DSNU-KP				DSNU-KP		
32	7	28	7	4	14	97.5	151	52	66	117.5	171	44	-
40	9	33	10	5	20	124.6	192.1	60	80	143.6	206.1	54	-
50	9	40	10	6	20	126.2	202.7	70	90	150.2	226.7	58	-
63	9	45	10	6	20	134.2	218.7	76	96	159.2	243.7	59	-

For Ø [mm]	Basic version				High corrosion protection			
	CRC <sup>1)</sup>	Weight [g]	Part no.	Type	CRC <sup>1)</sup>	Weight [g]	Part no.	Type
32	1	353	195851	HBN-32x2	4	353	162951	CRH-32
40	1	611	195852	HBN-40x2	4	611	162952	CRH-40
50	1	916	195853	HBN-50x2	4	916	162953	CRH-50
63	1	1066	195854	HBN-63x2	4	1066	162954	CRH-63

1) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)


## Accessories

### Flange mounting FBN/CRFBN

Material:

FBN: Galvanised steel

CRFBN: High-alloy stainless steel



#### Dimensions and ordering data

For Ø [mm]	AB ∅	AT	TF	UF	UR	W	ZF	
								DSNU-KP
8, 10	4.5	3	30	40	25	13	65	94
12	5.5	4	40	53	30	18	76	114
16	5.5	4	40	53	30	18	82	120
20	6.6	5	50	66	40	19	97	144
25	6.6	5	50	66	40	23	102.5	150.5

For Ø [mm]	Basic version				High corrosion protection			
	CRC <sup>1)</sup>	Weight [g]	Part no.	Type	CRC <sup>1)</sup>	Weight [g]	Part no.	Type
8, 10	1	12	<b>5129</b>	<b>FBN-8/10</b>	-	-	-	-
12, 16	1	26	<b>5130</b>	<b>FBN-12/16</b>	4	26	<b>161864</b>	<b>CRFBN-12/16</b>
20, 25	1	52	<b>5131</b>	<b>FBN-20/25</b>	4	52	<b>161865</b>	<b>CRFBN-20/25</b>

1) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

## Accessories


## Flange mounting FBN/CRFV

Material:

FBN: Galvanised steel

CRFV: High-alloy stainless steel

RoHS-compliant



## Dimensions and ordering data

For Ø [mm]	AB Ø	AT	H1	TF	TR	US	W ±1.2	ZF	
									DSNU-KP
32	7	4	14	28	52	66	30	107.5	161
40	9	5	18	30	60	80	29	128.6	191.1
50	9	6	20	40	70	90	38	136.2	212.6
63	9	6	20	50	76	96	39	145.2	229.7



For Ø [mm]	Basic version				High corrosion protection			
	CRC <sup>1)</sup>	Weight [g]	Part no.	Type	CRC <sup>1)</sup>	Weight [g]	Part no.	Type
32	1	103	<b>195855</b>	<b>FBN-32</b>	4	103	<b>161858</b>	<b>CRFV-32</b>
40	1	191	<b>195856</b>	<b>FBN-40</b>	4	191	<b>161859</b>	<b>CRFV-40</b>
50	1	292	<b>195857</b>	<b>FBN-50</b>	4	292	<b>161860</b>	<b>CRFV-50</b>
63	1	367	<b>195858</b>	<b>FBN-63</b>	4	367	<b>161861</b>	<b>CRFV-63</b>

1) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

## Accessories

### Swivel mounting SBN

Material:  
 Retaining ring: Anodised wrought aluminium alloy  
 Bearing: Bronze  
 Screws: Galvanised steel  
 Bracket: Steel  
 Cannot be used on the bearing cap in combination with bellows kit DADB.





#### Dimensions and ordering data

For Ø	CM	FL	GL	HB	L1	LE	MR	RF	RG	UK	UX	CRC <sup>1)</sup>	Weight	Part no.	Type
[mm]					max.								[g]		
20/25	38.1+0.4	35	20	7	60.2	31	12	20	24	46.1	40	1	238	539927	SBN-20/25
32	46.1+0.2	40	27	9	72.2	35	13	28	30	56.1	50	1	361	539924	SBN-32
40	57.1+0.2	45	30	9	88.2	39	14	36	34	69.1	54	1	593	539925	SBN-40
50/63	70.1+0.4	50	34	9	102.2	44	16	42	35	82.1	65	1	894	539926	SBN-50/63

1) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

### Swivel mounting WBN

Material:  
 Galvanised steel  
 RoHS-compliant  
 Cannot be used on the bearing cap in combination with bellows kit DADB.



+ = plus stroke length

#### Dimensions and ordering data

For Ø	TD	TK	TM	UM	UW	XH	XL		CRC <sup>1)</sup>	Weight	Part no.	Type
[mm]	Ø							DSNU-KP		[g]		
	-0.01/ -0.05											
8, 10	4	6	26	38	20	13	65	94	1	20	8608	WBN-8/10
12	6	8	38	58	25	18	76	114	1	51	8609	WBN-12/16
16	6	8	38	58	25	18	82	120	1	51	8609	WBN-12/16
20	6	8	46	66	30	20	96	143	1	67	8610	WBN-20/25
25	6	8	46	66	30	24	101.5	149.5	1	67	8610	WBN-20/25
32	8	12	50	76	40	28	109.5	163	1	131	195863	WBN-32
40	10	15	60	92	50	31.5	126.1	193.6	1	238	195864	WBN-40
50	12	20	80	116	65	34	140.2	216.7	1	596	195865	WBN-50/63
63	12	20	80	116	65	35	149.2	233.7	1	596	195865	WBN-50/63

1) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

## Accessories


## Clevis foot LBN/CRLBN

Material:

LBN: galvanised steel

CRLBN: High-alloy stainless steel

RoHS-compliant



## Dimensions and ordering data





For $\varnothing$ [mm]	CM	EK $\varnothing$	FL	GL	HB	LE	MR	RG	UX
8, 10	8.1	4	24 +0.3/-0.2	13.8	4.5	21.5	5	12.5	20
12, 16	12.1	6	27 +0.3/-0.2	13	5.5	24	7	15	25
20, 25	16.1	8	30 +0.4/-0.2	16	6.6	26	10	20	32
32	16.1	10	35 +0.4/-0.2	18.5	6.6	31	11	24	35
40	18.1	12	40 +0.4/-0.2	24.5	9	35	13	30	45
50, 63	21.1	16	45 +0.5/-0.2	28	9	39	14	34	50

For $\varnothing$ [mm]	Basic version				High corrosion protection			
	CRC <sup>1)</sup>	Weight [g]	Part no.	Type	CRC <sup>1)</sup>	Weight [g]	Part no.	Type
8, 10	1	20	<b>6057</b>	<b>LBN-8/10</b>	-	-	-	
12, 16	1	40	<b>6058</b>	<b>LBN-12/16</b>	4	39	<b>161862</b>	<b>CRLBN-12/16</b>
20, 25	1	84	<b>6059</b>	<b>LBN-20/25</b>	4	82	<b>161863</b>	<b>CRLBN-20/25</b>
32	1	110	<b>195860</b>	<b>LBN-32</b>	4	106	<b>195866</b>	<b>CRLBN-32</b>
40	1	191	<b>195861</b>	<b>LBN-40</b>	4	185	<b>195867</b>	<b>CRLBN-40</b>
50, 63	1	300	<b>195862</b>	<b>LBN-50/63</b>	4	283	<b>195868</b>	<b>CRLBN-50/63</b>





1) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

Accessories

Ordering data – Piston rod attachments



Designation	For Ø	Part no.	Type
<b>Rod eye SGS</b>			
	8	9253	SGS-M4
	10		
	12		
	16	9254	SGS-M6
	20		
	25		
	32	9255	SGS-M8
	40		
	50		
63	9261	SGS-M10x1.25	
63			
<b>Self-aligning rod coupler FK</b>			
	8	6528	FK-M4
	10		
	12		
	16	2061	FK-M6
	20		
	25		
	32	2062	FK-M8
	40		
	50		
63	6140	FK-M10x1.25	
63			
<b>Rod clevis SG</b>			
	8	6532	SG-M4
	10		
	12		
	16	3110	SG-M6
	20		
	25		
	32	3111	SG-M8
	40		
	50		
63	6144	SG-M10x1.25	
63			
<b>Coupling piece KSZ</b>			
	12	36123	KSZ-M6
	16		
	20	36124	KSZ-M8
	25		
	32	36125	KSZ-M10x1.25
	40		
	50	36126	KSZ-M12x1.25
63			

Datasheets → Internet: piston rod attachment


Designation	For Ø	Part no.	Type		
<b>Rod clevis SGA</b>					
	8	-			
	10				
	12				
	16				
	20				
	25				
	32			32954	SGA-M10x1.25
	40			10767	SGA-M12x1.25
	50			10768	SGA-M16x1.5
63					
<b>Self-aligning rod coupler DARP</b>					
	8	8170110	DARP-M4-F		
	10				
	12				
	16	8170115	DARP-M6-F		
	20				
	25				
	32	8170116	DARP-M8-F		
	40				
	50				
63	8170119	DARP-M10P-F			
63					
<b>Coupling piece KSG</b>					
	8	-			
	10				
	12				
	16				
	20				
	25			32963	KSG-M10x1.25
	32			32964	KSG-M12x1.25
	40				
	50				
63	32965	KSG-M16x1.5			
<b>Hex nut MSK</b>					
	16	189007	MSK-M16x1.5		
	20				
	25	189009	MSK-M22x1.5		

## Accessories


### Ordering data – Piston-rod attachments, corrosion-resistant

Designation	For Ø	Part no.	Type
<b>Rod eye CRSGS</b>			
	12	195580	CRSGS-M6
	16		
	20		
	25	195581	CRSGS-M8
	32		
	40	195583	CRSGS-M12x1.25
	50	195584	CRSGS-M16x1.5
	63		
<b>Self-aligning rod coupler CRFK</b>			
	25	2305778	CRFK-M10x1.25
	32		
	40	2305779	CRFK-M12x1.25
	50	2490673	CRFK-M16x1.5
	63		


Datasheets → Internet: piston rod attachment

Designation	For Ø	Part no.	Type
<b>Rod clevis CRSG</b>			
	8	8165295	CRSG-M4
	12	13567	CRSG-M6
	16		
	20	13568	CRSG-M8
	25	13569	CRSG-M10x1.25
	32		
	40	13570	CRSG-M12x1.25
	50	13571	CRSG-M16x1.5
	63		


### Ordering data – Mounting components

Designation	For Ø	Part no.	Type
<b>Clevis foot LBG</b>			
	32	31761	LBG-32
	40	31762	LBG-40
	50	31763	LBG-50
	63	31764	LBG-63

Datasheets → Internet: clevis foot

Designation	For Ø	Part no.	Type
<b>Right angle clevis foot LQG</b>			
	32	31768	LQG-32
	40	31769	LQG-40
	50	31770	LQG-50
	63	31771	LQG-63

### Ordering data – Guide units

	For Ø	Stroke [mm]	With recirculating ball bearing guide		With plain-bearing guide	
			Part no.	Type	Part no.	Type
	8, 10	1 ... 100	35197	FEN-8/10-...-KF	35196	FEN-8/10-...-GF
	12, 16	1 ... 200	33481	FEN-12/16-...-KF	19168	FEN-12/16-...-GF
	20	2 ... 250	33482	FEN-20-...-KF	19169	FEN-20-...-GF
	25	2 ... 250	33483	FEN-25-...-KF	19170	FEN-25-...-GF

Datasheets → Internet: feng

## Accessories

### Bellows kit DADB




General technical data								
Type DADB-S1-	12	16	20	25	32	40	50	63
Max. stroke range of the cylinder <sup>1)</sup>								
DSNU	[mm]	10 ... 200	10 ... 200	10 ... 320	10 ... 500			
Type of mounting		Via threaded pin						
Mounting position		Any						
Media resistance		Dust, chippings, oil, grease, fuel (→ Internet: media resistance)						
Ambient temperature <sup>2)</sup>	[°C]	-10 ... +80						
Corrosion resistance class CRC <sup>3)</sup>		3 - High corrosion stress						

- 1) In conjunction with the bellows kit DADB
- 2) Note operating range of proximity switches and cylinder
- 3) More information [www.festo.com/x/topic/crc](http://www.festo.com/x/topic/crc)

### Materials

#### Sectional view



Bellows	
[1] Connection	Polyamide
[2] Intermediate piece	Polyamide
[3] Bellows	NBR
[4] End piece	Polyamide
- O-ring	NBR
Note on materials	RoHS-compliant
Suitable for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)

## Accessories

<b>Weight [g]</b>				
Type DADB-S1- Stroke [mm]	12	16	20	25
10 ... 50	7	7	20	19
51 ... 100	9	9	32	31
101 ... 150	13	13	45	44
151 ... 200	16	16	58	57
201 ... 250	–	–	73	72
251 ... 300	–	–	85	84
301 ... 350	–	–	100	98
351 ... 400	–	–	–	109
401 ... 450	–	–	–	124
451 ... 500	–	–	–	136

Type DADB-S1- Stroke [mm]	32	40	50	63
10 ... 50	29	34	55	55
51 ... 125	41	49	75	75
126 ... 175	51	60	89	89
176 ... 250	66	78	113	113
251 ... 300	79	93	131	131
301 ... 350	92	108	149	149
351 ... 375	92	108	151	151
376 ... 425	104	122	169	169
426 ... 475	117	137	187	187
476 ... 500	117	137	189	189



Accessories

Travel speed  $v$  as a function of tubing length  $l$



The bellows kit is a leak-free system. To prevent unwanted media from being drawn in, the supply or exhaust air of the kit is ducted in the connection part via a pressure compensation opening. The pressure generated in the bellows kit by the positioning motion is primarily defined by the travel speed and tubing length. The recommended tube length in relation to the travel speed of the drive can be read from the diagram.



Advancing



— DSNU-12/16  
 - - - - - DSNU-20/25

— DSNU-32/50/63  
 - - - - - DSNU-40

Retracting



— DSNU-12/16  
 - - - - - DSNU-20/25

— DSNU-32  
 - - - - - DSNU-40  
 - - - - - DSNU-50/63


Note  
 The push-in fittings in the adjacent table must be used for the pressure compensation hole. Silencers can be used as an alternative. This reduces the travel speed slightly.

Tubing size and push-in fitting for pressure compensation hole			
∅ [mm]	Tubing O.D. [mm]	Push-in fitting	
		Part no.	Type
12, 16, 20, 25	6	153317	QSM-M5-6-I
		578371	NPQH-DK-M5-Q6-P10
		578335	NPQH-D-M5-Q6-P10
		578359	NPQH-D-M5-S6-P10
32, 40	8	186109	QS-G1/8-8-I
		578376	NPQH-DK-G18-Q8-P10
		578362	NPQH-D-G18-S8-P10
50, 63	12	186350	QS-G1/4-12
		578344	NPQH-D-G14-Q12-P10
		578366	NPQH-D-G14-S12-P10

Accessories

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



∅ Stroke [mm]	12/16							20						
	A2 <sup>1)</sup>	D1 ∅ max.	D2 ∅	EE	L1	L2	WF+A2	A2 <sup>1)</sup>	D1 ∅ max.	D2 ∅	EE	L1	L2	WF+A2
10 ... 50	23	22	8.5	M5	5	3.2	45	22	29	8.5	M5	4.2	2.7	46
51 ... 100	34						56	34						58
101 ... 150	48						70	47						71
151 ... 200	59						81	60						84
201 ... 250	–						–	75						99
251 ... 300	–						–	86						110
301 ... 350	–						–	101						125
351 ... 400	–						–	–						–
401 ... 450	–						–	–						–
451 ... 500	–						–	–						–


∅ Stroke [mm]	25						
	A2 <sup>1)</sup>	D1 ∅ max.	D2 ∅	EE	L1	L2	WF+A2
10 ... 50	22	29	8.5	M5	4.2	2.7	50
51 ... 100	34						62
101 ... 150	47						75
151 ... 200	60						88
201 ... 250	75						103
251 ... 300	86						114
301 ... 350	101						129
351 ... 400	112						140
401 ... 450	127						155
451 ... 500	138						166

1) The dimension corresponds to the K8 value (extended piston rod) of the drive

Accessories

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



∅ Stroke [mm]	32							40						
	A2 <sup>1)</sup>	D1 ∅ max.	D2 ∅	EE	L1	L2	WF+A2	A2 <sup>1)</sup>	D1 ∅ max.	D2 ∅	EE	L1	L2	WF+A2
10 ... 50	30	38	14	G1/8	12.9	5.4	64	29	46	14	G1/8	8.1	5.4	68
51 ... 125	48						82	44						83
126 ... 175	63						97	57						96
176 ... 250	82						116	73						112
251 ... 300	97						131	87						126
301 ... 350	113						147	101						140
351 ... 375	115						149	102						141
376 ... 425	131						165	116						155
426 ... 475	147						181	131						170
476 ... 500	149						183	132						171

∅ Stroke [mm]	50/63						
	A2 <sup>1)</sup>	D1 ∅ max.	D2 ∅	EE	L1	L2	WF+A2
10 ... 50	30	57	17	G1/4	10.65	7	74/75
51 ... 125	48						92/93
126 ... 175	58						102/103
176 ... 250	77						121/122
251 ... 300	88						132/133
301 ... 350	99						143/144
351 ... 375	106						150/151
376 ... 425	117						161/162
426 ... 475	128						172/173
476 ... 500	135						179/180

1) The dimension corresponds to the K8 value (extended piston rod) of the drive

## Accessories

## Ordering data – Bellows kit

An extended piston rod (order code K8) is absolutely essential when using a bellows kit → Ordering data – Modular product system.

The necessary dimension for K8 as a function of piston diameter and cylinder stroke as well as the corresponding bellows kit is indicated in the table below:

## Order example:

Selected round cylinder:

DSNU-25-320-PPV-A-MQ-...

The dimension for the corresponding K8 value (see table): 101 mm

Complete order reference for round cylinder:


DSNU-25-320-PPV-A-MQ-...-101K8


The corresponding bellows kit:


DADB-S1-25-S301-350


Cylinder data			Bellows kit		
∅	Stroke	Dimension for K8	Part no.	Type	
[mm]	[mm]	[mm]			
12	10 ... 50	23	553391	DADB-S1-12-S10-50	
	51 ... 100	34	553393	DADB-S1-12-S51-100	
	101 ... 150	48	553395	DADB-S1-12-S101-150	
	151 ... 200	59	553397	DADB-S1-12-S151-200	
20	10 ... 50	22	553407	DADB-S1-20-S10-50	
	51 ... 100	34	553409	DADB-S1-20-S51-100	
	101 ... 150	47	553411	DADB-S1-20-S101-150	
	151 ... 200	60	553413	DADB-S1-20-S151-200	
	201 ... 250	75	553415	DADB-S1-20-S201-250	
	251 ... 300	86	553417	DADB-S1-20-S251-300	
	301 ... 320	101	553419	DADB-S1-20-S301-350	
32	10 ... 50	30	553441	DADB-S1-32-S10-50	
	51 ... 125	48	553443	DADB-S1-32-S51-125	
	126 ... 175	63	553445	DADB-S1-32-S126-175	
	176 ... 250	82	553447	DADB-S1-32-S176-250	
	251 ... 300	97	553449	DADB-S1-32-S251-300	
	301 ... 350	113	553451	DADB-S1-32-S301-350	
	351 ... 375	115	553453	DADB-S1-32-S351-375	
	376 ... 425	131	553455	DADB-S1-32-S376-425	
	426 ... 475	147	553457	DADB-S1-32-S426-475	
476 ... 500	149	553459	DADB-S1-32-S476-500		
50	10 ... 50	30	553481	DADB-S1-50-S10-50	
	51 ... 125	48	553483	DADB-S1-50-S51-125	
	126 ... 175	58	553485	DADB-S1-50-S126-175	
	176 ... 250	77	553487	DADB-S1-50-S176-250	
	251 ... 300	88	553489	DADB-S1-50-S251-300	
	301 ... 350	99	553491	DADB-S1-50-S301-350	
	351 ... 375	106	553493	DADB-S1-50-S351-375	
	376 ... 425	117	553495	DADB-S1-50-S376-425	
	426 ... 475	128	553497	DADB-S1-50-S426-475	
476 ... 500	135	553499	DADB-S1-50-S476-500		
16	10 ... 50	23	553399	DADB-S1-16-S10-50	
	51 ... 100	34	553401	DADB-S1-16-S51-100	
	101 ... 150	48	553403	DADB-S1-16-S101-150	
	151 ... 200	59	553405	DADB-S1-16-S151-200	
	25	10 ... 50	22	553421	DADB-S1-25-S10-50
		51 ... 100	34	553423	DADB-S1-25-S51-100
		101 ... 150	47	553425	DADB-S1-25-S101-150
		151 ... 200	60	553427	DADB-S1-25-S151-200
		201 ... 250	75	553429	DADB-S1-25-S201-250
251 ... 300		86	553431	DADB-S1-25-S251-300	
301 ... 350		101	553433	DADB-S1-25-S301-350	
351 ... 400		112	553435	DADB-S1-25-S351-400	
401 ... 450		127	553437	DADB-S1-25-S401-450	
451 ... 500	138	553439	DADB-S1-25-S451-500		
40	10 ... 50	29	553461	DADB-S1-40-S10-50	
	51 ... 125	44	553463	DADB-S1-40-S51-125	
	126 ... 175	57	553465	DADB-S1-40-S126-175	
	176 ... 250	73	553467	DADB-S1-40-S176-250	
	251 ... 300	87	553469	DADB-S1-40-S251-300	
	301 ... 350	101	553471	DADB-S1-40-S301-350	
	351 ... 375	102	553473	DADB-S1-40-S351-375	
	376 ... 425	116	553475	DADB-S1-40-S376-425	
	426 ... 475	131	553477	DADB-S1-40-S426-475	
476 ... 500	132	553479	DADB-S1-40-S476-500		
63	10 ... 50	30	553501	DADB-S1-63-S10-50	
	51 ... 125	48	553503	DADB-S1-63-S51-125	
	126 ... 175	58	553505	DADB-S1-63-S126-175	
	176 ... 250	77	553507	DADB-S1-63-S176-250	
	251 ... 300	88	553509	DADB-S1-63-S251-300	
	301 ... 350	99	553511	DADB-S1-63-S301-350	
	351 ... 375	106	553513	DADB-S1-63-S351-375	
	376 ... 425	117	553515	DADB-S1-63-S376-425	
	426 ... 475	128	553517	DADB-S1-63-S426-475	
476 ... 500	135	553519	DADB-S1-63-S476-500		


Accessories

Ordering data – Proximity switch for T-slot, magneto-resistive						Datasheets → Internet: smt
Type of mounting	Switching output	Electrical connection	Cable length [m]	Part no.	Type	
<b>N/O</b>						
	Inserted in the slot from above, flush with the cylinder profile, short design	PNP	Cable, 3-core	2.5	574335	SMT-8M-A-PS-24V-E-2.5-OE
			Cable, 2-core	5	8165237	SMT-8M-A-ZS-24V-E-5.0-OE
			Plug M8x1, 3-pin	0.3	574334	SMT-8M-A-PS-24V-E-0.3-M8D
		NPN	Cable, 3-core	2.5	574338	SMT-8M-A-NS-24V-E-2.5-OE
			Plug M8x1, 3-pin	0.3	574339	SMT-8M-A-NS-24V-E-0.3-M8D





Ordering data – Proximity switch for T-slot, magneto-resistive						Datasheets → Internet: crsmt
Type of mounting	Switching output	Electrical connection	Cable length [m]	Part no.	Type	
<b>N/O</b>						
	Inserted in the slot from above, flush with the cylinder profile	PNP	Cable, 3-core	5.0	574380	CRSMT-8M-PS-24V-K-5.0-OE
			Cable, 3-core	10.0	574381	CRSMT-8M-PS-24V-K-10.0-OE
			Plug M8x1, 3-pin	0.3	574383	CRSMT-8M-PS-24V-K-0.3-M8D
			Plug M12x1, 3-pin	0.3	574382	CRSMT-8M-PS-24V-K-0.3-M12

Ordering data – Proximity switch for T-slot, magnetic Hall						Datasheets → Internet: sdbt
Type of mounting	Switching output	Electrical connection	Cable length [m]	Part no.	Type	
<b>N/O or N/C contact, switchable</b>						
	Inserted in the slot from above, flush with the cylinder profile, short design	PNP, switchable to NPN	Plug M8x1, 3-pin	0.3	8059120	SDBT-MSX-1L-PU-E-0.3-N-M8
			Cable, 3-core	2.5	8059121	SDBT-MSX-1L-PU-E-2.5-N-LE
		NPN, switchable to PNP	Plug M8x1, 3-pin	0.3	8059123	SDBT-MSX-1L-NU-E-0.3-N-M8
			Cable, 3-core	2.5	8059124	SDBT-MSX-1L-NU-E-2.5-N-LE

Ordering data – Mounting kits for proximity switches				Datasheets → Internet: smbr
Designation	For Ø	Part no.	Type	
<b>Mounting kit SMBR-8</b>				
	8	175091	SMBR-8-8	
	10	175092	SMBR-8-10	
	12	175093	SMBR-8-12	
	16	175094	SMBR-8-16	
	20	175095	SMBR-8-20	
	25	175096	SMBR-8-25	
	32	175097	SMBR-8-32	
	40	175098	SMBR-8-40	
	50	175099	SMBR-8-50	
63	175100	SMBR-8-63		

Ordering data – Mounting kits for proximity switches, temperature range S6				Datasheets → Internet: smbr
Designation	For Ø	Part no.	Type	
<b>Mounting kit SMBR-8</b>				
	8 ... 63	538937	SMBR-8-8/100-S6	

## Accessories

Connecting cables NEBA, straight, M8 connection						
	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M8x1 A-coded to EN 61076-2-104	Open end	3	2.5 m	8078223	NEBA-M8G3-U-2.5-N-LE3
				5 m	8078224	NEBA-M8G3-U-5-N-LE3
Connecting cables NEBA, straight, M12 connection						
	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	3	2.5 m	8078236	NEBA-M12G5-U-2.5-N-LE3
				5 m	8078237	NEBA-M12G5-U-5-N-LE3
Connecting cables NEBA, angled, M8 connection						
	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M8x1 A-coded to EN 61076-2-104	Open end	3	2.5 m	8078230	NEBA-M8W3-U-2.5-N-LE3
				5 m	8078231	NEBA-M8W3-U-5-N-LE3
Connecting cables NEBA, angled, M12 connection						
	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M12x1, A-coded to EN 61076-2-101	Open end	3	2.5 m	8078245	NEBA-M12W5-U-2.5-N-LE3
				5 m	8078246	NEBA-M12W5-U-5-N-LE3

## Accessories


### Position transmitter

The position transmitter continuously senses the position of the piston.

It has an analogue output with an output signal that is proportional to the piston position.


#### Ordering data – Position transmitter for T-slot

Datasheets → Internet: sdas

	Position measuring range	Description	Type of mounting	Electrical connection	Cable length [m]	Part no.	Type
	≤ 52	Choice of two operating modes: • Two adjustable switching outputs • IO-Link®	Inserted in the slot from above	Plug M8x1, 4-pin, lengthwise	0.3	<b>8063974</b>	<b>SDAS-MHS-M40-1L-PNLK-PN-E-0.3-M8</b>


#### Ordering data – Position transmitter for T-slot

Datasheets → Internet: sdat

	Position measuring range	Analogue output		Type of mounting	Electrical connection	Cable length [m]	Part no.	Type
		[V]	[mA]					
	0 ... 50	–	4 ... 20	Inserted in the slot from above	Plug M8x1, 4-pin, lengthwise	0.3	<b>1531265</b>	<b>SDAT-MHS-M50-1L-SA-E-0.3-M8</b>
	0 ... 80						<b>1531266</b>	<b>SDAT-MHS-M80-1L-SA-E-0.3-M8</b>
	0 ... 100						<b>1531267</b>	<b>SDAT-MHS-M100-1L-SA-E-0.3-M8</b>
	0 ... 125						<b>1531268</b>	<b>SDAT-MHS-M125-1L-SA-E-0.3-M8</b>
	0 ... 160						<b>1531269</b>	<b>SDAT-MHS-M160-1L-SA-E-0.3-M8</b>


#### Ordering data – Position transmitter for T-slot

Datasheets → Internet: smat


	Position measuring range	Analogue output		Type of mounting	Electrical connection	Cable length [m]	Part no.	Type
		[V]	[mA]					
	0 ... 40	0 ... 10	–	Inserted in the slot from above	Plug M8x1, 4-pin, lengthwise	0.3	<b>553744</b>	<b>SMAT-8M-U-E-0.3-M8D</b>


#### Ordering data – Mounting kits for position transmitters


Datasheets → Internet: smbr



Designation	For Ø	Part no.	Type
<b>Mounting kit SMBR-8</b>			
	8	<b>175091</b>	<b>SMBR-8-8</b>
	10	<b>175092</b>	<b>SMBR-8-10</b>
	12	<b>175093</b>	<b>SMBR-8-12</b>
	16	<b>175094</b>	<b>SMBR-8-16</b>
	20	<b>175095</b>	<b>SMBR-8-20</b>
	25	<b>175096</b>	<b>SMBR-8-25</b>
	32	<b>175097</b>	<b>SMBR-8-32</b>
	40	<b>175098</b>	<b>SMBR-8-40</b>
	50	<b>175099</b>	<b>SMBR-8-50</b>
	63	<b>175100</b>	<b>SMBR-8-63</b>

## Accessories

Ordering data – Mounting kits for position transmitters, temperature range S6				Datasheets → Internet: smbr	
Designation	For Ø	Part no.	Type		
<b>Mounting kit SMBR-8</b>					
	8 ... 63	538937	SMBR-8-8/100-S6		

Connecting cables NEBA, straight						
	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M8x1 A-coded to EN 61076-2-104	Open end	4	2.5 m	8078227	NEBA-M8G4-U-2.5-N-LE4
				5 m	8078228	NEBA-M8G4-U-5-N-LE4

Connecting cables NEBA, angled						
	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/cores	Cable length	Part no.	Type
	M8x1 A-coded to EN 61076-2-104	Open end	4	2.5 m	8078233	NEBA-M8W4-U-2.5-N-LE4
				5 m	8078234	NEBA-M8W4-U-5-N-LE4

Ordering data – One-way flow control valves					Datasheets → Internet: grl		
	Connection Thread	For tubing O.D.	Material	Part no.	Type		
<b>For exhaust air</b>							
	M5	3	Metal design	193137	GRLA-M5-QS-3-D		
		4		193138	GRLA-M5-QS-4-D		
		6		193139	GRLA-M5-QS-6-D		
	G1/8	3		193142	GRLA-1/8-QS-3-D		
		4		193143	GRLA-1/8-QS-4-D		
		6		193144	GRLA-1/8-QS-6-D		
	G1/4	8		193145	GRLA-1/8-QS-8-D		
		6		193146	GRLA-1/4-QS-6-D		
		8		193147	GRLA-1/4-QS-8-D		
	G3/8	10		193148	GRLA-1/4-QS-10-D		
		6		193149	GRLA-3/8-QS-6-D		
		8		193150	GRLA-3/8-QS-8-D		
		10	193151	GRLA-3/8-QS-10-D			
<b>For supply air</b>							
	M5	3	Metal design	193153	GRLZ-M5-QS-3-D		
		4		193154	GRLZ-M5-QS-4-D		
		6		193155	GRLZ-M5-QS-6-D		
	G1/8	3		193156	GRLZ-1/8-QS-3-D		
		4		193157	GRLZ-1/8-QS-4-D		
		6		193158	GRLZ-1/8-QS-6-D		
				8	193159	GRLZ-1/8-QS-8-D	