# Solenoid valves MH2, MH3, MH4, fast-switching valves





### Key features

#### Fast-switching valves from Festo: it's not just the switching that's fast

Pros that switch as fast as 2 milliseconds

Speed, dynamic response and precision are more sought after than ever before in modern automation. The solution lies in pneumatic components. The result: shorter cycle times in return for comparatively low investment costs for the components. Maximum process reliability, sturdiness and service life are guaranteed. High speed in production

The fast-switching valves are a technological treat for all things high-speed. With switching times  $\leq 2$  ms and a repetition accuracy  $\leq 0.2$  ms, they represent the pinnacle of what is technologically achievable worldwide – even in 24-hour continuous operation with over 500 million cycles. Simple to retrofit in existing systems, or setting the pace for newly designed systems. Naturally compact, including maximum component density. Indispensable for sorting parts using an air ejector, in flap control systems, for gluing, dispensing, packaging and, of course, also suitable for pick & place vacuum applications, for example (continuous holding not possible).

#### Faster switching

Extremely short switching times enable short cycle times. Extremely precise switching makes it possible to control the timing of process sequences accurately.

High output and very good machine utilisation are included. Excellent repetition accuracy of switching times ensures consistent processes, improves process and part quality and reduces rejects and rework.

#### Faster installation

With a variety of connection options such as thread or integrated push-in tubing connectors and a range of mounting options for individual valves or valve manifold assembly, the installation can be perfectly adapted to onsite circumstances while the footprint is kept to a minimum. Fast-switching valves can be used directly in the application without additional protective measures. As a result, very short pneumatic lines guarantee short signal paths and fast response times.

### Key features

#### Fast-switching valves from Festo: it's not just the switching that's fast



- Variants with and without fastswitching electronics as 3/2-way and 5/2-way valves
- Extremely short switching times with maximum repetition accuracy and outstanding service life
- Directly actuated poppet valve with degree of protection IP65

#### Advantages for designers



# • Very high cycle rates

- Extremely short cycle times
- Maximum repetition accuracy
- Suitable for vacuum thanks to
- directly actuated poppet valve (time limited)
- Flexible design principle
- Direct activation via standard PLC possible
- Direct mounting in the application with IP65 protection

#### Advantages for purchasers



- Everything from a single source
- Low ordering costs
- No additional mounting components
- No costs for additional power outputs
- Use of standard PLCs
- Increased system productivity

#### Advantages for installation



- Easy installation
- Direct pneumatic connection via integrated tubing connections
- Reduced assembly costs with pre-assembled cables
- No additional protection required thanks to IP65

### Key features

#### Fast and precise – sturdy and economical

High performance, process stability and extremely easy handling

Fast-switching valves MH increase switching frequencies and improve process and part quality with their excellent repetition accuracy. Integrated: the fast-switching electronics

- All 3/2- and 5/2-way valves are available with built-in fast-switching electronics
- This enables constant dynamic response independent of temperature or supply voltage fluctuations
- With Festo plug & work, installation is easy, and no additional electronics or pneumatics know-how is necessary

Optimised: systems and processes

- On-site assembly thanks to IP65 not sensitive to dust and humidity
- Direct activation with 24 V DC/1 A use of PLC standard outputs
- With an extremely long service life of 500 million cycles, and continuous three-shift operation with no need for maintenance, optimum efficiency comes as standard!

#### Key features

- Repetition accuracy ≤ 0.2 ms for accurate dispensing/bonding, for example
- Switching time ≤ 3 ms for short cycle times and very quick response characteristics
- 10 mm width for compact assembly
- Choice of connections as an individual valve, semi in-line or sub-base variant, enabling need-optimised installation
- Degree of protection IP65 enables direct mounting in the application without additional safeguarding
- Easy installation via direct activation from the standard PLC with 24 V DC/1 A

#### Small and fast – a good combination

The switching time plays a crucial role with small cylinder volumes, especially with short-stroke cylinders. In the adjacent example, the combination with a fast-switching valve is 30% faster. In concrete terms, this means that the cylinder controlled using the fastswitching valve is already in the end position before the cylinder with the universal valve even begins to move. This equates to a significant increase in both the efficiency and the economy of the system, especially when taking into account that the two valves have comparable space requirements and weight, and the fast-switching valve uses less air and lasts 10 times as long!

# Fast valves and an optimised control chain – two guarantees for success

To generate speed in pneumatics, the valve and cylinder must be perfectly matched. The correct combination can result in a 30% increase in efficiency. Cylinders with small diameters and short strokes need fast valves!

# Length means losses – focus on tubing

In terms of pneumatic efficiency, short tubing is a key factor. Reducing the tubing length from 1 m to 0.5 m, for example, improves the max. possible flow rate by 20%. A tube length greater than 2 m results in losses of up to 50%. In this case it is recommended to use tubing of the next size up.

# Small and nearby – the clever alternative

Short tubing with a small diameter is ideal for mounting valves close to the cylinder. The small and light fast-switching valves are suitable for direct mounting in the application, thanks also to their degree of protection IP65. By using them together with smaller and lighter fittings, the weight is reduced, too. This results in particular in an improvement in the efficiency of moving systems.

# Product range overview

Function Circuit symbol		Design	Switching time [ms]				Operating voltage	→ Page/
			Off <sup>2)</sup>	On <sup>2)</sup>	Off	On	[V DC]	Internet
3/2-way valve <sup>1)</sup> Standard nominal flow rate 100 l/min								
	2	Individual valve	2	1.7	3.5	7	24	9
		Semi-in-line valve	2	1.7	3.5	7	24	22
	1 3	Sub-base valve	2	1.7	3.5	7	24	40
	21							

Can be used as a 2/2-way valve by sealing port 3 or 33
 With integrated fast-switching electronics

	Function	Circuit symbol Design		Switching time [ms] Off On		Operating voltage [V DC]	→ Page/ Internet
5/2-way valve Standard nominal flow rate 100 l/min							
	14	4 2	Individual valve	1.7	1.9	24	16
			Semi-in-line valve	1.7	1.9	24	31
			Sub-base valve	1.7	1.9	24	49

Design		Individual valve		Semi-in-line valv	/e	Sub-base valve	
Valve function		3/2-way	5/2-way	3/2-way	5/2-way	3/2-way	5/2-way
Plug vanes							
	Direct mounting			-	-	-	-
	Individual sub-base	-	-				
	Manifold assembly	-	-				
Moulded-in cable							
	Direct mounting	•	•	-	-	-	-
	Individual sub-base	-	-	-	-		
	Manifold assembly	-	-	-	_	•	•

### Solenoid valves MH3, fast-switching valves

# Product range overview

Function Circuit symbol		Design	Switching time [ms]				Operating voltage	→ Page/
			Off <sup>2)</sup>	On <sup>2)</sup>	Off	On	[V DC]	Internet
3/2-way valve <sup>1)</sup>	Standard nominal flo	w rate 200 l/min						
	2	Individual valve	2.8	2.3	4.5	8.3	24	58
		Semi-in-line valve	2.8	2.3	4.5	8.3	24	66
	1 3	Sub-base valve	2.8	2.3	4.5	8.3	24	75

Can be used as a 2/2-way valve by sealing port 3 or 33
 With integrated fast-switching electronics

Mounting options				
Design		Individual valve	Semi-in-line valve	Sub-base valve
Plug vanes				
	Direct mounting		-	-
	Individual sub-base	-		
	Manifold assembly	-	•	•
Moulded-in cable				
//	Direct mounting		-	-
	Individual sub-base	-		•
	Manifold assembly	-	•	•

# Product range overview

Function Circuit symbol		Design		g time [ms]			Operating voltage	→ Page/
			Off <sup>2)</sup>	On <sup>2)</sup>	Off	On	[V DC]	Internet
3/2-way valve <sup>1)</sup>	Standard nominal flo	w rate 400 l/min						
	2	Individual valve	3.5	3.5	5	10.5	24	85
		Semi-in-line valve	3.5	3.5	5	10.5	24	92
	1 3	Sub-base valve	3.5	3.5	5	10.5	24	101
	21							

Can be used as a 2/2-way valve by sealing port 3 or 33
 With integrated fast-switching electronics

Mounting options		Individual valve		
Design		Individual valve	Semi-in-line valve	Sub-base valve
Plug vanes				
	Direct mounting	•	-	-
	Individual sub-base	-		•
	Manifold assembly	-	•	•
Moulded-in cable				
	Direct mounting		-	-
d	Individual sub-base	-		•
	Manifold assembly	-	•	•

# Type codes

001	Series				
MHA2	Solenoid valve MHA2				
MHE2	Solenoid valve MHE2				
MHP2	Solenoid valve MHP2				
MHA3	Solenoid valve MHA3				
MHE3	Solenoid valve MHE3				
MHP3	Solenoid valve MHP3				
MHA4	Solenoid valve MHA4				
MHE4	Solenoid valve MHE4				
MHP4	Solenoid valve MHP4				
002	Drive system				
М	Solenoid, switching				
003	Nominal operating voltage				
1	24 V DC				
004	Manual override				
Н	Non-detenting				
005	Valve function				
3/2	3/2-way valve				
5/2	5/2-way valve				

006	Normal position				
	5/2-way valve				
G	Closed				
0	Open				
007	Pneumatic connection				
2	Sub-base, nominal width 2 mm				
3	Sub-base, nominal width 3 mm				
4	Sub-base, nominal width 4 mm				
1/8	Thread G1/8				
1/4	Thread G1/4				
M5	Thread M5				
M7	Thread M7				
QS-4	Push-in connector, 4 mm				
QS-6	Push-in connector 6 mm				
QS-8	Push-in connector 8 mm				
008	Electrical connection				
	Plug tabs				
К	Moulded cable, 2.5 m long				

# Peripherals overview – Individual valve, 3/2-way valve

### Connection with plug vanes - Connection with moulded-in cable



Desig	Designation Type		Description	→ Page/Internet
[1]	Individual valve	MHE2	With plug vanes	14
[2]	Individual valve	MHE2K	With moulded-in cable, IP55	14
[3]	Connecting cable	NEBV	PUR cable, signal status indication with LED, plug M8x1 3-pin, IP65	15
[4]	Connecting cable	NEBV	PUR cable, signal status indication with LED, IP65	15
[5]	Plug socket with cable	KMYZ-4	PVC cable, without signal status indication, IP50	15
[6]	Adapter	VAVE-C8	For connecting the valves via connecting cable M8 3-pin or 4-pin, IP65	15
[7]	Mounting bracket	MHE2-BG-L	For wall mounting	15
[8]	Push-in fittings	QS	For connecting tubing with standard O.D.	15
[9]	Silencer	UC	For mounting in exhaust ports	15

### Solenoid valves MHE2, fast-switching valves

### Datasheet - Individual valve, 3/2-way valve







. . . . . .

Temperature range
 -5 ... +60 °C



#### General technical data

Scherat technicat auta		
Valve function		3/2 way, single solenoid <sup>1)</sup>
Design		Pressure relief poppet valve
Overlap		Negative overlap
Sealing principle		Soft
Reset method		Mechanical spring
Actuation type		Electrical
Type of control		Direct
Flow direction		Reversible with restrictions <sup>2)</sup>
Exhaust air function		Can be throttled
Manual override		Non-detenting
Mounting position		Any
Width	[mm]	10
Grid dimension	[mm]	14
Note on grid dimension		Minimum distance between the valves is 4 mm
Nominal width	[mm]	2
Standard nominal flow rate	[l/min]	100
Type of mounting		Via through-hole
Pneumatic connection		Connecting thread M7
		Push-in connector for tubing O.D. 4 mm
Product weight	[g]	60

1) Can be used as a 2/2-way valve by sealing port 3 or 33

2) Slight leakage can occur in the pressure range -0.8 bar to +0.5 bar.

# Datasheet – Individual valve, 3/2-way valve

#### Operating and environmental conditions

			With fast-switching electronics	Without fast-switching electronics		
Operating medium		·	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on the operating/pilot medium		Lubricated operation possible (in which cas	e lubricated operation will always be required)			
Operating pressure		[MPa]	-0.09 +0.8			
		[bar]	-0.9 +8			
		[psi]	-13.05 +116			
	Reversible	[MPa]	-0.09 +0.1			
		[bar]	-0.9 +1			
		[psi]	-13.05 +14.5			
Ambient temperature		[°C]	-5 +60			
Temperature of medium		[°C]	-5 +60			
Restricted ambient temperature and temperature of the second seco	medium		As a function of the switching frequency	-		
			(see graph)			
Corrosion resistance class CRC <sup>1)</sup>			2	2		
CE marking (see declaration of conformity) <sup>3)</sup>			To EU EMC Directive <sup>2</sup> )	-		
			To EU RoHS Directive	-		
UKCA marking (see declaration of conformity) <sup>3)</sup>			To UK EMC regulations	-		
			To UK RoHS regulations	-		
Certification			c UL us - Recognized (OL)	c UL us - Recognized (OL)		
			RCM	-		
Cleanroom class			Class 6 to ISO 14644-1	•		
Shock resistance			Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27			
Vibration resistant			Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6			

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) More information www.festo.com/catalogue/...  $\rightarrow$  Support/Downloads.

#### Electrical data

			With fast-switching electronics	Without fast-switching electronics
Electrical connection			Plug, 2-pin or cable	
Operating voltage		[V DC]	24	
Permissible voltage fluctuations			±10%	
Power consumption		[W]	5 for approx. 3 ms (high-current phase, inrush current 1 A)	2.88
		[W]	1.25 (low-current phase)	-
Reverse polarity protection			Bipolar	-
Duty cycle		[%]	100	100
Additional functions			Spark arresting	-
			Holding current reduction	-
			Protective circuit	-
Degree of protection to EN 60529	Electrical connection: plug, 2-pin		IP65	IP65
	Electrical connection: cable		IP55	IP55

#### Switching times and frequencies

			With fast-switching electronics	Without fast-switching electronics
Switching time	On	[ms]	1.7	7
	Off	[ms]	2	3.5
Tolerance for switching time	On	[%]	+1030	-
	Off	[%]	+1030	-
Switching time variation from 1 Hz upwards		[ms]	0.2	-
Maximum switching frequency		[Hz]	330	130

### Datasheet – Individual valve, 3/2-way valve

Materials	
Housing	Die-cast zinc, coated
Cable sheath	PUR
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L



#### Restricted ambient temperature and temperature of medium as a function of switching frequency

Current curve for valves with fast-switching electronics (MHE2-MS1H)



Internal current in the coil

External current in the supply line

- [1] Valve manifold assembly, 6 valves, unpressurised
- [2] Valve manifold assembly, 6 valves, through-flow, 0.6 MPa
- [3] Individual valve, unpressurised
- [4] Individual valve, through-flow, 0.6 MPa

- [1] Capacitor charging
- Controlled coil current 1 A [2]
- [3] Holding current reduction
- Controlled holding current 0.5 A [4]



Ē







Туре	B1	B2	B3	D1	D2 Ø	D3 Ø	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8	L9
MHE23/0M7	10	-	-	M7	-	3.4	34	-	31	21	73	32	16.5	16	7	12	10.5	16.5	0.5
MHE23/0QS-4	10	-	-	-	4	3.4	34	40.4	31	21	73	32	16.5	16	7	12	10.5	16.5	0.5
MHE2-BG-L	20	10	2	4.5	-	-	55	92.3	-	-	40	25	7.5	-	-	-	-	-	-

# Solenoid valves MHE2, fast-switching valves

# Datasheet – Individual valve, 3/2-way valve

Ordering data						
					Part no.	Туре
Valves						
	Electrical connection:	With fast-switching	Pneumatic connection: thread	Normally open	196151	MHE2-MS1H-3/20-M7
	plug, 2-pin	electronics, switching	M7	Normally closed	196131	MHE2-MS1H-3/2G-M7
		time 2 ms	Pneumatic connection: push-in	Normally open	196155	MHE2-MS1H-3/20-QS-4
O L			connector for tubing O.D. 4 mm	Normally closed	196135	MHE2-MS1H-3/2G-QS-4
		Without fast-switching	ut fast-switching Pneumatic connection: thread		196150	MHE2-M1H-3/20-M7
	electronics, switching		M7	Normally closed	196130	MHE2-M1H-3/2G-M7
	time 7 ms	Pneumatic connection: push-in	Normally open	196154	MHE2-M1H-3/20-QS-4	
			connector for tubing O.D. 4 mm	Normally closed	196134	MHE2-M1H-3/2G-QS-4
$\sim$	Electrical connection:	With fast-switching	Pneumatic connection: thread	Normally open	196153	MHE2-MS1H-3/20-M7-K
	cable	electronics, switching	M7	Normally closed	196133	MHE2-MS1H-3/2G-M7-K
A B B B		time 2 ms	Pneumatic connection: push-in	Normally open	196157	MHE2-MS1H-3/20-QS-4-K
El Ball			connector for tubing O.D. 4 mm	Normally closed	196137	MHE2-MS1H-3/2G-QS-4-K
		Without fast-switching	Pneumatic connection: thread	Normally open	196152	MHE2-M1H-3/20-M7-K
		electronics, switching	M7	Normally closed	196132	MHE2-M1H-3/2G-M7-K
		time 7 ms	Pneumatic connection: push-in	Normally open	196156	MHE2-M1H-3/20-QS-4-K
			connector for tubing O.D. 4 mm	Normally closed	196136	MHE2-M1H-3/2G-QS-4-K

# Datasheet – Individual valve, 3/2-way valve

Ordering data					Part no.	Туре
onnecting cable (for	valves with 2-pin plug)					Datasheets $\rightarrow$ Internet: net
	2-pin socket,	PUR cable,	Signal status indica-	Length 2.5 m	8047671	NEBV-Z4WA2L-P-E-2.5-N-LE2-S1
	Open cable end 2-wire	degree of protection	tion with LED	Length 5 m	8047672	NEBV-Z4WA2L-P-E-5-N-LE2-S1
		IP65		Length 10 m	8047670	NEBV-Z4WA2L-P-E-10-N-LE2-S1
and a second sec		PVC cable,	Without signal status	Length 0.5 m	193690	КМҮZ-4-24-0.5-В
		degree of protection IP40	indication	Length 2.5 m	193691	КМҮZ-4-24-2.5-В
	2-pin socket, plug	PUR cable,	Signal status indica-	Length 0.5 m	8047673	NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1
STA IN	M8x1 3-pin	degree of protection IP65	tion with LED	Length 2.5 m	8047674	NEBV-Z4WA2L-P-E-2.5-N-M8G3-S1
Adapter (for valves w	ith 2-pin plug) 2-pin socket	Signal status indica-	Plug M8, 3-pin		571686	VAVE-C8-1R8
		tion with LED	Plug M8, 4-pin		573194	VAVE-C8-1R1
Wall mounting						
	Mounting bracket				196165	MHE2-BG-L
×						
Silencer				1		Datasheets → Internet:
$\sim$	Push-in sleeve with O.D.			1 pieces	165006	UC-QS-4H
	With M7 threaded conne	ection		1 pieces	161418	UC-M7
				50 piece	534218	UC-M7-50
Push-in fitting			1	1		Datasheets → Internet:
s)	Male thread M7 with inte	ernal hex for tubing O.D.	4 mm	Pack of 10	153319	QSM-M7-4-I
				100 units	133006	QSM-M7-4-I-100
			6 mm	Pack of 10	153321	QSM-M7-6-1
	Male thread M7 with ext		4 mm	Pack of 10	186352	QSML-M7-4
	L-fitting rotatable throug	h 360º, for tubing O.D.		100 units	130773	QSML-M7-4-100
			6 mm	Pack of 10	186353	QSML-M7-6

# Peripherals overview – Individual valve, 5/2-way valve

### Connection with plug vanes – Connection with moulded-in cable



Desigr	nation	Туре	Description	→ Page/Internet
[1]	Individual valve	MHE2M7	With plug vanes and connection M7	21
[2]	Individual valve	MHE2QS-4	With plug vanes and push-in connector for standard O.D. tubing	21
[3]	Individual valve	MHE2K	With moulded-in cable, IP55	21
[4]	Connecting cable	NEBV	PUR cable, signal status indication with LED, plug M8x1 3-pin, IP65	21
[5]	Connecting cable	NEBV	PUR cable, signal status indication with LED, IP65	21
[6]	Plug socket with cable	KMYZ-4	PVC cable, without signal status indication, IP50	21
[7]	Adapter	VAVE-C8	For connecting the valves via connecting cable M8 3-pin or 4-pin, IP65	21
[8]	Mounting bracket	MHE2-BG-L	For wall mounting	21
[9]	Retaining screws	-	Hole diameter: see dimensional drawing	-
[10]	Silencer	UC	For mounting in exhaust ports	21
[11]	Push-in fittings	QS	For connecting tubing with standard O.D.	21

# Datasheet – Individual valve, 5/2-way valve







Temperature range
 −5 ... +60 °C



#### General technical data

General technical data		
Valve function		5/2-way, single solenoid
Design		Pressure relief poppet valve
Overlap		Negative overlap
Sealing principle		Soft
Reset method		Mechanical spring
Actuation type		Electrical
Type of control		Direct
Flow direction		Not reversible
Exhaust air function		Can be throttled
Manual override		Non-detenting
Mounting position		Any
Width	[mm]	10
Grid dimension	[mm]	14
Note on grid dimension		Minimum distance between the valves is 4 mm
Nominal width	[mm]	2
Standard nominal flow rate	[l/min]	90
Type of mounting		Via through-hole
Pneumatic connection		Connecting thread M7
		Push-in connector for tubing O.D. 4 mm
Max. tightening torque of fitting	[Nm]	2
Product weight	[g]	70

# Datasheet - Individual valve, 5/2-way valve

### Operating and environmental conditions

Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa]	-0.09 +0.8
	[bar]	-0.9 +8
	[psi]	-13.05 +116
Ambient temperature	[°C]	-5 +60
Temperature of medium	[°C]	-5 +60
Restricted ambient temperature and temperature of medium		As a function of the switching frequency (see graph)
Corrosion resistance class CRC <sup>1)</sup>		2
CE marking (see declaration of conformity) <sup>3)</sup>		To EU EMC Directive <sup>2</sup> )
		To EU RoHS Directive
UKCA marking (see declaration of conformity) <sup>3)</sup>		To UK EMC regulations
		To UK RoHS regulations
Certification		c UL us - Recognized (OL)
		RCM
Cleanroom class		Class 6 to ISO 14644-1
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) More information www.festo.com/catalogue/...  $\rightarrow$  Support/Downloads.

Electrical data				
Electrical connection			Plug, 2-pin	Cable
Operating voltage		[V DC]	24	
Permissible voltage fluctuat	ions	[%]	±10	
Power consumption	Low-current phase	[W]	1.625	
	High-current phase	[W]	6.5	
Reverse polarity protection			Bipolar	
Duty cycle		[%]	100	
Additional functions			Spark arresting	
			Holding current reduction	
			Protective circuit	
Degree of protection to EN 6	0529		IP65	IP55

#### Switching times and frequencies

Switching time	On	[ms]	1.9
	Off	[ms]	1.7
Tolerance for switching time	On	[%]	+1030
	Off	[%]	+1030
Switching time variation from 1 Hz upwards		[ms]	0.2
Maximum switching frequency		[Hz]	300

#### Materials

Housing	Die-cast zinc, coated
Cable sheath	PUR
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

T

# Datasheet – Individual valve, 5/2-way valve

### Restricted ambient temperature and temperature of medium as a function of switching frequency



Current curve for valves with fast-switching electronics (MHE2-MS1H)



Internal current in the coil
 External current in the supply line

[1] Capacitor charging

S www.festo.com/catalogue/...

- [2] Controlled coil current 1 A
- [3] Holding current reduction
- [4] Controlled holding current 0.5 A

- Valve manifold assembly, 6 valves, unpressurised
   Valve manifold assembly,
  - 6 valves, through-flow, 0.6 MPa[3] Individual valve, unpressurised
  - [4] Individual valve, through-flow,0.6 MPa

### Datasheet - Individual valve, 5/2-way valve





Туре	B1	B2	B3	D1	D2 Ø	D3 Ø	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
MHE25/2-M7	10	-	-	M7	-	3.4	34	-	31	21	84	43	16.3	25	9	11.5	10.5	16.5	0.5	11
MHE25/2-QS-4	10	-	-	-	4	3.4	34	40.4	31	21	84	43	16.3	25	9	11.5	10.5	16.5	0.5	11
MHE2-BG-L	20	10	2	4.5	-	-	55	92.3	-	-	40	25	7.5	-	-	-	-	-	-	-

 $\bigcirc \bigcirc$ 

# Datasheet – Individual valve, 5/2-way valve

Ordering data					1	1-
				-	Part no.	Туре
Valves	Electrical connection:	With fast-switching	Pneumatic connection:	thread M7	525113	MHE2-MS1H-5/2-M7
	plug, 2-pin	electronics, switching	Pneumatic connection:		525115	MHE2-MS1H-5/2-QS-4
	F	time 2 ms	tubing O.D. 4 mm		,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	militz mozili 5/2 45 4
	Electrical connection:	With fast-switching	Pneumatic connection:	thread M7	525115	MHE2-MS1H-5/2-M7-K
and a second	cable	electronics, switching time 2 ms	Pneumatic connections tubing O.D. 4 mm	push-in connector for	525119	MHE2-MS1H-5/2-QS-4-K
Connecting cable (for	valves with 2-pin plug)					Datachasta > Internet. poly
Connecting cable (for	2-pin socket,	PUR cable, degree of	Signal status indica-	Length 2.5 m	8047671	Datasheets → Internet: neb
	Open cable end 2-wire	protection IP65	tion with LED	Length 5 m	8047672	NEBV-Z4WA2L-P-E-5-N-LE2-S1
				Length 10 m	8047670	NEBV-Z4WA2L-P-E-10-N-LE2-S1
ell en la companya de		PVC cable, degree of	Without signal status	Length 0.5 m	193690	KMYZ-4-24-0.5-B
		protection IP40	indication	Length 2.5 m	193691	KMYZ-4-24-2.5-B
$\Psi$						
Ŕ	2-pin socket, plug	PUR cable, degree of	Signal status indica-	Length 0.5 m	8047673	NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1
C.S.	M8x1 3-pin	protection IP65	tion with LED	Length 2.5 m	8047674	NEBV-Z4WA2L-P-E-2.5-N-M8G3-S1
Adapter (for valves wi		Circul status in disc			574/0/	
	2-pin socket	Signal status indica- tion with LED	Plug M8, 3-pin Plug M8, 4-pin		571686 573194	VAVE-C8-1R8 VAVE-C8-1R1
					575174	VAVE-CO-INI
Wall mounting						
	Mounting bracket				196165	MHE2-BG-L
Silencer						Datashaata N Internatiu
	Push-in sleeve with O.D.	4 mm		1 pieces	165006	Datasheets → Internet: u
	With M7 threaded conne			1 pieces	161418	UC-M7
				50 piece	534218	UC-M7-50
	1			1		
Push-in fitting						Datasheets → Internet: q
	Male thread M7 with int	ernal hex for tubing O.D.	4 mm	Pack of 10	153319	QSM-M7-4-I
		0.000		100 units	133006	QSM-M7-4-I-100
-			6 mm	Pack of 10	153321	QSM-M7-6-1
	Male thread M7 with ext	ernal hex, push-in	4 mm	Pack of 10	186352	QSML-M7-4
	L-fitting rotatable 360 <sup>o</sup> ,			100 units	130773	QSML-M7-4-100
		-	6 mm	Pack of 10	186353	QSML-M7-6
				100 units	130774	QSML-M7-6-100

# Peripherals overview – Semi in-line valve, 3/2-way valve

### Connection via plug vanes



Desig	nation	Туре	Description	→ Page/Internet
[1]	Semi-in-line valve	MHP2	With plug vanes	29
[2]	Connecting cable	NEBV	PUR cable, signal status indication with LED, plug M8x1 3-pin, IP65	29
[3]	Plug socket with cable	KMYZ-4	PVC cable, without signal status indication, IP50	29
[4]	Connecting cable	NEBV	PUR cable, signal status indication with LED, IP65	29
[5]	Adapter	VAVE-C8	For connecting the valves via connecting cable M8 3-pin or 4-pin, IP65	29
[6]	Push-in fittings	QS	For connecting tubing with standard O.D.	30
[7]	Cover plate	MHAP2-BP-3	For sealing vacant positions	29
[8]	Inscription labels	MH-BZ-80X	For identifying the valves	30
[9]	Blanking plug	В	For sealing unused ports	30
[10]	DIN rail mounting	MHAP2-BG-NRH-35	For mounting the manifold block on DIN rails to EN 60715	29
[11]	Silencer	UC	For mounting in exhaust ports	30
[12]	Individual sub-base	MHA2-AS-3-M5	For semi in-line valve, the individual sub-base is also used for the sub-base valve; here the outlet port must be sealed with a blanking plug	29
	Manifold block	MHP2-PR3	For semi in-line valves	29

### Solenoid valves MHP2, fast-switching valves

# Datasheet – Semi in-line valve, 3/2-way valve







#### General technical data

ocherat teenmeat aata			
Valve function		3/2	<sup>/</sup> 2 way, single solenoid <sup>1)</sup>
Design		Pre	essure relief poppet valve
Overlap		Ne	egative overlap
Sealing principle		Sot	oft
Reset method		Me	echanical spring
Actuation type		Ele	ectrical
Type of control		Dir	rect
Flow direction		Rev	eversible with restrictions <sup>2)</sup>
Exhaust air function		Car	an be throttled
Manual override		No	on-detenting
Mounting position		Any	лу
Width	[mn	ı] 10	)
Grid dimension	(mn	ı] 14	4
Note on grid dimension		Mir	inimum distance between the valves is 4 mm
Nominal width	[mn	ı] 2	
Standard nominal flow rate	[l/m	in] 10	00
Type of mounting		On	n PR rail
Pneumatic connection	2	Cor	onnecting thread M5
	1, 3, 11, 33	Su	ıb-base
Product weight	[g]	60	)

Can be used as a 2/2-way valve by sealing port 3 or 33.
 Slight leakage can occur in the pressure range -0.8 bar to +0.5 bar.

#### Operating and environmental conditions

			With fast-switching electronics	Without fast-switching electronics						
Operating medium			Compressed air to ISO 8573-1:2010 [2	7:4:4]						
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)							
Operating pressure		[MPa]	-0.09 +0.8							
		[bar]	-0.9 +8							
		[psi]	-13.05 +116							
	Reversible	[MPa]	-0.09 +0.1							
		[bar]	-0.9 +1							
		[psi]	-13.05 +14.5							
Ambient temperature		[°C]	-5 +40							
Temperature of medium		[°C]	-5 +40							
Restricted ambient temperature and temperature of	of medium		As a function of the switching frequency (see graph)							
Corrosion resistance class CRC <sup>1)</sup>			2							
CE marking (see declaration of conformity) <sup>3)</sup>			To EU EMC Directive <sup>2</sup> )	-						
			To EU RoHS Directive	-						
UKCA marking (see declaration of conformity) <sup>3)</sup>			To UK EMC regulations	-						
			To UK RoHS regulations	-						
Certification			c UL us - Recognized (OL)	c UL us - Recognized (OL)						
			RCM	-						
Cleanroom class			Class 6 to ISO 14644-1							
Shock resistance			Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27							
Vibration resistant			Transport application test with severit	y level 2 to FN 942017-4 and EN 60068-2-6						

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary. 3) More information www.festo.com/catalogue/... → Support/Downloads.

Electrical data			
		With fast-switching electronics	Without fast-switching electronics
Electrical connection		Plug, 2-pin	
Operating voltage	[V DC]	24	
Permissible voltage fluctuations	[%]	±10	
Power consumption	[W]	5 for approx. 3 ms (high-current phase, inrush current 1 A)	2.88
	[W]	1.25 (low-current phase)	-
Reverse polarity protection		Bipolar	-
Duty cycle	[%]	100	100
Additional functions		Spark arresting	-
		Holding current reduction	-
		Protective circuit	-
Degree of protection to EN 60529		IP65	IP65

#### Switching times and frequencies

Switching times and nequencies				
			With fast-switching electronics	Without fast-switching electronics
Switching time	On	[ms]	1.7	7
	Off	[ms]	2	3.5
Tolerance for switching time	On	[%]	+1030	-
	Off	[%]	+1030	-
Switching time variation from 1 Hz upwards		[ms]	0.2	-
Maximum switching frequency		[Hz]	330	130

Materials

Housing	Die-cast zinc, coated
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

I

### Restricted ambient temperature and temperature of medium as a function of switching frequency



#### Current curve for valves with fast-switching electronics (MHP2-MS1H)



---- Internal current in the coil

External current in the supply line

- Valve manifold assembly, 6 valves, unpressurised
   Valve manifold assembly,
- 6 valves, through-flow, 0.6 MPa[3] Individual valve, unpressurised
- [4] Individual valve, through-flow, 0.6 MPa

- [1] Capacitor charging
- [2] Controlled coil current 1 A
- [3] Holding current reduction
- [4] Controlled holding current 0.5 A



#### Dimensions

Download CAD data → <u>www.festo.com</u>





Туре	B1	B2	B3	B4	B5	D1	D2 Ø	D3 Ø	D4 Ø	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8	L9	T1
MHA2-AS-3-M5	21	9	3.5	10	36.6	M5	3.4	6	3.3	18.3	12.9	5	57.4	57.4	31.4	12.6	37.7	12.6	4.3	16.3	73	16.5	6.8
MHAP2-BG-NRH-35	49.1	67.6	-	-	-	-	-	-	-	10.7	28.3	10	20	-	*	-	6.5	-	-	-	-	-	-

See dimensional table for the manifold block used

#### Dimensions

Download CAD data → <u>www.festo.com</u>



- 📲 - Note

Valve types 3/2G and 3/2O must not be mixed on one manifold block.

Ordering data					Part no.	Туре
Valves						
	With fast-switching electronics	Switching time on	Normally open		196143	MHP2-MS1H-3/20-M5
		1.7 ms	Normally closed		196123	MHP2-MS1H-3/2G-M5
	Without fast-switching electronics	Switching time on	Normally open		196142	MHP2-M1H-3/2O-M5
		7 ms	Normally closed		196122	MHP2-M1H-3/2G-M5
Manifold rail						
	Individual sub-base <sup>1)</sup>			1 valve position	197438	MHA2-AS-3-M5
	Pneumatic connection: M5 thread				177450	
	Manifold block			2 valve positions	197442	MHP2-PR2-3
	Pneumatic connection: thread M7			4 valve positions	197443	MHP2-PR4-3
				6 valve positions	197444	MHP2-PR6-3
				8 valve positions	197445	MHP2-PR8-3
				10 valve positions	197446	MHP2-PR10-3
Cover plate						
	Vacant valve positions must be sea	led with a cover plate	e		197470	MHAP2-BP-3
Connecting cable						Datasheets → Internet: ne
	2-pin socket,	PUR cable, degree	Signal status indica-	Length 2.5 m	8047671	NEBV-Z4WA2L-P-E-2.5-N-LE2-S1
	Open cable end 2-wire	of protection IP65	tion with LED		8047672	
/	open cable end 2-wire	of protection if 05		Length 5 m		NEBV-Z4WA2L-P-E-5-N-LE2-S1
		DVG LL L	14001	Length 10 m	8047670	NEBV-Z4WA2L-P-E-10-N-LE2-S1
L.		PVC cable, degree	Without signal	Length 0.5 m	193690	KMYZ-4-24-0.5-B
		of protection IP40	status indication	Length 2.5 m	193691	КМҮZ-4-24-2.5-В
<u>J</u>	2-pin socket, plug M8x1 3-pin	PUR cable, degree of protection IP65	Signal status indica- tion with LED	Length 0.5 m Length 2.5 m	8047673 8047674	NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1 NEBV-Z4WA2L-P-E-2.5-N-M8G3-S1
E THE ME THE						
Adapter						
	2-pin socket	Signal status indi-	Plug M8, 3-pin		571686	VAVE-C8-1R8
		cation with LED	Plug M8, 4-pin		573194	VAVE-C8-1R1
DIN rail mounting						
	For 3/2-way solenoid valves				525053	MHAP2-BG-NRH-35
DIN rail						
	To EN 60715			2 m	35430	NRH-35-2000

1) Seal ports 2 and 4 on the individual sub-base with blanking plugs. These ports on the individual sub-base have no function when using semi in-line valves.

# Solenoid valves MHP2, fast-switching valves

# Datasheet – Semi in-line valve, 3/2-way valve

				Part no.	Туре
Silencer					Datasheets → Internet: u
	With threaded connection	M5	1 piece	165003	UC-M5
			50 piece	534217	UC-M5-50
		M7	1 piece	161418	UC-M7
			50 piece	534218	UC-M7-50
Push-in fitting					Datasheets → Internet: 0
S)	Male thread M5 with internal hex for tubing O.D.	4 mm	Pack of 10	153315	QSM-M5-4-I
Survey and the second s		6 mm	Pack of 10	153317	QSM-M5-6-I
	Male thread M7 with internal hex for tubing O.D.	4 mm	Pack of 10	153319	QSM-M7-4-I
			100 units	133006	QSM-M7-4-I-100
		6 mm	Pack of 10	153321	QSM-M7-6-I
	Male thread M5 with external hex, push-in L-fitting	4 mm	Pack of 10	153333	QSML-M5-4
	rotatable 360°, for tubing O.D.		100 units	130771	QSML-M5-4-100
		6 mm	Pack of 10	153335	QSML-M5-6
			100 units	130772	QSML-M5-6-100
	Male thread M7 with external hex, push-in L-fitting	4 mm	Pack of 10	186352	QSML-M7-4
	rotatable 360⁰, for tubing O.D.		100 units	130773	QSML-M7-4-100
		6 mm	Pack of 10	186353	QSML-M7-6
			100 units	130774	QSML-M7-6-100
Blanking plug					1
STILL ST	For M5 thread		Pack of 10	3843	B-M5
O	For M7 thread		Pack of 10	174309	B-M7
nscription label					
	For solenoid valve		80 pieces in a frame	197259	MH-BZ-80X

# Peripherals overview – Semi in-line valve, 5/2-way valve

Connection via plug vanes



Desig	nation	Туре	Description	→ Page/Internet
[1]	Semi-in-line valve	MHP2	With plug vanes	38
[2]	Connecting cable	NEBV	PUR cable, signal status indication with LED, plug M8x1 3-pin, IP65	38
[3]	Plug socket with cable	KMYZ-4	PVC cable, without signal status indication, IP50	38
[4]	Connecting cable	NEBV	PUR cable, signal status indication with LED, IP65	38
[5]	Adapter	VAVE-C8	For connecting the valves via connecting cable M8 3-pin or 4-pin, IP65	38
[6]	Push-in fittings	QS	For connecting tubing with standard O.D.	39
[7]	Cover plate	MHAP2-BP-5	For sealing vacant positions	38
[8]	Inscription labels	MH-BZ-80X	For identifying the valves	39
[9]	Blanking plug	В	For sealing unused ports	39
[10]	Manifold block	MHP2-PR5	For semi in-line valves	38
[11]	DIN rail mounting	CPV10/14-VI-BG-NRH-35	For mounting the manifold block on DIN rails to EN 60715	38
[12]	Silencer	UC	For mounting in exhaust ports	39
[13]	Individual sub-base	MHA2-AS-5-M5	For semi in-line valve, the individual sub-base is also used for sub-base valves and must be	38
			sealed with a blanking plug here	

### Solenoid valves MHP2, fast-switching valves

# Datasheet – Semi in-line valve, 5/2-way valves

Function





- **L** - Pressure -0.09 ... +0.8 MPa

- Temperature range -5 ... +40 °C



#### General technical data

Valve function		5/2-way, single solenoid							
Design		Pressure relief poppet valve							
Overlap		Negative overlap							
Sealing principle		Soft							
Reset method		Mechanical spring							
Actuation type		Electrical							
Type of control		Direct							
Flow direction		Not reversible							
Exhaust air function		Can be throttled							
Manual override		Non-detenting							
Mounting position		Any							
Width	[mm]	10							
Grid dimension	[mm]	14							
Note on grid dimension		Minimum distance between the valves is 4 mm							
Nominal width	[mm]	2							
Standard nominal flow rate	[l/min]	90							
Type of mounting		On PR rail							
Max. tightening torque for valve mounting [N		0.4							
Pneumatic connection	1, 3, 5	Sub-base							
	2,4	Connecting thread M5							
Max. tightening torque of fitting	[Nm]	1.5							
Product weight	[g]	70							

Operating and environmental conditions									
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]							
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)							
Operating pressure	[MPa]	-0.09 +0.8							
	[bar]	-0.9 +8							
	[psi]	-13.05 +116							
Ambient temperature	[°C]	-5 +40							
Temperature of medium	[°C]	-5 +40							
Restricted ambient temperature and temperature of medium		As a function of switching frequency							
Corrosion resistance class CRC <sup>1)</sup>		2							
CE marking (see declaration of conformity) <sup>3)</sup>		To EU EMC Directive <sup>2</sup> )							
		To EU RoHS Directive							
UKCA marking (see declaration of conformity) <sup>3)</sup>		To UK EMC regulations							
		To UK RoHS regulations							
Certification		c UL us - Recognized (OL)							
		RCM							
Cleanroom class		Class 6 to ISO 14644-1							
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27							
Vibration resistant		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6							

#### Operating and environmental conditions

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) More information www.festo.com/catalogue/...  $\rightarrow$  Support/Downloads.

#### Electrical data

Electrical connection			Plug, 2-pin						
Operating voltage [V DC]		[V DC]	24						
Permissible voltage fluctuations [%		[%]	±10						
Power consumption	Low-current phase	[W]	1.625						
	High-current phase	[W]	6.5						
Reverse polarity protection			Bipolar						
Duty cycle [%]		[%]	100						
Additional functions			Spark arresting						
			Holding current reduction						
			Protective circuit						
Degree of protection to EN 6	0529		IP65						

#### Switching times and frequencies

Switching time	On	[ms]	1.9
	Off	[ms]	1.7
Tolerance for switching time	On	[%]	+1030
	Off	[%]	+1030
Maximum switching frequency		[Hz]	300
Switching time variation from 1 Hz upwards		[ms]	0.2

#### Materials

Housing	Die-cast zinc, coated
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

#### Restricted ambient temperature and temperature of medium as a function of switching frequency



Current curve for valves with fast-switching electronics (MHP2-MS1H)



Internal current in the coil
 External current in the supply line

- Valve manifold assembly, 6 valves, unpressurised
   Valve manifold assembly,
- 6 valves, through-flow, 0.6 MPa[3] Individual valve, unpressurised
- [4] Individual valve, through-flow, 0.6 MPa

[1] Capacitor charging

- [2] Controlled coil current 1 A
- [3] Holding current reduction
- [4] Controlled holding current 0.5 A

34



- 📲 - Note

Ports 2 and 4 are not required with semi in-line valves.

#### Dimensions

Download CAD data → <u>www.festo.com</u>







#### [1] Plug pins

Туре	B1	B2	B3	D1	D2 Ø	D3 Ø	D4 Ø	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6	L7	L8	T1
MHA2-AS-5-M5	21	8.8	3.5	M5	3.4	6	3.3	22.2	13.9	6.9	6.2	45.2	68.4	42.4	12.6	48.7	13.9	10.3	11.7	84.5	10.7
# Datasheet – Semi in-line valve, 5/2-way valves

## Dimensions

Download CAD data → <u>www.festo.com</u>



59

42

87

70

115

98

143

126

L2

L3

31

14

## Solenoid valves MHP2, fast-switching valves

# Datasheet – Semi in-line valve, 5/2-way valve

Ordering data					Part no.	Туре
Valves					l	
Volves	With fast-switching electronics	Switching time on 1.9	9 ms		525105	MHP2-MS1H-5/2-M5
		1			1	
Manifold rail						
Contraction of the second seco	Individual sub-base <sup>1)</sup> Pneumatic connection: M5 threa	d		1 valve position	525120	MHA2-AS-5-M5
	Manifold block			2 valve positions	525122	MHP2-PR2-5
	Pneumatic connection 1, 3, 5: th	read M7		4 valve positions	525123	MHP2-PR4-5
				6 valve positions	525124	MHP2-PR6-5
				8 valve positions	525125	MHP2-PR8-5
				10 valve positions	525126	MHP2-PR10-5
Cover plate						
	Vacant valve positions must be s	ealed with a cover plate	2.		525132	MHAP2-BP-5
Connecting cable						Datasheets → Internet: nebv
	2-pin socket,	PUR cable, degree of	Signal status indica-	Length 2.5 m	8047671	NEBV-Z4WA2L-P-E-2.5-N-LE2-S1
	Open cable end 2-wire	protection IP65	tion with LED	Length 5 m	8047672	NEBV-Z4WA2L-P-E-5-N-LE2-S1
				Length 10 m	8047670	NEBV-Z4WA2L-P-E-10-N-LE2-S1
		PVC cable, degree of	Without signal sta-	Length 0.5 m	193690	KMYZ-4-24-0.5-B
		protection IP40	tus indication	Length 2.5 m	193691	КМҮZ-4-24-2.5-В
L A	2-pin socket, plug M8x1 3-pin	PUR cable, degree of		Length 0.5 m	8047673	NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1
Carlin Maria		protection IP65	tion with LED	Length 2.5 m	8047674	NEBV-Z4WA2L-P-E-2.5-N-M8G3-S1
Adapter		1				1
	2-pin socket	Signal status indica-	Plug M8, 3-pin		571686	VAVE-C8-1R8
		tion with LED	Plug M8, 4-pin		573194	VAVE-C8-1R1
DIN rail mounting	1					
	For 5/2-way solenoid valves				162556	CPV10/14-VI-BG-NRH-35
DIN rail	1			1		
	To EN 60715			2 m	35430	NRH-35-2000

1) Seal ports 2 and 4 on the individual sub-base with blanking plugs. These ports on the individual sub-base have no function when using semi in-line valves.

# Datasheet – Semi in-line valve, 5/2-way valve

Ordering data				Dart no	Time
				Part no.	Туре
Silencer					Datasheets → Internet: u
	with threaded connection	M5	1 piece	165003	UC-M5
			50 piece	534217	UC-M5-50
		M7	1 piece	161418	UC-M7
			50 piece	534218	UC-M7-50
Push-in fitting					Datasheets → Internet: q
	Male thread M5 with internal hex for tubing O.D.	4 mm	Pack of 10	153315	QSM-M5-4-I
		6 mm	Pack of 10	153317	QSM-M5-6-I
	Male thread M7 with internal hex for tubing O.D.	4 mm	Pack of 10	153319	QSM-M7-4-I
			100 units	133006	QSM-M7-4-I-100
		6 mm	Pack of 10	153321	QSM-M7-6-I
	Male thread M5 with external hex, push-in L-fitting rotatable 360°, for tubing O.D.	4 mm	Pack of 10	153333	QSML-M5-4
			100 units	130771	QSML-M5-4-100
		6 mm	Pack of 10	153335	QSML-M5-6
			100 units	130772	QSML-M5-6-100
	Male thread M7 with external hex, push-in L-fitting	4 mm	Pack of 10	186352	QSML-M7-4
	rotatable 360⁰, for tubing O.D.		100 units	130773	QSML-M7-4-100
		6 mm	Pack of 10	186353	QSML-M7-6
			100 units	130774	QSML-M7-6-100
				•	•
Blanking plug					
A	For M5 thread		Pack of 10	3843	B-M5
	For M7 thread		Pack of 10	174309	B-M7
Inscription label					
	For solenoid valve		80 pieces in a frame	197259	MH-BZ-80X

# Peripherals overview – Sub-base valve, 3/2-way valve

## Connection with 2-pin plug – Connection with moulded-in cable



Desigr	ation	Туре	Description	→ Page/Internet
[1]	Sub-base valve	MHA2	With plug vanes	47
[2]	Sub-base valve	MHA2K	With moulded-in cable, IP55	47
[3]	Connecting cable	NEBV	PUR cable, signal status indication with LED, plug M8x1 3-pin, IP65	47
[4]	Plug socket with cable	KMYZ-4	PVC cable, without signal status indication, IP50	47
[5]	Connecting cable	NEBV	PUR cable, signal status indication with LED, IP65	47
[6]	Adapter	VAVE-C8	For connecting the valves via connecting cable M8 3-pin or 4-pin, IP65	48
[7]	Cover plate	MHAP2-BP-3	For sealing vacant positions	47
[8]	Inscription labels	MH-BZ-80X	For identifying the valves	48
[9]	Blanking plug	В	For sealing unused ports	48
[10]	Push-in fittings	QS	For connecting tubing with standard O.D.	48
[11]	DIN rail mounting	MHAP2-BG-NRH-35	For mounting the manifold block on DIN rails to EN 60715	48
[12]	Silencer	UC	For mounting in exhaust ports	48
[13]	Individual sub-base	MHA2-AS-3-M5	For sub-base valve	47
[14]	Manifold block	MHA2-PR3-M5	For sub-base valve	47

# Solenoid valves MHA2, fast-switching valves

# Datasheet – Sub-base valve, 3/2-way valve





#### General technical data

Schelat technicat data		
Valve function		3/2 way, single solenoid <sup>1)</sup>
Design		Pressure relief poppet valve
Overlap		Negative overlap
Sealing principle		Soft
Reset method		Mechanical spring
Actuation type		Electrical
Type of control		Direct
Flow direction		Reversible with restrictions
Exhaust air function		Can be throttled
Manual override		Non-detenting
Mounting position		Any
Width	[mm]	10
Grid dimension	[mm]	14
Note on grid dimension		Minimum distance between the valves is 4 mm
Nominal width	[mm]	2
Standard nominal flow rate	[l/min]	100
Type of mounting		To sub-base
Pneumatic connection		Sub-base
Product weight	[g]	60

1) Can be used as a 2/2-way valve by sealing port 3 or 33

## Operating and environmental conditions

			With fast-switching electronics	Without fast-switching electronics		
Operating medium			Compressed air to ISO 8573-1:2010 [7	7:4:4]		
Note on the operating/pilot medium			Lubricated operation possible (in whic	h case lubricated operation will always be required)		
Operating pressure		[MPa]	-0.09 +0.8			
		[bar]	-0.9 +8	-0.9 +8		
		[psi]	-13.05 +116			
	Reversible	[MPa]	-0.09 +0.1			
		[bar]	-0.9 +1			
		[psi]	-13.05 +14.5			
Ambient temperature		[°C]	-5 +40			
Temperature of medium		[°C]	-5 +40			
Restricted ambient temperature and temperature	of medium		As a function of the switching frequence	cy (see graph)		
Corrosion resistance class CRC <sup>1)</sup>			2			
CE marking (see declaration of conformity) <sup>3)</sup>			To EU EMC Directive <sup>2</sup> )	-		
			To EU RoHS Directive	-		
UKCA marking (see declaration of conformity) <sup>3)</sup>			To UK EMC regulations	-		
			To UK RoHS regulations	-		
Certification			c UL us - Recognized (OL)	c UL us - Recognized (OL)		
			RCM	-		
Cleanroom class			Class 6 to ISO 14644-1			
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27				
Vibration resistant			Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6			

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary. 3) More information www.festo.com/catalogue/... → Support/Downloads.

#### Electrical data

			With fast-switching electronics	Without fast-switching electronics
Electrical connection			Plug, 2-pin or cable	
Operating voltage		[V DC]	24	
Permissible voltage fluctuations		[%]	±10	
Power consumption		[W]	5 for approx. 3 ms (high-current phase, inrush current 1 A)	2.88
		[W]	1.25 (low-current phase)	-
Reverse polarity protection			Bipolar	-
Duty cycle		[%]	100	100
Additional functions			Spark arresting	-
			Holding current reduction	-
			Protective circuit	-
Degree of protection to EN 60529	Electrical connection: plug, 2-pin		IP65	IP65
	Electrical connection: cable		IP55	IP55

#### Switching times and frequencies

			With fast-switching electronics	Without fast-switching electronics
Switching time	On	[ms]	1.7	7
	Off	[ms]	2	3.5
Tolerance for switching time	On	[%]	+1030	-
	Off	[%]	+1030	-
Switching time variation from 1 Hz upwards		[ms]	0.2	-
Maximum switching frequency		[Hz]	330	130

Materials
-----------

Materials	
Housing	Die-cast zinc, coated
Cable sheath	PUR
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L



## Restricted ambient temperature and temperature of medium as a function of switching frequency





- Internal current in the coil

- External current in the supply line

- [1] Valve manifold assembly, 6 valves, unpressurised
- [2] Valve manifold assembly, 6 valves, through-flow, 0.6 MPa
- [3] Individual valve, unpressurised
- [4] Individual valve, through-flow, 0.6 MPa

- [1] Capacitor charging
- Controlled coil current 1 A [2]
- [3] Holding current reduction
- [4] Controlled holding current 0.5 A

## Dimensions







Hole pattern on sub-bases



H2 Туре Β1 D1 D2 Η1 H3 H4 L1 L2 L3 L4 L9 ø MHA2-...-3/2.. 10 31 23 29 0.5 73 Hole pattern \_ M2.5 3 18.5 13.5 7.5 1 14 8.5 2 13 \_

Download CAD data → <u>www.festo.com</u>

## Dimensions

Download CAD data → www.festo.com



\* See dimensional table for the manifold block used

#### Dimensions Download CAD data → <u>www.festo.com</u> Manifold assembly, MHA2-PR...-3-M5 Β6 D3 D2 Β7 D4 2 З £ 둼 Å H Η ₽₽ **⊕** 1010Σ H Β1 .8 Β5 Ξ Ť Ľ7 L4 D1 L5 Β4 L3 L1 4 1 L6 EB. B2 Ħ L2 [1] Plug pins [2] Blanking plate [3] Silencer [4] Cable, 2.5 m B7 H1 H6 H7 Туре Β1 B2 Β3 B6 D1 D2 D3 D4 H2 H4 H5 Β4 B5 H3 ø ø ø MHP2-PR...-3-M5 57.4 31.4 12.6 12 4.3 87.9 73 M7 3.3 6.3 M5 18.3 10 8.2 4.9 10.9 41.3 25.1 T1 Туре L4 L5 L6 L7 L8 MHP2-PR...-3-M5 12 14 3.5 24.5 15.4 6.8 Туре No. of valve positions 4 6 8 10 2 MHP2-PR...-3-M5 38 66 94 122 150 L1 L2 31 59 87 115 143 L3 14 42 70 98 126

- **Note** Valve types 3/2G and 3/2O must not be mixed on one manifold block.

# Solenoid valves MHA2, fast-switching valves

# Datasheet – Sub-base valve, 3/2-way valve

Ordering data						
					Part no.	Туре
Valves						
	Electrical connection:	With fast-switching el	ectronics,	Normally open	196139	MHA2-MS1H-3/20-2
	plug, 2-pin switching time 2 ms			Normally closed	196119	MHA2-MS1H-3/2G-2
		Without fast-switching	g electronics,	Normally open	196138	MHA2-M1H-3/20-2
		switching time 7 ms		Normally closed	196118	MHA2-M1H-3/2G-2
	Electrical connection:	With fast-switching el	ectronics,	Normally open	196141	MHA2-MS1H-3/20-2-K
	cable	switching time 2 ms		Normally closed	196121	MHA2-MS1H-3/2G-2-K
		Without fast-switching electronics,		Normally open	196140	MHA2-M1H-3/20-2-K
₹		switching time 7 ms		Normally closed	196120	MHA2-M1H-3/2G-2-K
Manifold rail						
	Individual sub-base			1 valve position	197438	MHA2-AS-3-M5
	Pneumatic connection:	M5 thread				
	Manifold block			2 valve positions	197447	MHA2-PR2-3-M5
	Pneumatic connection 1	1. 11. 3. 33: thread M7		4 valve positions	197448	MHA2-PR4-3-M5
	Pneumatic connection 2			6 valve positions	197449	MHA2-PR6-3-M5
*****				8 valve positions	197450	MHA2-PR8-3-M5
				10 valve positions	197451	MHA2-PR10-3-M5
	l					
Cover plate						
	Vacant valve positions r	must be sealed with a co	over plate.		197470	MHAP2-BP-3
	I.					
Connecting cable (for v	alves with 2-pin plug)					Datasheets → Internet: nebv
11	2-pin socket,	PUR cable, degree of	Signal status	Length 2.5 m	8047671	NEBV-Z4WA2L-P-E-2.5-N-LE2-S1
	open cable end	protection IP65	indication with	Length 5 m	8047672	NEBV-Z4WA2L-P-E-5-N-LE2-S1
	2-wire		LED	Length 10 m	8047670	NEBV-Z4WA2L-P-E-10-N-LE2-S1
line -		PVC cable, degree of	Without signal	Length 0.5 m	193690	КМҮZ-4-24-0.5-В
		protection IP40	status indica-	Length 2.5 m	193691	КМҮZ-4-24-2.5-В
$ $ $\checkmark$			tion			
<u>k</u>	2-pin socket,	PUR cable, degree of	Signal status	Length 0.5 m	8047673	NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1
ALL HAR	plug M8x1 3-pin	protection IP65	indication with	Length 2.5 m	8047674	NEBV-Z4WA2L-P-E-2.5-N-M8G3-S1
			LED			
the second se						
$\checkmark$						

- Valve types 3/2G and 3/20 must not be mixed on one manifold block.

# Solenoid valves MHA2, fast-switching valves

# Datasheet – Sub-base valve, 3/2-way valve

Ordering data					Part no.	Туре
Adapter (for valves wit	h 2-pin plug)		-	-	1	
	2-pin socket	Signal status indica-	Plug M8, 3-pin		571686	VAVE-C8-1R8
	F	tion with LED	Plug M8, 4-pin		573194	VAVE-C8-1R1
DIN rail mounting						
and the second s	For 3/2-way solenoid valves				525053	MHAP2-BG-NRH-35
DIN rail						
	To EN 60715			2 m	35430	NRH-35-2000
	- <b>·</b>					
Silencer						Datasheets → Internet: uc
	with threaded connection		M5	1 piece	165003	UC-M5
				50 piece	534217	UC-M5-50
			M7	1 piece	161418	UC-M7
				50 piece	534218	UC-M7-50
Push-in fitting						Datasheets → Internet: qs
	Male thread M5 with internal hex for tubing O.D.		4 mm	Pack of 10	153315	QSM-M5-4-I
			6 mm	Pack of 10	153317	QSM-M5-6-I
	Male thread M7 with internal hex for tubing O.D.		4 mm	Pack of 10	153319	QSM-M7-4-I
				100 units	133006	QSM-M7-4-I-100
			6 mm	Pack of 10	153321	QSM-M7-6-I
	Male thread M5 with external hex,		4 mm	Pack of 10	153333	QSML-M5-4
	rotatable through 360°, for tubin	g O.D.		100 units	130771	QSML-M5-4-100
<b>•</b>			6 mm	Pack of 10	153335	QSML-M5-6
				100 units	130772	QSML-M5-6-100
	Male thread M7 with external her	x, push-in L-fitting	4 mm	Pack of 10	186352	QSML-M7-4
	rotatable 360⁰, for tubing O.D.			100 units	130773	QSML-M7-4-100
			6 mm	Pack of 10	186353	QSML-M7-6
				100 units	130774	QSML-M7-6-100
Dia altra altra						
Blanking plug				Deals of 10	20/2	DMC
	For M5 thread For M7 thread			Pack of 10 Pack of 10	3843	B-M5 B-M7
	For M7 Inread			Pack of 10	174309	B-M/
Inscription label						
	For solenoid valve			80 pieces in a frame	197259	MH-BZ-80X
				1		

# Peripherals overview – Sub-base valve, 5/2-way valve



Desig	Designation Type		Description	→ Page/Internet
[1]	Sub-base valve	MHA2	With plug vanes	56
[2]	Sub-base valve	MHA2K	With moulded-in cable, IP55	56
[3]	Connecting cable	NEBV	PUR cable, signal status indication with LED, plug M8x1 3-pin, IP65	56
[4]	Plug socket with cable	KMYZ-4	PVC cable, without signal status indication, IP50	56
[5]	Connecting cable	NEBV	PUR cable, signal status indication with LED, IP65	56
[6]	Adapter	VAVE-C8	For connecting the valves via connecting cable M8 3-pin or 4-pin, IP65	57
[7]	Cover plate	MHAP2-BP-5	For sealing vacant positions	56
[8]	Inscription labels	MH-BZ-80X	For identifying the valves	57
[9]	Blanking plug	В	For sealing unused ports	57
[10]	DIN rail mounting	CPV10/14-VI-BG-NRH-35	For mounting the manifold block on DIN rails to EN 60715	57
[11]	Silencer	UC	For mounting in exhaust ports	57
[12]	Push-in fittings	QS	For connecting tubing with standard O.D.	57
[13]	Individual sub-base	MHA2-AS-5-M5	For sub-base valve	56
[14]	Manifold block	MHA2-PR5-M5	For sub-base valve	56

## Solenoid valves MHA2, fast-switching valves

# Datasheet – Sub-base valve, 5/2-way valve







- **L** - Pressure -0.09 ... +0.8 MPa

- Temperature range -5 ... +40 °C



## General technical data

Valve function		5/2-way, single solenoid
Design		Pressure relief poppet valve
Overlap		Negative overlap
Sealing principle		Soft
Reset method		Mechanical spring
Actuation type		Electrical
Type of control		Direct
Flow direction		Not reversible
Exhaust air function		Can be throttled
Manual override		Non-detenting
Mounting position		Any
Width	[mm]	10
Grid dimension	[mm]	14
Note on grid dimension		Minimum distance between the valves is 4 mm
Nominal width	[mm]	2
Standard nominal flow rate	[l/min]	90
Type of mounting		On PR rail
Max. tightening torque for valve mounting	[Nm]	0.4
Pneumatic connection		Sub-base
Product weight	[g]	70

Operating and environmental conditions			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	-0.09 +0.8	
	[bar]	-0.9 +8	
	[psi]	-13.05 +116	
Ambient temperature	[°C]	-5 +40	
Temperature of medium	[°C]	-5 +40	
Restricted ambient temperature and temperature of medium		As a function of the switching frequency (see graph)	
Corrosion resistance class CRC <sup>1)</sup>		2	
CE marking (see declaration of conformity) <sup>3)</sup>		To EU EMC Directive <sup>2</sup> )	
		To EU RoHS Directive	
UKCA marking (see declaration of conformity) <sup>3)</sup>		To UK EMC regulations	
		To UK RoHS regulations	
Certification		c UL us - Recognized (OL)	
		RCM	
Cleanroom class		Class 6 to ISO 14644-1	
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	
Vibration resistant		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6	

## Operating and environmental conditions

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) More information www.festo.com/catalogue/...  $\rightarrow$  Support/Downloads.

Electrical data			1	1
Electrical connection			Plug, 2-pin	Cable
Operating voltage		[V DC]	24	
Permissible voltage fluctuat	ions	[%]	±10	
Power consumption	Low-current phase	[W]	1.625	
	High-current phase	[W]	6.5	
Reverse polarity protection			Bipolar	
Duty cycle		[%]	100	
Additional functions			Spark arresting	
			Holding current reduction	
			Protective circuit	
Degree of protection to EN 60529		IP65	IP55	

## Switching times and frequencies

Switching time	On	[ms]	1.9
	Off	[ms]	1.7
Tolerance for switching time	On	[%]	+1030
	Off	[%]	+1030
Maximum switching frequency		[Hz]	300
Switching time variation from 1 Hz upwards		[ms]	0.2

Materials	
Housing	Die-cast zinc, coated
Cable sheath	PUR
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

## Restricted ambient temperature and temperature of medium as a function of switching frequency



Current curve for valves with fast-switching electronics (MHA2-MS1H)



Internal current in the coil
External current in the supply line

- . .
- [1] Capacitor charging
- [2] Controlled coil current 1 A[3] Holding current reduction
- [4] Controlled holding current 0.5 A

- Valve manifold assembly, 6 valves, unpressurised
  Valve manifold assembly.
- [2] Valve manifold assembly,6 valves, through-flow, 0.6 MPa
- [3] Individual valve, unpressurised[4] Individual valve, through-flow,
- 0.6 MPa



Valve with plug vanes or moulded-in cable, MHA2-...-5/2...



Download CAD data → www.festo.com



## Dimensions

Download CAD data → <u>www.festo.com</u>



## Dimensions

Download CAD data → www.festo.com



# Solenoid valves MHA2, fast-switching valves

# Datasheet – Sub-base valve, 5/2-way valve

				Part no.	Туре
Electrical connection: plug, 2-pin	With fast-switching electronics, switching time 2 ms			525101	MHA2-MS1H-5/2-2
Electrical connection: cable	With fast-switching electronics, switching time 2 ms			525103	MHA2-MS1H-5/2-2-K
					-
Individual sub-base Pneumatic connection: M5 threa	d		1 valve position	525120	MHA2-AS-5-M5
Manifold block			2 valve positions	525127	MHA2-PR2-5-M5
			4 valve positions	525128	MHA2-PR4-5-M5
Pneumatic connection 2, 4: threa	ad M5		6 valve positions	525129	MHA2-PR6-5-M5
			8 valve positions	525130	MHA2-PR8-5-M5
	10 valve positions			525131	MHA2-PR10-5-M5
Vacant valve positions must be s	ealed with a cover plate	е.		525132	MHAP2-BP-5
valves with 2-pin plug)					Datasheets → Internet: neb
2-pin socket,	PUR cable, degree of		Length 2.5 m	8047671	NEBV-Z4WA2L-P-E-2.5-N-LE2-S1
Open cable end 2-wire	protection IP65	tion with LED	Length 5 m	8047672	NEBV-Z4WA2L-P-E-5-N-LE2-S1
			Length 10 m	8047670	NEBV-Z4WA2L-P-E-10-N-LE2-S1
	PVC cable, degree of	Without signal	Length 0.5 m	193690	КМҮZ-4-24-0.5-В
	protection IP40	status indication	Length 2.5 m	193691	КМҮZ-4-24-2.5-В
2-pin socket, plug M8x1 3-pin	PUR cable, degree of	Signal status indica-	Length 0.5 m	8047673	NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1
	protection IP65	tion with LED	Length 2.5 m	8047674	NEBV-Z4WA2L-P-E-2.5-N-M8G3-S1
	2-pin Electrical connection: cable Individual sub-base Pneumatic connection: M5 threa Manifold block Pneumatic connection 1, 3, 5: th Pneumatic connection 2, 4: threa Vacant valve positions must be s valves with 2-pin plug) 2-pin socket, Open cable end 2-wire	2-pin   2-pin     Electrical connection: cable   With fast-switching el     Individual sub-base   Pneumatic connection: M5 thread     Manifold block   Pneumatic connection 1, 3, 5: thread M7     Pneumatic connection 2, 4: thread M5     Vacant valve positions must be sealed with a cover plate     valves with 2-pin plug)     2-pin socket,     Open cable end 2-wire     PUR cable, degree of protection IP40     2-pin socket, plug M8x1 3-pin     PUR cable, degree of protection IP40	2-pin   2-pin     Electrical connection: cable   With fast-switching electronics, switching tir     Individual sub-base   Pneumatic connection: M5 thread     Manifold block   Pneumatic connection 1, 3, 5: thread M7     Pneumatic connection 2, 4: thread M5   Vacant valve positions must be sealed with a cover plate.     valves with 2-pin plug)   2-pin socket, Open cable end 2-wire     PUR cable, degree of Open cable end 2-wire   PUR cable, degree of protection IP40     Signal status indication   2-pin socket, plug M8x1 3-pin     PUR cable, degree of Signal status indication   PUR cable, degree of Signal status indication	2-pin   2-pin     Electrical connection: cable   With fast-switching electronics, switching time 2 ms     Individual sub-base   1 valve position     Pneumatic connection: M5 thread   1 valve positions     Manifold block   2 valve positions     Pneumatic connection 1, 3, 5: thread M7   4 valve positions     Pneumatic connection 2, 4: thread M5   6 valve positions     8 valve positions   8 valve positions     10 valve positions   8 valve positions     Vacant valve positions must be sealed with a cover plate.   10 valve positions     valves with 2-pin plug)   2-pin socket,   PUR cable, degree of protection IP65   Signal status indica- tength 2.5 m     Length 10 m   Length 0.5 m   Length 0.5 m   Length 0.5 m     2-pin socket, plug M8x1 3-pin   PUR cable, degree of protection IP40   Signal status indica- tength 0.5 m     2-pin socket, plug M8x1 3-pin   PUR cable, degree of Signal status indication   Length 0.5 m     2-pin socket, plug M8x1 3-pin   PUR cable, degree of Signal status indication   Length 0.5 m	Electrical connection: plug, 2-pin   With fast-switching electronics, switching time 2 ms   525101     Electrical connection: cable   With fast-switching electronics, switching time 2 ms   525103     Individual sub-base Pneumatic connection: M5 thread   1 valve position   525120     Manifold block Pneumatic connection 1, 3, 5: thread M7 Pneumatic connection 2, 4: thread M5   2 valve positions   525129 8 valve positions     Vacant valve positions must be sealed with a cover plate.   525132   525132     valves with 2-pin plug)   2 valve, degree of protection IP65   Signal status indica- tion with LED   Length 2.5 m   8047671 Length 5 m     V2-pin socket, plug M8x1 3-pin   PUR cable, degree of protection IP40   Without signal status indica- tatus indication   Length 0.5 m   193690 Length 0.5 m     2-pin socket, plug M8x1 3-pin   PUR cable, degree of protection IP40   Signal status indica- tatus indication   Length 0.5 m   193691     2-pin socket, plug M8x1 3-pin   PUR cable, degree of protection IP40   Signal status indica- tatus indication   Length 0.5 m   193691

DIN rail mounting	pin plug) 2-pin socket For 5/2-way solenoid valves To EN 60715	Signal status indica- tion with LED	Plug M8, 3-pin Plug M8, 4-pin		571686 573194 162556	VAVE-C8-1R8 VAVE-C8-1R1 CPV10/14-VI-BG-NRH-35
DIN rail mounting	For 5/2-way solenoid valves				573194	VAVE-C8-1R1
		tion with LED	Plug M8, 4-pin			
					162556	CPV10/14-VI-BG-NRH-35
					162556	CPV10/14-VI-BG-NRH-35
					162556	CPV10/14-VI-BG-NRH-35
	To EN 60715					
DIN rail	To EN 60715					
	10 LN 007 15			2 m	35430	NRH-35-2000
				2 111	55450	NKI1-53-2000
				·		
Silencer	with three deal as a setion		LAG .	1	1(5000	Datasheets → Internet: uc
	with threaded connection		M5	1 piece	165003	UC-M5
				50 piece	534217	UC-M5-50
			M7	1 piece	161418	UC-M7
				50 piece	534218	UC-M7-50
Duch in fitting						Detected a lateration
Push-in fitting	Male thread ME with internal her	for tubing O D	4 mm	Pack of 10	153315	Datasheets → Internet: qs QSM-M5-4-I
	Male lineau M5 with milemat nex	e thread M5 with internal hex for tubing O.D.		Pack of 10	153313	QSM-M5-6-I
	Malo throad M7 with internal box	hread M7 with internal hex for tubing O.D.		Pack of 10	153317	QSM-M7-4-I
				100 units	133006	QSM-M7-4-I-100
			6 mm	Pack of 10	153321	QSM-M7-6-I
	Male thread M5 with external hex, push-in L-fitting		4 mm	Pack of 10	153333	QSML-M5-4
	rotatable 360 <sup>o</sup> , for tubing O.D.			100 units	130771	QSML-M5-4-100
			6 mm	Pack of 10	153335	QSML-M5-6
				100 units	130772	QSML-M5-6-100
-	Male thread M7 with external hex, push-in L-fitting		4 mm	Pack of 10	186352	QSML-M7-4
	rotatable 360°, for tubing O.D.	, push in Entiting		100 units	130773	QSML-M7-4-100
	,		6 mm	Pack of 10	186353	QSML-M7-6
				100 units	130774	QSML-M7-6-100
				100 01110		
Blanking plug						
	For M5 thread			Pack of 10	3843	B-M5
	For M7 thread			Pack of 10	174309	B-M7
				1		
Inscription label						
	For solenoid valve			80 pieces in a frame	197259	MH-BZ-80X

# Peripherals overview - Individual valve

## Connection with plug vanes - Connection with moulded-in cable



Desigr	Description Type Description		Description	→ Page/Internet
[1]	Individual valve	MHE3	With plug vanes	64
[2]	Individual valve	MHE3K	With moulded-in cable, IP65	64
[3]	Connecting cable	NEBV	PUR cable, signal status indication with LED, IP65	65
[4]	Plug socket with cable	KMYZ-4	PVC cable, without signal status indication, IP50	65
[5]	Adapter	VAVE-C8	For connecting the valves via connecting cable M8 3-pin or 4-pin, IP65	65
[6]	Mounting bracket	MHE2-BG-L	For wall mounting	65
[7]	Push-in fittings	QS	For connecting tubing with standard O.D.	65
[8]	Silencer	UC	For mounting in exhaust ports	65







#### General technical data

General technical data		
Valve function		3/2 way, single solenoid <sup>1)</sup>
Design		Pressure relief poppet valve
Overlap		Negative overlap
Sealing principle		Soft
Reset method		Mechanical spring
Actuation type		Electrical
Type of control		Direct
Flow direction		Reversible with restrictions <sup>2)</sup>
Exhaust air function		Can be throttled
Manual override		Non-detenting
Mounting position		Any
Width	[mm]	14
Grid dimension	[mm]	19
Note on grid dimension		Minimum distance between the valves is 5 mm
Nominal width	[mm]	3
Standard nominal flow rate	[l/min]	200
Type of mounting		Via through-hole
Pneumatic connection		Connecting thread G1/8
		Push-in connector for tubing O.D. 6 mm
Product weight	[g]	120

1) Can be used as a 2/2-way valve by sealing port 3 or 33

2) Slight leakage can occur in the pressure range -0.8 bar to +0.5 bar.

#### Operating and environmental conditions

		With fast-switching electronics	Without fast-switching electronics
Operating medium		Compressed air to ISO 8573-1:2010 [7:4	:4]
Note on the operating/pilot medium		Lubricated operation possible (in which o	case lubricated operation will always be required)
Ambient temperature	[°C]	-5 +60	
Temperature of medium	[°C]	-5 +60	
Restricted ambient temperature and temperature of medium		As a function of switching frequency	-
Corrosion resistance class CRC <sup>1)</sup>		2	2
CE marking (see declaration of conformity) <sup>3)</sup>		To EU EMC Directive <sup>2</sup> )	-
		To EU RoHS Directive	-
UKCA marking (see declaration of conformity) <sup>3)</sup>		To UK EMC regulations	-
		To UK RoHS regulations	-
Certification		c UL us - Recognized (OL)	c UL us - Recognized (OL)
		RCM	-
Cleanroom class		Class 6 to ISO 14644-1	
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	
Vibration resistant		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6	

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) More information www.festo.com/catalogue/...  $\rightarrow$  Support/Downloads.

## Operating and environmental conditions

			With fast-switching electronics	Without fast-switching electronics
Operating pressure		[MPa]	-0.09 +0.8	
		[bar]	-0.9 +8	
		[psi]	-13.05 +116	
	Reversible	[MPa]	-0.09 +0.1	
		[bar]	-0.9 +1	
		[psi]	-13.05 +14.5	

## Electrical data

		With fast-switching electronics	Without fast-switching electronics
Electrical connection		Plug, 2-pin or cable	
Operating voltage	[V DC]	24	
Permissible voltage fluctuations	[%]	±10	
Power consumption	[W]	6.5 for approx. 4.5 ms (high-current phase, inrush current 1 A)	3.7
	[W]	1.6 (low-current phase)	-
Reverse polarity protection		Bipolar	-
Duty cycle	[%]	100	100
Additional functions		Spark arresting	-
		Holding current reduction	-
		Protective circuit	-
Degree of protection to EN 60529		IP65	IP65

## Switching times and frequencies

			With fast-switching electronics	Without fast-switching electronics
Switching time	On	[ms]	2.3	8.3
	Off	[ms]	2.8	4.5
Tolerance for switching time	On	[%]	+1030	-
	Off	[%]	+1050	-
Switching time variation from 1 Hz upwards		[ms]	0.2	-
Maximum switching frequency		[Hz]	280	130

# MaterialsHousingDie-cast zinc, coatedCable sheathPURSealsHNBR, NBRScrewsGalvanised steelNote on materialsRoHS-compliantLABS (PWIS) conformityVDMA24364-B1/B2-L

I



## Restricted ambient temperature and temperature of medium as a function of switching frequency





[1] Valve manifold assembly, 6 valves, unpressurised

[2] Valve manifold assembly, 6 valves, through-flow, 0.6 MPa

[3] Individual valve, unpressurised

No restrictions for individual valve, through-flow, 0.6 MPa.

[1] Capacitor charging

[2] Controlled coil current 1 A

- [3] Holding current reduction
- [4] Controlled holding current 0.5 A

- Internal current in the coil

External current in the supply line

## Dimensions



Туре	B1	D1	D2 Ø	D3 Ø	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8	L9
MHE31/8	14	G1/8	-	4.5	45	-	38	25	94.5	46	23	20	13	16	15	23	0.6
MHE3QS-6	14	-	6	4.5	45	53.6	38	25	94.5	46	23	20	13	16	15	23	0.6

## Solenoid valves MHE3, fast-switching valves

40

25

7.5

# Datasheet – Individual valve



MHE2-BG-L

20

10

2



4.5

55

113.3

## Solenoid valves MHE3, fast-switching valves

# Datasheet – Individual valve

Ordering data						
					Part no.	Туре
/alves						
<i>,</i>	Electrical connec-	With fast-switching	Pneumatic connection: thread	Normally open	525167	MHE3-MS1H-3/20-1/8
92	tion: plug, 2-pin	electronics, switching	G1/8	Normally closed	525147	MHE3-MS1H-3/2G-1/8
2		time 2.3 ms	Pneumatic connection: push-in	Normally open	525171	MHE3-MS1H-3/20-QS-6
			connector for tubing O.D. 6 mm	Normally closed	525151	MHE3-MS1H-3/2G-QS-6
		Without fast-switching	Pneumatic connection: thread	Normally open	525166	MHE3-M1H-3/20-1/8
	electronics, switching	G1/8	Normally closed	525146	MHE3-M1H-3/2G-1/8	
	electronics, switching time 8.3 ms	Pneumatic connection: push-in	Normally open	525170	MHE3-M1H-3/20-QS-6	
			connector for tubing O.D. 6 mm	Normally closed	525150	MHE3-M1H-3/2G-QS-6
$\mathcal{A}$	Electrical connec-	With fast-switching	Pneumatic connection: thread	Normally open	525169	MHE3-MS1H-3/20-1/8-K
	tion: cable	electronics, switching	G1/8	Normally closed	525149	MHE3-MS1H-3/2G-1/8-K
and a second		time 2.3 ms	Pneumatic connection: push-in connector for tubing O.D. 6 mm	Normally closed	525153	MHE3-MS1H-3/2G-QS-6-K
		Without fast-switching	Pneumatic connection: thread	Normally open	525168	MHE3-M1H-3/20-1/8-K
		electronics, switching	G1/8	Normally closed	525148	MHE3-M1H-3/2G-1/8-K
		time 8.3 ms	Pneumatic connection: push-in connector for tubing O.D. 6 mm	Normally closed	525152	MHE3-M1H-3/2G-QS-6-K

Ordering data						
					Part no.	Туре
Connecting cable (for	valves with 2-pin plug)					Datasheets → Internet: neb
ll ll	2-pin socket,	PUR cable, degree of	Signal status indica-	Length 2.5 m	8047671	NEBV-Z4WA2L-P-E-2.5-N-LE2-S1
ll ll	Open cable end 2-wire	protection IP65	tion with LED	Length 5 m	8047672	NEBV-Z4WA2L-P-E-5-N-LE2-S1
				Length 10 m	8047670	NEBV-Z4WA2L-P-E-10-N-LE2-S1
ps -		PVC cable, degree of	Without signal	Length 0.5 m	193690	КМҮZ-4-24-0.5-В
		protection IP40	status indication	Length 2.5 m	193691	КМҮZ-4-24-2.5-В
<u> </u>	2-pin socket, plug M8x1	PUR cable, degree of	Signal status indica-	Length 0.5 m	8047673	NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1
S THE REAL PROPERTY IN	3-pin	protection IP65	tion with LED	Length 2.5 m	8047674	NEBV-Z4WA2L-P-E-2.5-N-M8G3-S1
Adapter (for valves wi	ith 2-pin plug)			I		
	2-pin socket	Signal status indication	Plug M8, 3-pin		571686	VAVE-C8-1R8
		with LED	Plug M8, 4-pin		573194	VAVE-C8-1R1
Nall mounting	Mounting bracket				196165	MHE2-BG-L
Silencer						Datasheets → Internet: u
	Push-in sleeve with O.D. 6	mm		1 pieces	165007	UC-QS-6H
	With threaded connection (	G1/8		1 pieces	161419	UC-1/8
				50 pieces	534219	UC-1/8-50
Push-in fitting						Datasheets → Internet: q
<b>_</b>	Male thread G1/8 with exte	ernal hex for tubing O.D.	6 mm	Pack of 10	186096	QS-G1/8-6
				100 pieces	132037	QS-G1/8-6-100
►			8 mm	Pack of 10	186098	QS-G1/8-8
				50 pieces	132038	QS-G1/8-8-50
	Male thread G1/8 with exte	ernal hex, push-in L-fitting	6 mm	Pack of 10	186117	QSL-G1/8-6
	rotatable 360°, for tubing (			100 pieces	132049	QSL-G1/8-6-100
			8 mm	Pack of 10	186119	QSL-G1/8-8

# Peripherals overview - Semi in-line valve

## Connection with plug vanes - Connection with moulded-in cable



Desigr	nation	Туре	Description	→ Page/Internet
[1]	Semi-in-line valve	MHP3	With plug vanes	73
[2]	Semi-in-line valve	МНР3К	With moulded-in cable, IP65	73
[3]	Plug socket with cable	KMYZ-4	PVC cable, without signal status indication, IP50	73
[4]	Connecting cable	NEBV	PUR cable, signal status indication with LED, IP65	73
[5]	Adapter	VAVE-C8	For connecting the valves via connecting cable M8 3-pin or 4-pin, IP65	73
[6]	Push-in fittings	QS	For connecting tubing with standard O.D.	74
[7]	Cover plate	MHAP3-BP-3	For sealing vacant positions	73
[8]	Blanking plug	В	For sealing unused ports	74
[9]	Inscription labels	MH-BZ-80X	For identifying the valves	74
[10]	DIN rail mounting	CPV10/14-VI-BG-NRH-35	For mounting the manifold block on DIN rails to EN 60715	74
[11]	Silencer	UC	For mounting in exhaust ports	74
[12]	Individual sub-base	MHA3-AS-3-1/8	For semi in-line valves; the individual sub-base is also used for sub-base valves and must be sealed with a blanking plug here	73
[13]	Manifold block	MHA3-PR	For semi in-line valves	73

## Solenoid valves MHP3, fast-switching valves

# Datasheet – Semi in-line valve



#### General technical data

General technical data							
Valve function			3/2 way, single solenoid <sup>1)</sup>				
Design			Pressure relief poppet valve				
Overlap			Negative overlap				
Sealing principle			Soft				
Reset method			Mechanical spring				
Actuation type			Electrical				
Type of control			Direct				
Flow direction			Reversible with restrictions <sup>2)</sup>				
Exhaust air function			Can be throttled				
Manual override			Non-detenting				
Mounting position			Any				
Width		[mm]	14				
Grid dimension		[mm]	19				
Note on grid dimension			Minimum distance between the valves is 5 mm				
Nominal width		[mm]	3				
Standard nominal flow rate		[l/min]	200				
Type of mounting			On PR rail				
Pneumatic connection	2		Connecting thread G1/8, push-in connector for tubing O.D. 6 mm				
	1, 11, 3, 33		Sub-base				
Product weight		[g]	120				

Can be used as a 2/2-way valve by sealing port 3 or 33
Slight leakage can occur in the pressure range -0.8 bar to +0.5 bar.

## Operating and environmental conditions

			With fast-switching electronics	Without fast-switching electronics				
Operating medium			Compressed air to ISO 8573-1:2010 [7:4	:4]				
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required					
Operating pressure		[MPa]	-0.09 +0.8					
ote on the operating/pilot medium     perating pressure     Reversible     mbient temperature     emperature of medium     estricted ambient temperature and temperature of medium     porrosion resistance class CRC <sup>1)</sup> E marking (see declaration of conformity) <sup>3)</sup> KCA marking (see declaration of conformity) <sup>3)</sup> ertification     leanroom class     hock resistance		[bar]	-0.9 +8					
		[psi]	-13.05 +116					
	Reversible [MPa]		-0.09 +0.1					
		[bar]	-0.9 +1					
		[psi]	-13.05 +14.5					
Ambient temperature	nt temperature							
Temperature of medium		[°C]	-5 +40					
Restricted ambient temperature and temperature of	of medium		As a function of switching frequency	-				
Corrosion resistance class CRC <sup>1)</sup>			2	2				
CE marking (see declaration of conformity) <sup>3)</sup>			To EU EMC Directive <sup>2</sup> )	-				
emperature of medium testricted ambient temperature and temperature of m corrosion resistance class CRC <sup>1)</sup>			To EU RoHS Directive	-				
UKCA marking (see declaration of conformity) <sup>3)</sup>			To UK EMC regulations	-				
			To UK RoHS regulations	-				
Certification			c UL us - Recognized (OL)	c UL us - Recognized (OL)				
			RCM	-				
Cleanroom class			Class 6 to ISO 14644-1					
Shock resistance			Shock test with severity level 2 to FN 942	017-5 and EN 60068-2-27				
Vibration resistant			Transport application test with severity le	evel 2 to FN 942017-4 and EN 60068-2-6				

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary. 3) More information www.festo.com/catalogue/... → Support/Downloads.

Electrical data			
		With fast-switching electronics	Without fast-switching electronics
Electrical connection		Plug, 2-pin or cable	
Operating voltage	[V DC]	24	
Permissible voltage fluctuations	[%]	±10	
Power consumption	[W]	6.5 (high-current phase)	3.7
	[W]	1.6 (low-current phase)	-
Reverse polarity protection		Bipolar	-
Duty cycle	[%]	100	100
Additional functions		Spark arresting	-
		Holding current reduction	-
		Protective circuit	-
Degree of protection to EN 60529		IP65	IP65

## Switching times and frequencies

			With fast-switching electronics	Without fast-switching electronics
Switching time	On	[ms]	2.3	8.3
	Off	[ms]	2.8	4.5
Tolerance for switching time	On	[%]	+1030	-
	Off	[%]	+1050	-
Switching time variation from 1 Hz upwards		[ms]	0.2	-
Maximum switching frequency		[Hz]	280	130

Materials

Housing	Die-cast zinc, coated
Cable sheath	PUR
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

I





## Current curve for valves with fast-switching electronics (MHP3-MS1H)



Internal current in the coil
External current in the supply line

 Valve manifold assembly, 6 valves, unpressurised

[2] Valve manifold assembly,6 valves, through-flow, 0.6 MPa

[3] Individual valve, unpressurised

No restrictions for individual valve, through-flow, 0.6 MPa.

[1] Capacitor charging

[2] Controlled coil current 1 A

[3] Holding current reduction

[4] Controlled holding current 0.5 A



Download CAD data → www.festo.com

# Datasheet - Semi in-line valve

## Dimensions



#### [1] Hole for coding pin, 2mm deep [2] Mounting thread, 8 mm deep

Individual sub-base, MHA3-AS-3-1/8

1



Туре	B1	B2	B3	B4	B5	B6	D1	D2 Ø	D3 Ø	H1	H2	H3	H4	H5
Hole pattern	-	-	-	-	-	-	5	4	M3	35.3	28	8.3	8	6.3
MHA3-AS-3-1/8	28	11.8	5	9.3	31.5	13.3	G1/8	4.5	8	31.3	21	11.7	8.6	59.3
Туре	L1		L2	L:	3	L4		L5	L6		L7	L8		T1
Hole pattern	18		4	-	-	-		-	-		-	-		-
MHA3-AS-3-1/8	78.9		45.3	1	8	54.3	1	7.9	12.5		21	95		16.4

\_ Note With semi in-line valves, port 2 is

not used. If used as a 2/2-way valve, normally closed, ports 3/11 are not used.

If used as a 2/2-way valve, normally open, ports 1/33 are not used.

## Dimensions

Download CAD data → <u>www.festo.com</u>



Valve types 3/2G and 3/20 must not be mixed on one manifold block.
# Datasheet – Semi in-line valve

Ordering data						
					Part no.	Туре
Valves		[		I		
	Electrical connection:	With fast-switching	Pneumatic connection: thread	Normally open	525159	MHP3-MS1H-3/20-1/8
	plug, 2-pin	electronics, switch-	G1/8	Normally closed	525139	MHP3-MS1H-3/2G-1/8
8		ing time 2.3 ms	Pneumatic connection: push- in connector for tubing O.D. 6 mm	Normally closed	525143	MHP3-MS1H-3/2G-QS-6
		Without fast-switch-	Pneumatic connection: thread	Normally open	525158	MHP3-M1H-3/20-1/8
		ing electronics,	G1/8	Normally closed	525138	MHP3-M1H-3/2G-1/8
		switching time 8.3 ms	Pneumatic connection: push- in connector for tubing O.D. 6 mm	Normally closed	525142	MHP3-M1H-3/2G-QS-6
AND	Electrical connection: cable	With fast-switching electronics, switch- ing time 2.3 ms	Pneumatic connection: push- in connector for tubing O.D. 6 mm	Normally closed	525145	MHP3-MS1H-3/2G-QS-6-K
Manifold rail						
	Individual sub-base <sup>1)</sup> Pneumatic connection:	: thread G1/8		1 valve position	525214	MHA3-AS-3-1/8
	Manifold block <sup>1)</sup>			2 valve positions	525221	MHA3-PR2-3-1/8
	Pneumatic connection	1, 11, 3, 33: thread G	1/4	4 valve positions	525222	MHA3-PR4-3-1/8
	Pneumatic connection			6 valve positions	525223	MHA3-PR6-3-1/8
<b>N 1 1 1 1 1 1 1 1 1 1</b>				8 valve positions	525223	MHA3-PR8-3-1/8
				10 valve positions	525225	MHA3-PR10-3-1/8
Cover plate						
	Vacant valve positions	must be sealed with a	cover plate.		525226	MHAP3-BP-3
Connecting cable (fo	r valves with 2-pin plug)					Datasheets → Internet: neb
	2-pin socket,	PUR cable, degree of	Signal status indication with	Length 2.5 m	8047671	NEBV-Z4WA2L-P-E-2.5-N-LE2-S1
ll ll	open cable end,	protection IP65	LED	Length 5 m	8047672	NEBV-Z4WA2L-P-E-5-N-LE2-S1
	2-wire			Length 10 m	8047670	NEBV-Z4WA2L-P-E-10-N-LE2-S1
the second se		PVC cable, degree of	Without signal status indica-	Length 0.5 m	193690	KMYZ-4-24-0.5-B
		protection IP40	tion	Length 2.5 m	193691	КМҮZ-4-24-2.5-В
	2-pin socket, plug	PUR cable, degree of	Signal status indication with	Length 0.5 m	8047673	NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1
C. M. DV	M8x1 3-pin	protection IP65	LED	Length 2.5 m	8047674	NEBV-Z4WA2L-P-E-2.5-N-M8G3-S1
Adapter (for valves w	vith 2-pin plug)					
	2-pin socket	Signal status indica-	Plug M8, 3-pin		571686	VAVE-C8-1R8
		tion with LED	Plug M8, 4-pin		573194	VAVE-C8-1R1

1) Seal port 2 with a blanking plug. These ports have no function when using semi in-line valves.

# Datasheet – Semi in-line valve

Ordering data				Part no.	Туре
DIN rail mounting					
	For manifold block				CPV10/14-VI-BG-NRH-35
DIN rail					
	To EN 60715	2 m	35430	NRH-35-2000	
Silencer			<u> </u>		Datasheets $\rightarrow$ Internet: uc
	Push-in sleeve with O.D. 6 mm	1	1 pieces	165007	UC-QS-6H
	with threaded connection	G1/8	1 piece	161419	UC-1/8
			50 pieces	534219	UC-1/8-50
		G1/4	1 piece	165004	UC-1/4
			20 pieces	534220	UC-1/4-20
			-		
Push-in fitting	1	1	Ť		Datasheets → Internet: qs
	Male thread G1/8 with external hex for tubing O.D.	6 mm	Pack of 10	186096	QS-G1/8-6
Salar Salar			100 pieces	132037	QS-G1/8-6-100
		8 mm	Pack of 10	186098	QS-G1/8-8
			50 pieces	132038	QS-G1/8-8-50
	Male thread G1/4 with external hex for tubing O.D.	8 mm	Pack of 10	186099	QS-G1/4-8
			50 pieces	132040	QS-G1/4-8-50
		10 mm	Pack of 10	186101	QS-G1/4-10
			50 pieces	132041	QS-G1/4-10-50
	Male thread G1/8 with external hex, push-in L-fitting	6 mm	Pack of 10	186117	QSL-G1/8-6
	rotatable 360°, for tubing O.D.		100 pieces	132049	QSL-G1/8-6-100
		8 mm	Pack of 10	186119	QSL-G1/8-8
			50 pieces	132050	QSL-G1/8-8-50
	Male thread G1/4 with external hex, push-in L-fitting	8 mm	Pack of 10	186120	QSL-G1/4-8
	rotatable 360 <sup>o</sup> , for tubing O.D.		50 pieces	132052	QSL-G1/4-8-50
		10 mm	Pack of 10	186122	QSL-G1/4-10
			50 pieces	132053	QSL-G1/4-10-50
Blanking plug					
	For G1/8 thread		Pack of 10	3568	B-1/8
	For G1/4 thread		Pack of 10	3569	B-1/4
Inscription label					
	For solenoid valve		80 pieces in a frame	197259	MH-BZ-80X

# Peripherals overview – Sub-base valve

### Connection with plug vanes – Connection with moulded-in cable



Desigr	nation	Туре	Description	→ Page/Internet
[1]	Sub-base valve	МНАЗ	With plug vanes	82
[2]	Sub-base valve	МНАЗК	HA3K With moulded-in cable, IP65	
[3]	Adapter	VAVE-C8	For connecting the valves via connecting cable M8 3-pin or 4-pin, IP65	82
[4]	Plug socket with cable	KMYZ-4	PVC cable, without signal status indication, IP50	82
[5]	Connecting cable	NEBV	PUR cable, signal status indication with LED, IP65	82
[6]	Cover plate	MHAP3-BP-3	For sealing vacant positions	82
[7]	Blanking plug	В	For sealing unused ports	83
[8]	Inscription labels	MH-BZ-80X	For identifying the valves	83
[9]	Push-in fittings	QS	For connecting tubing with standard O.D.	83
[10]	DIN rail mounting	CPV10/14-VI-BG-NRH-35	For mounting the manifold block on DIN rails to EN 60715	83
[11]	Silencer	UC	For mounting in exhaust ports	83
[12]	Individual sub-base	MHA3-AS-3-1/8	For sub-base valve	82
[13]	Manifold block	MHA3-PR3-1/8	For sub-base valve	82

### Solenoid valves MHA3, fast-switching valves

### Datasheet – Sub-base valve







–0.09 ... +0.8 MPa

- Temperature range -5 ... +40 °C



#### General technical data

Valve function		3/2 way, single solenoid <sup>1)</sup>
Design		Pressure relief poppet valve
Overlap		Negative overlap
Sealing principle		Soft
Reset method		Mechanical spring
Actuation type		Electrical
Type of control		Direct
Flow direction		Reversible with restrictions <sup>2)</sup>
Exhaust air function		Can be throttled
Manual override		Non-detenting
Mounting position		Any
Width	[mm]	14
Grid dimension	[mm]	19
Note on grid dimension		Minimum distance between the valves is 5 mm
Nominal width	[mm]	3
Standard nominal flow rate	[l/min]	200
Type of mounting		On PR rail, via through-hole
Pneumatic connection		Sub-base
Product weight	[g]	120

1) Can be used as a 2/2-way valve by sealing port 3 or 33

2) Slight leakage can occur in the pressure range –0.8 bar to +0.5 bar.

# Datasheet – Sub-base valve

#### Operating and environmental conditions

			With fast-switching electronics	Without fast-switching electronics			
Operating medium			Compressed air to ISO 8573-1:2010 [7:4	i:4]			
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure		[MPa]	-0.09 +0.8				
		[bar]	-0.9 +8	-0.9 +8			
		[psi]	-13.05 +116				
	Reversible	[MPa]	-0.09 +0.1				
		[bar]	-0.9 +1				
		[psi]	-13.05 +14.5				
Ambient temperature		[°C]	-5 +40				
Temperature of medium		[°C]	-5 +40				
Restricted ambient temperature and temperature	of medium		As a function of switching frequency	-			
Corrosion resistance class CRC <sup>1)</sup>			2	2			
CE marking (see declaration of conformity) <sup>3)</sup>			To EU EMC Directive <sup>2</sup> )	-			
			To EU RoHS Directive	-			
UKCA marking (see declaration of conformity) <sup>3)</sup>			To UK EMC regulations	-			
			To UK RoHS regulations	-			
Certification			c UL us - Recognized (OL)	c UL us - Recognized (OL)			
			RCM	-			
Cleanroom class			Class 6 to ISO 14644-1				
Shock resistance			Shock test with severity level 2 to FN 942	2017-5 and EN 60068-2-27			
Vibration resistant			Transport application test with severity le	evel 2 to FN 942017-4 and EN 60068-2-6			

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) More information www.festo.com/catalogue/...  $\rightarrow$  Support/Downloads.

#### Electrical data

		With fast-switching electronics	Without fast-switching electronics
Electrical connection	-	Plug, 2-pin or cable	
Operating voltage	[V DC]	24	
Permissible voltage fluctuations	[%]	±10	
Power consumption	[W]	6.5 for approx. 4.5 ms (high-current phase, inrush current 1 A)	3.7
	[W]	1.6 (low-current phase)	-
Reverse polarity protection		Bipolar	-
Duty cycle	[%]	100	100
Additional functions		Spark arresting	-
		Holding current reduction	-
		Protective circuit	-
Degree of protection to EN 60529		IP65	IP65

#### Switching times and frequencies

			With fast-switching electronics	Without fast-switching electronics
Switching time	On	[ms]	2.3	8.3
	Off	[ms]	2.8	4.5
Tolerance for switching time	On	[%]	+1030	-
	Off	[%]	+1050	-
Switching time variation from 1 Hz upwards		[ms]	0.2	-
Maximum switching frequency		[Hz]	280	130

#### Materials

Housing	Die-cast zinc, coated
Cable sheath	PUR
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

#### Restricted ambient temperature and temperature of medium as a function of switching frequency



#### Current curve for valves with fast-switching electronics (MHA3-MS1H)



- - - Internal current in the coil

External current in the supply line

- [1] Valve manifold assembly, 6 valves, unpressurised
- [2] Valve manifold assembly,6 valves, through-flow, 0.6 MPa
- [3] Individual valve, unpressurised

No restrictions for individual valve, through-flow, 0.6 MPa.

[1] Capacitor charging

- [2] Controlled coil current 1 A
- [3] Holding current reduction
- [4] Controlled holding current 0.5 A

Download CAD data → www.festo.com

# Datasheet – Sub-base valve

### Dimensions

Valve with plug vanes or moulded-in cable, MHA3-...-3/2G...



#### Hole pattern on sub-bases



[1] Hole for coding pin, 2mm deep [2] Mounting thread, 8 mm deep

Туре Β1 D1 D2 D3 Η1 H2 H3 H4 H5 L1 L2 L9 Ø Ø 38 94.5 MHA3-...-3/2G... 14 28 42 0.6 \_ \_ \_ \_ \_ \_ Hole pattern 5 М3 35.3 28 8 18 4 8.3 6.3 4 \_

#### Dimensions

Download CAD data → <u>www.festo.com</u>



### Dimensions

Download CAD data → <u>www.festo.com</u>



### Solenoid valves MHA3, fast-switching valves

# Datasheet – Sub-base valve

					Part no.	Туре
/es						
	Electrical connection: plug, 2-pin	With fast-switching	electronics	Normally closed	525135	MHA3-MS1H-3/2G-3
	Licentear connection, plug, 2 pin	switching time 2.3		Normally closed	525155	
		Without fast-switch		Normally closed	525134	MHA3-M1H-3/2G-3
		switching time 8.3	•	Nonnutry closed	525254	,
	Electrical connection: cable With fast-switching electronics,			Normally closed	525137	MHA3-MS1H-3/2G-3-K
		switching time 2.3 ms Without fast-switching electronics,		,		
1				Normally closed	525136	MHA3-M1H-3/2G-3-K
~		switching time 8.3	switching time 8.3 ms			
ifold rail	Individual sub-base			1	525244	
Individual sub-base Pneumatic connection: thread G1/8		1 valve position	525214	MHA3-AS-3-1/8		
	Filedinatic connection: (filed0 G1	/0				
	Manifold block			2 valve positions	525221	MHA3-PR2-3-1/8
Pneumatic connection 1, 11, 3, 33: thread G1/4				4 valve positions	525222	MHA3-PR4-3-1/8
	Pneumatic connection 2: thread G	51/8		6 valve positions	525223	MHA3-PR6-3-1/8
				8 valve positions	525224	MHA3-PR8-3-1/8
				10 valve positions	525225	MHA3-PR10-3-1/8
er plate						
۹	Vacant valve positions must be se	ealed with a cover plat	e.		525226	MHAP3-BP-3
	Vacant valve positions must be se	ealed with a cover plat	e.		525226	MHAP3-BP-3
	Vacant valve positions must be se	ealed with a cover plat	е.		525226	МНАРЗ-ВР-З
	Vacant valve positions must be se	ealed with a cover plat	е.		525226	МНАРЗ-ВР-З
necting cable (for	Vacant valve positions must be se	ealed with a cover plat	e.		525226	
necting cable (for		PUR cable,	e. Signal status indica-	Length 2.5 m	525226 8047671	
necting cable (for	valves with 2-pin plug)			Length 2.5 m Length 5 m		Datasheets → Internet:
necting cable (for	valves with 2-pin plug) 2-pin socket,	PUR cable,	Signal status indica-	· ·	8047671	Datasheets → Internet: NEBV-Z4WA2L-P-E-2.5-N-LE2-S1
necting cable (for	valves with 2-pin plug) 2-pin socket,	PUR cable, degree of protec-	Signal status indica-	Length 5 m	8047671 8047672	Datasheets → Internet: NEBV-Z4WA2L-P-E-2.5-N-LE2-S1 NEBV-Z4WA2L-P-E-5-N-LE2-S1
necting cable (for	valves with 2-pin plug) 2-pin socket,	PUR cable, degree of protec- tion IP65	Signal status indica- tion with LED	Length 5 m Length 10 m	8047671 8047672 8047670	Datasheets → Internet: NEBV-Z4WA2L-P-E-2.5-N-LE2-S1 NEBV-Z4WA2L-P-E-5-N-LE2-S1 NEBV-Z4WA2L-P-E-10-N-LE2-S1
necting cable (for	valves with 2-pin plug) 2-pin socket, Open cable end 2-wire	PUR cable, degree of protec- tion IP65 PVC cable, degree of protection IP40	Signal status indica- tion with LED Without signal status indication	Length 5 m Length 10 m Length 0.5 m Length 2.5 m	8047671 8047672 8047670 193690 193691	Datasheets → Internet:           NEBV-Z4WA2L-P-E-2.5-N-LE2-S1           NEBV-Z4WA2L-P-E-5-N-LE2-S1           NEBV-Z4WA2L-P-E-10-N-LE2-S1           KMYZ-4-24-0.5-B           KMYZ-4-24-2.5-B
necting cable (for	valves with 2-pin plug) 2-pin socket,	PUR cable, degree of protec- tion IP65 PVC cable, degree of protection IP40 PUR cable,	Signal status indica- tion with LED Without signal status indication Signal status indica-	Length 5 m Length 10 m Length 0.5 m Length 2.5 m Length 0.5 m	8047671 8047672 8047670 193690 193691 8047673	Datasheets → Internet           NEBV-Z4WA2L-P-E-2.5-N-LE2-S1           NEBV-Z4WA2L-P-E-5-N-LE2-S1           NEBV-Z4WA2L-P-E-10-N-LE2-S1           KMYZ-4-24-0.5-B           KMYZ-4-24-2.5-B           NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1
necting cable (for	valves with 2-pin plug) 2-pin socket, Open cable end 2-wire	PUR cable, degree of protec- tion IP65 PVC cable, degree of protection IP40	Signal status indica- tion with LED Without signal status indication	Length 5 m Length 10 m Length 0.5 m Length 2.5 m	8047671 8047672 8047670 193690 193691	Datasheets → Internet           NEBV-Z4WA2L-P-E-2.5-N-LE2-S1           NEBV-Z4WA2L-P-E-5-N-LE2-S1           NEBV-Z4WA2L-P-E-10-N-LE2-S1           KMYZ-4-24-0.5-B           KMYZ-4-24-2.5-B
necting cable (for	valves with 2-pin plug) 2-pin socket, Open cable end 2-wire	PUR cable, degree of protec- tion IP65 PVC cable, degree of protection IP40 PUR cable, degree of protec-	Signal status indica- tion with LED Without signal status indication Signal status indica-	Length 5 m Length 10 m Length 0.5 m Length 2.5 m Length 0.5 m	8047671 8047672 8047670 193690 193691 8047673	Datasheets → Internet:           NEBV-Z4WA2L-P-E-2.5-N-LE2-S1           NEBV-Z4WA2L-P-E-5-N-LE2-S1           NEBV-Z4WA2L-P-E-10-N-LE2-S1           KMYZ-4-24-0.5-B           KMYZ-4-24-2.5-B           NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1
necting cable (for	valves with 2-pin plug)         2-pin socket,         Open cable end 2-wire         2-pin socket, plug M8x1 3-pin         2-pin socket, plug M8x1 3-pin	PUR cable, degree of protec- tion IP65 PVC cable, degree of protection IP40 PUR cable, degree of protec- tion IP65	Signal status indica- tion with LED Without signal status indication Signal status indica- tion with LED	Length 5 m Length 10 m Length 0.5 m Length 2.5 m Length 0.5 m	8047671 8047672 8047670 193690 193691 8047673 8047674	Datasheets → Internet: NEBV-Z4WA2L-P-E-2.5-N-LE2-S1 NEBV-Z4WA2L-P-E-5-N-LE2-S1 NEBV-Z4WA2L-P-E-10-N-LE2-S1 KMYZ-4-24-0.5-B KMYZ-4-24-2.5-B NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1 NEBV-Z4WA2L-P-E-2.5-N-M8G3-S1
39 39 39	valves with 2-pin plug)         2-pin socket,         Open cable end 2-wire         2-pin socket, plug M8x1 3-pin	PUR cable, degree of protec- tion IP65 PVC cable, degree of protection IP40 PUR cable, degree of protec-	Signal status indica- tion with LED Without signal status indication Signal status indica-	Length 5 m Length 10 m Length 0.5 m Length 2.5 m Length 0.5 m	8047671 8047672 8047670 193690 193691 8047673	Datasheets → Internet:           NEBV-Z4WA2L-P-E-2.5-N-LE2-S1           NEBV-Z4WA2L-P-E-5-N-LE2-S1           NEBV-Z4WA2L-P-E-10-N-LE2-S1           KMYZ-4-24-0.5-B           KMYZ-4-24-2.5-B           NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1

Ordering data				Part no.	Туре
DIN rail mounting					
	For manifold block				CPV10/14-VI-BG-NRH-35
DIN rail					
	To EN 60715		2 m	35430	NRH-35-2000
Silencer					Datasheets → Internet: uc
	With threaded connection	G1/8	1 piece	161419	UC-1/8
			50 pieces	534219	UC-1/8-50
		G1/4	1 piece	165004	UC-1/4
			20 pieces	534220	UC-1/4-20
Push-in fitting					Datasheets → Internet: qs
<u>a</u>	Male thread G1/8 with external hex for tubing O.D.	6 mm	Pack of 10	186096	QS-G1/8-6
			100 pieces	132037	QS-G1/8-6-100
		8 mm	Pack of 10	186098	QS-G1/8-8
			50 pieces	132038	QS-G1/8-8-50
	Male thread G1/4 with external hex for tubing O.D.	8 mm	Pack of 10	186099	QS-G1/4-8
			50 pieces	132040	QS-G1/4-8-50
		10 mm	Pack of 10	186101	QS-G1/4-10
			50 pieces	132041	QS-G1/4-10-50
	Male thread G1/8 with external hex, push-in L-fitting	6 mm	Pack of 10	186117	QSL-G1/8-6
	rotatable 360°, for tubing O.D.		100 pieces	132049	QSL-G1/8-6-100
		8 mm	Pack of 10	186119	QSL-G1/8-8
			50 pieces	132050	QSL-G1/8-8-50
	Male thread G1/4 with external hex, push-in L-fitting	8 mm	Pack of 10	186120	QSL-G1/4-8
	rotatable 360°, for tubing O.D.		50 pieces	132052	QSL-G1/4-8-50
		10 mm	Pack of 10	186122	QSL-G1/4-10
			50 pieces	132053	QSL-G1/4-10-50
Blanking plug					
	For G1/8 thread		Pack of 10	3568	B-1/8
(0)	For G1/4 thread		Pack of 10	3569	B-1/4
Inscription label					
	For solenoid valve		80 pieces in a frame	197259	MH-BZ-80X

# Peripherals overview - Individual valve

Connection with plug vanes - Connection with moulded-in cable



Designation Type		Туре	Description	→ Page/Internet
[1]	Individual valve	MHE4	With plug vanes	90
[2]	Individual valve	MHE4K	With moulded-in cable, IP65	90
[3]	Plug socket	MSSD-EB-S-M14	With insulation displacement connector	91
[4]	Plug socket with cable	KMEB-1	PVC cable, with or without LED	91
[5]	Plug socket with cable	KMEB-2	With LED, without LED; PUR cable, with or without LED	91
[6]	Plug socket	MSSD-EB	With clamping screw	91
[7]	Mounting bracket	MHE2-BG-L	For wall mounting	91
[8]	Push-in fittings	QS	For connecting tubing with standard O.D.	91
[9]	Silencer	UC	For mounting in exhaust ports	91

### Solenoid valves MHE4, fast-switching valves

# Datasheet – Individual valve





#### General technical data

General technical data		
Valve function		3/2 way, single solenoid <sup>1)</sup>
Design		Pressure relief poppet valve
Overlap		Negative overlap
Sealing principle		Soft
Reset method		Mechanical spring
Actuation type		Electrical
Type of control		Direct
Flow direction		Reversible with restrictions <sup>2</sup> )
Exhaust air function		Can be throttled
Manual override		Non-detenting
Mounting position		Any
Width	[mm]	18
Grid dimension	[mm]	24
Note on grid dimension		Minimum distance between the valves is 6 mm
Nominal width	[mm]	4
Standard nominal flow rate	[l/min]	400
Type of mounting		Via through-hole
Pneumatic connection		Connecting thread G1/4
		Push-in connector for tubing O.D. 8 mm
Product weight	[g]	270

Can be used as a 2/2-way valve by sealing port 3 or 33
 Slight leakage can occur in the pressure range -0.8 bar to +0.5 bar.

### Datasheet - Individual valve

#### Operating and environmental conditions

			With fast-switching electronics	Without fast-switching electronics			
Operating medium			Compressed air to ISO 8573-1:2010 [	7:4:4]			
Note on the operating/pilot medium			Lubricated operation possible (in white	ch case lubricated operation will always be required)			
Operating pressure		[MPa]	-0.09 +0.8				
		[bar]	-0.9 +8				
		[psi]	-13.05 +116				
	Reversible	[MPa]	-0.09 +0.1				
		[bar]	-0.9 +1				
		[psi]	-13.05 +14.5				
Ambient temperature		[°C]	-5 +60				
Temperature of medium		[°C]	-5 +60				
Corrosion resistance class CRC <sup>1)</sup>			2				
CE marking (see declaration of conformity) <sup>3)</sup>			To EU EMC Directive <sup>2</sup> )	-			
			To EU RoHS Directive	-			
UKCA marking (see declaration of conformity) <sup>3)</sup>			To UK EMC regulations	-			
			To UK RoHS regulations	-			
Certification			c UL us - Recognized (OL)	c UL us - Recognized (OL)			
			RCM	-			
Cleanroom class			Class 6 to ISO 14644-1				
Shock resistance			Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27				
Vibration resistant			Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6				

1) More information www.festo.com/x/topic/crc

For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads. 2)

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) More information www.festo.com/catalogue/...  $\rightarrow$  Support/Downloads.

#### Electrical data

		With fast-switching electronics	Without fast-switching electronics
Electrical connection		Plug, 2-pin or cable	
Operating voltage	[V DC]	24	
Permissible voltage fluctuations	[%]	±10	
Power consumption	[W]	8.5 (high-current phase)	5.6
	[W]	2.125 (low-current phase)	-
Reverse polarity protection		Bipolar	-
Duty cycle	[%]	100	100
Additional functions		Spark arresting	-
		Holding current reduction	-
		Protective circuit	-
Degree of protection to EN 60529		IP65	IP65

#### Switching times and frequencies

		-	With fast-switching electronics	Without fast-switching electronics
Switching time	On	[ms]	3.5	10.5
	Off	[ms]	3.5	5
Tolerance for switching time	On	[%]	+1030	-
	Off	[%]	+1040	-
Switching time variation from 1 Hz upwards		[ms]	0.3	-
Maximum switching frequency		[Hz]	210	120

Materials	
Housing	Die-cast zinc, coated
Cable sheath	PUR
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

### Solenoid valves MHE4, fast-switching valves

# Datasheet – Individual valve

#### Current curve for valves with fast-switching electronics (MHE4-MS1H)



**—** — — Internal current in the coil

External current in the supply line

- [1] Capacitor charging
- [2] Controlled coil current 1 A
- [3] Holding current reduction
- [4] Controlled holding current 0.5 A

### Datasheet - Individual valve



Туре	B1	D1	D2 Ø	D3 Ø	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8	L9
MHE41/4	18	G1/4	-	4.5	56	-	48	32	114.6	56	29	28	13	20	19	29	0.8
MHE4QS-8	18	-	8	4.5	52	62.4	48	32	114.6	56	29	28	13	20	19	29	0.8

### Solenoid valves MHE4, fast-switching valves

# Datasheet – Individual valve



# Solenoid valves MHE4, fast-switching valves

# Datasheet – Individual valve

Ordering data						
					Part no.	Туре
Valves						
	Electrical connec-	With fast-switching	Pneumatic connection: thread	Normally open	525207	MHE4-MS1H-3/20-1/4
	tion: plug, 2-pin	electronics, switching	G1/4	Normally closed	525187	MHE4-MS1H-3/2G-1/4
		time 3.5 ms	Pneumatic connection: push-	Normally open	525211	MHE4-MS1H-3/20-QS-8
			in connector for tubing O.D.	Normally closed	525191	MHE4-MS1H-3/2G-QS-8
			8 mm			
	Without fast-switchingPneumatic connection: the electronics, switchingG1/4		Pneumatic connection: thread	Normally open	525206	MHE4-M1H-3/20-1/4
			G1/4	Normally closed	525186	MHE4-M1H-3/2G-1/4
		time 10.5 ms	Pneumatic connection: push-	Normally open	525210	MHE4-M1H-3/20-QS-8
			in connector for tubing O.D.	Normally closed	525190	MHE4-M1H-3/2G-QS-8
			8 mm			
	Electrical connec-	With fast-switching	Pneumatic connection: thread	Normally closed	525189	MHE4-MS1H-3/2G-1/4-K
A DE D	tion: cable	electronics, switching	G1/4			
0 2021		time 3.5 ms	Pneumatic connection: push-	Normally open	525213	MHE4-MS1H-3/20-QS-8-K
<b> </b> <sup>≁</sup>			in connector for tubing O.D.	Normally closed	525193	MHE4-MS1H-3/2G-QS-8-K
			8 mm			
		Without fast-switching	Pneumatic connection: thread	Normally open	525208	MHE4-M1H-3/20-1/4-K
		electronics, switching	G1/4	Normally closed	525188	MHE4-M1H-3/2G-1/4-K
		time 10.5 ms				

# Datasheet – Individual valve

	a valves with 2-pin plug) 3-pin socket, Open cable end 3-wire Signal status indication with LED 4-pin socket, Open cable end 3-wire Signal status indication with LED	PVC cable, degree c IP65	f protection	length 2.5 m	Part no.	Туре КМЕВ-1-24-2.5-LED			
	3-pin socket, Open cable end 3-wire Signal status indication with LED 4-pin socket, Open cable end 3-wire		of protection	Length 2.5 m	151(00				
	Open cable end 3-wire Signal status indication with LED 4-pin socket, Open cable end 3-wire								
Das-Call	4-pin socket, Open cable end 3-wire			Length 5 m	151689	KMEB-1-24-5-LED			
1 Sur	Open cable end 3-wire			Length 10 m	193457	KMEB-1-24-10-LED			
		PUR cable, degree	of protection	Length 2.5 m	174844	KMEB-2-24-2.5-LED			
19/1/	Signal status indication with LED	IP65		Length 5 m	174845	KMEB-2-24-5-LED			
	Signal status multation with LED								
	5-pin socket, plug M12 5-pin Signal status indication with LED	Cable sheath TPE-U protection IP65	(PU), degree of	Length 0.5 m	177677	KMEB-2-24-M12-0.5-LED			
Plug socket (for valves wit	th 2-pin plug)								
1	Angled socket,	Screw terminal		3-pin	151687	MSSD-EB			
	Without signal status indication	Degree of protection	n IP65						
$\bigvee$		Insulation displace Degree of protectio		4-pin	192745	MSSD-EB-S-M14			
Illuminating seal	For mounting between plug socket (with	out cignal status indi	(cation) and value		151717	MEB-LD-12-24DC			
	For mounting between plug socket (with	iout signal status indi	cation) and valve		151/1/	MEB-LU-12-24UC			
Wellmeuntine									
Wall mounting	Mounting bracket				196165	MHE2-BG-L			
1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	mounting blacket				190105	WITE2*DU*L			
Silencer						Datasheets → Internet: u			
I	Push-in sleeve	Screwed plug	8 mm	Pack of 1	175611	UC-QS-8H			
		PE	-						
	Threaded connection, polymer design	Screwed plug G1/4 PE G1/4		1 piece	165004	UC-1/4			
				20 pieces	534220	UC-1/4-20			
Push-in fitting				1		Datasheets → Internet: q			
	Male thread with external hex	G1/4	8 mm	Pack of 10	186099	QS-G1/4-8			
				50 pieces	132040	QS-G1/4-8-50			
			10 mm	Pack of 10	186101	QS-G1/4-10			
				50 pieces	132041	QS-G1/4-10-50			
	Push-in L-fitting, rotatable through	G1/4	8 mm	Pack of 10	186120	QSL-G1/4-8			
	360°, male thread with external hex			50 pieces	132052	QSL-G1/4-8-50			
-			10 mm	Pack of 10	186122	QSL-G1/4-10			
				50 pieces	132053	QSL-G1/4-10-50			
Blanking plug									
	For G1/4 thread			3569	B-1/4				
Inscription label				1					
	For solenoid valve			80 piece	197259	MH-BZ-80X			

# Peripherals overview - Semi in-line valve

Connection via plug vanes



Desig	nation	Туре	Description	→ Page/Internet
[1]	Semi-in-line valve	MHP4	With plug vanes	98
[2]	Plug socket with cable	KMEB-2	PUR cable, with or without LED	99
[3]	Plug socket	MSSD-EB	With clamping screw	99
[4]	Plug socket	MSSD-EB-S-M14	With insulation displacement connectors	99
[5]	Plug socket with cable	KMEB-1	PVC cable, with or without LED	99
[6]	Push-in fittings	QS	For connecting tubing with standard O.D.	100
[7]	Cover plate	MHAP4-BP-3	For sealing vacant positions	98
[8]	Blanking plug	В	For sealing unused ports	100
[9]	Inscription labels	MH-BZ-80X	For identifying the valves	100
[10]	DIN rail mounting	CPV10/14-VI-BG-NRH-35	For mounting the manifold block on DIN rails to EN 60715	99
[11]	Silencer	UC	For mounting in exhaust ports	100
[12]	Individual sub-base	MHA4-AS-3-1/4	For semi in-line valves; the individual sub-base is also used for sub-base valves; the extra connection must be sealed with a plug here	98
[13]	Manifold block	MHA4-PR1/4	For semi in-line valves	98

### Solenoid valves MHP4, fast-switching valves

# Datasheet – Semi in-line valve



#### General technical data

General technical aata			
Valve function			3/2 way, single solenoid <sup>1)</sup>
Design			Pressure relief poppet valve
Overlap			Negative overlap
Sealing principle			Soft
Reset method			Mechanical spring
Actuation type			Electrical
Type of control			Direct
Flow direction			Reversible with restrictions <sup>2)</sup>
Exhaust air function			Can be throttled
Manual override			Non-detenting
Mounting position			Any
Width		[mm]	18
Grid dimension		[mm]	24
Note on grid dimension			Minimum distance between the valves is 6 mm
Nominal width		[mm]	4
Standard nominal flow rate		[l/min]	400
Type of mounting			On PR rail
Pneumatic connection	2		Connecting thread G1/4, push-in connector for tubing O.D. 8 mm
	1, 11, 3, 33		Sub-base
Product weight		[g]	270

Can be used as a 2/2-way valve by sealing port 3 or 33
 Slight leakage can occur in the pressure range -0.8 bar to +0.5 bar.

### Datasheet – Semi in-line valve

#### Operating and environmental conditions

			With fast-switching electronics	Without fast-switching electronics	
Operating medium			Compressed air to ISO 8573-1:2010 [	7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in white	ch case lubricated operation will always be required)	
Operating pressure		[MPa]	-0.09 +0.8		
		[bar]	-0.9 +8		
		[psi]	-13.05 +116		
	Reversible	[MPa]	-0.09 +0.1		
		[bar]	-0.9 +1		
		[psi]	-13.05 +14.5		
Ambient temperature		[°C]	-5 +40		
Temperature of medium		[°C]	-5 +40		
Corrosion resistance class CRC <sup>1)</sup>			2		
CE marking (see declaration of conformity) <sup>3)</sup>			To EU EMC Directive <sup>2</sup> )	-	
			To EU RoHS Directive	-	
UKCA marking (see declaration of conformity) <sup>3)</sup>			To UK EMC regulations	-	
			To UK RoHS regulations	-	
Certification			c UL us - Recognized (OL)	c UL us - Recognized (OL)	
			RCM	-	
Cleanroom class			Class 6 to ISO 14644-1		
Shock resistance			Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27		
Vibration resistant			Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6		

1) More information www.festo.com/x/topic/crc

For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 -> Support/Downloads. 2)

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) More information www.festo.com/catalogue/...  $\rightarrow$  Support/Downloads.

#### Electrical data

		With fast-switching electronics	Without fast-switching electronics
Electrical connection		Plug, 2-pin	
Operating voltage	[V DC]	24	
Permissible voltage fluctuations	[%]	±10	
Power consumption	[W]	8.5 (high-current phase)	5.6
	[W]	2.125 (low-current phase)	-
Reverse polarity protection		Bipolar	-
Duty cycle	[%]	100	100
Additional functions		Spark arresting	-
		Holding current reduction	-
		Protective circuit	-
Degree of protection to EN 60529		IP65	IP65

#### Switching times and frequencies

		-	With fast-switching electronics	Without fast-switching electronics
Switching time	On	[ms]	3.5	10.5
	Off	[ms]	3.5	5
Tolerance for switching time	On	[%]	+1030	-
	Off	[%]	+1040	-
Switching time variation from 1 Hz upwards		[ms]	0.3	-
Maximum switching frequency		[Hz]	210	120

Materials		
Housing	Die-cast zinc, coated	
Seals	HNBR, NBR	-
Screws	Galvanised steel	
Note on materials	RoHS-compliant	
LABS (PWIS) conformity	VDMA24364-B1/B2-L	

### Datasheet - Semi in-line valve



### Datasheet – Semi in-line valve

#### Dimensions



#### Download CAD data → <u>www.festo.com</u>

- 🏺 - Note

With semi in-line valves, port 2 is not used. If used as a 2/2-way valve, normally closed, ports 3/11 are not used. If used as a 2/2-way valve, normally open, ports 1/33 are not used.

#### Individual sub-base, MHA4-AS-3-1/4







H5

#### [1] Plug pins

[2] Silencer

[3] Push-in fitting

Туре	B1	B2	B3	Β4	B5	B6	D1	D2 Ø	D3 Ø	H1	H2	H3	H4	H5
Hole pattern	-	-	-	-	-	-	6	5.2	M4	43.3	34	8.8	10	7.7
MHA4-AS-3-1/4	36	14.8	6	12.3	42.5	20.5	G1/4	5.5	10	31	27.5	14.3	11.4	75.8
Туре	L1		L2	L:	3	L4		.5	L6		L7	L8		T1
Hole pattern	22.5	5	5	-		-		-	-		-	-		-
MHA4-AS-3-1/4	99		55.8	2	4	67.8	2	1.9	17.8		22.4	115.4		21.8

### Datasheet - Semi in-line valve

#### Dimensions Manifold assembly, MHA4-PR...-1/4

Download CAD data → <u>www.festo.com</u>









[1] Connection block

[2] DIN mounting rail

Туре	B1	B2	B3	B4	B5	B6	B7	D1	D2 Ø	D3 Ø	H1	H2	H3	H4	H5	H6	L4	L5	L6	T1	T2
MHA4-PR1/4	99	55.8	24	47.8	25	5.3	114.6	G3/8	5.5	10	42	17	12	55	77	96.5	21	24	8	23	12
CPV10/14-VI-BG	49.1	110	-	-	-	-	-	-	-	-	10.7	42	-	-	-	-	6.5	-	-	-	-

Туре		No. of valve positions	No. of valve positions								
		2	4	6	8	10					
MHA4-PR1/4	L1	66	114	162	210	258					
	L2	50	98	146	194	242					
	L3	24	72	120	168	216					
CPV10/14-VI-BG	L2	53	101	149	197	245					

### - 🗍 - Note

Valve types 3/2G and 3/2O must not be mixed on one manifold block.

### Solenoid valves MHP4, fast-switching valves

## Datasheet – Semi in-line valve

					Part no.	Туре
alves						
	Electrical connec-	With fast-switching elec-	Pneumatic connection: thread	Normally open	525199	MHP4-MS1H-3/20-1/4
90 1	tion: plug, 2-pin	tronics, switching time	G1/4	Normally closed	525179	MHP4-MS1H-3/2G-1/4
8		3.5 ms	Pneumatic connection: push- in connector for tubing O.D. 8 mm	Normally closed	525183	MHP4-MS1H-3/2G-QS-8
		Without fast-switching	Pneumatic connection: thread	Normally open	525198	MHP4-M1H-3/20-1/4
		electronics, switching time 10.5 ms	G1/4	Normally closed	525178	MHP4-M1H-3/2G-1/4
Aanifold rail	Individual sub-bas Pneumatic connec			1 valve position	525227	MHA4-AS-3-1/4
	Manifold block <sup>1)</sup>			2 valve positions	525234	MHA4-PR2-3-1/4
		tion 1, 11, 3, 33: thread G	3/8	4 valve positions	525235	MHA4-PR4-3-1/4
	Pneumatic connec	tion 2: thread G1/4		6 valve positions	525236	MHA4-PR6-3-1/4
				8 valve positions	525237	MHA4-PR8-3-1/4
				10 valve positions	525238	MHA4-PR10-3-1/4
Cover plate						
	Vacant valve posit	ions must be sealed with a	cover plate.		525239	MHAP4-BP-3

1) Seal port 2 with a blanking plug. These ports have no function when using semi in-line valves.

- **Note** Valve types 3/2G and 3/20 must not be mixed on one manifold block.

# Datasheet – Semi in-line valve

				Part no.	Туре
lug socket with ca	ble				
AP	3-pin socket,	PVC cable, degree of protection	Length 2.5 m	151688	KMEB-1-24-2.5-LED
	Open cable end 3-wire	IP65	Length: 5 m	151689	KMEB-1-24-5-LED
$\checkmark$	Signal status indication with LED		Length: 10 m	193457	KMEB-1-24-10-LED
<u>M</u>	4-pin socket,	PUR cable, degree of protection	Length 2.5 m	174844	KMEB-2-24-2.5-LED
	Open cable end 3-wire	IP65	Length: 5 m	174845	KMEB-2-24-5-LED
Ë	Signal status indication with LED				
	5-pin socket, plug M12 5-pin	Cable sheath TPE-U (PU), degree of	Length: 0.5 m	177677	KMEB-2-24-M12-0.5-LED
The second	Signal status indication with LED	protection IP65			
r 🖏 🗌					
•					
lug socket					
	Angled socket,	Screw terminal	3-pin	151687	MSSD-EB
TP .	Without signal status indication	Degree of protection IP65			
$\downarrow$		Insulation displacement technology	4-pin	192745	MSSD-EB-S-M14
		Degree of protection IP67			
luminating seal					
	For mounting between plug socket (wi	thout signal status indication) and valve		151717	MEB-LD-12-24DC
IN rail mounting					
<u>v</u>	For manifold block			162556	CPV10/14-VI-BG-NRH-35
	11				
IN rail					
Ron	To EN 60715		2 m	35430	NRH-35-2000
17.01					

# Solenoid valves MHP4, fast-switching valves

# Datasheet – Semi in-line valve

Ordering data						
					Part no.	Туре
Silencer						Datasheets → Internet: u
	Push-in sleeve	Screwed plug PE	8 mm	Pack of 1	175611	UC-QS-8H
	Threaded connection, polymer design	Screwed plug	G1/4	1 piece	165004	UC-1/4
		PE		20 pieces	534220	UC-1/4-20
		Housing	G3/8	1 piece	2309	U-3/8
		Polyacetal		20 pieces	534224	U-3/8-20
Push-in fitting						Datasheets → Internet: q
	Male thread with external hex	G1/4	8 mm	Pack of 10	186099	QS-G1/4-8
				50 pieces	132040	QS-G1/4-8-50
			10 mm	Pack of 10	186101	QS-G1/4-10
				50 pieces	132041	QS-G1/4-10-50
		G3/8	10 mm	Pack of 10	186102	QS-G3/8-10
				50 pieces	132044	QS-G3/8-10-50
			12 mm	Pack of 10	186103	QS-G3/8-12
				20 pieces	132045	QS-G3/8-12-20
	Push-in L-fitting, rotatable through	G1/4	8 mm	Pack of 10	186120	QSL-G1/4-8
	360°, male thread with external hex			50 pieces	132052	QSL-G1/4-8-50
			10 mm	Pack of 10	186122	QSL-G1/4-10
				50 pieces	132053	QSL-G1/4-10-50
		G3/8	10 mm	Pack of 10	186123	QSL-G3/8-10
				20 pieces	132056	QSL-G3/8-10-20
			12 mm	Pack of 10	186124	QSL-G3/8-12
				20 pieces	132057	QSL-G3/8-12-20
Blanking plug						
	For G1/4 thread			Pack of 10	3569	B-1/4
O)	For G3/8 thread					B-3/8
Inscription label						
	For solenoid valve			80 piece	197259	MH-BZ-80X

# Peripherals overview – Sub-base valve

### Connection with plug vanes - Connection with moulded-in cable



Desigr	Designation Type		Description	→ Page/Internet
[1]	Sub-base valves MHA4		With plug vanes	108
[2]	Sub-base valves	МНА4К	With moulded-in cable, IP65	108
[3]	Plug socket	MSSD-EB-S-M14	With insulation displacement connectors	109
[4]	Plug socket with cable	KMEB-1	PVC cable, with or without LED	109
[5]	Plug socket with cable	KMEB-2	PUR cable, with or without LED	109
[6]	Plug socket	MSSD-EB	With clamping screw	109
[7]	Cover plate	MHAP4-BP-3	For sealing vacant positions	108
[8]	Blanking plug	В	For sealing unused ports	110
[9]	Inscription labels	MH-BZ-80X	For identifying the valves	110
[10]	DIN rail mounting	CPV10/14-VI-BG-NRH-35	For mounting the manifold block on DIN rails to EN 60715	109
[11]	Push-in fittings	QS	For connecting tubing with standard O.D.	110
[12]	Silencer	UC	For mounting in exhaust ports	110
[13]	Individual sub-base	MHA4-AS-3-1/4	For sub-base valves	108
[14]	Manifold block	MHA4-PR1/4	For sub-base valves	108

### Solenoid valves MHA4, fast-switching valves

### Datasheet - Sub-base valve









#### General technical data

Valve function			3/2 way, single solenoid <sup>1)</sup>
Design			Pressure relief poppet valve
Overlap			Negative overlap
Sealing principle			Soft
Reset method			Mechanical spring
Actuation type			Electrical
Type of control			Direct
Flow direction			Reversible with restrictions <sup>2)</sup>
Exhaust air function			Can be throttled
Manual override			Non-detenting
Mounting position			Any
Width		[mm]	18
Grid dimension		[mm]	24
Note on grid dimension			Minimum distance between the valves is 6 mm
Nominal width		[mm]	4
Standard nominal flow rate		[l/min]	400
Type of mounting			On PR rail
Pneumatic connection	1, 11, 2, 3, 33		Sub-base
Product weight		[g]	270

1) Can be used as a 2/2-way valve by sealing port 3 or 33

2) Slight leakage can occur in the pressure range –0.8 bar to +0.5 bar.

# Datasheet – Sub-base valve

#### Operating and environmental conditions

			With fast-switching electronics	Without fast-switching electronics				
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)					
Operating pressure		[MPa]	[MPa] -0.09 +0.8					
		[bar]	-0.9 +8					
		[psi]	-13.05 +116					
	Reversible	[MPa]	-0.09 +1					
		[bar]	-0.9 +1					
		[psi]	-13.05 +14.5					
Ambient temperature		[°C]	-5 +40					
Temperature of medium		[°C]	-5 +40					
Corrosion resistance class CRC <sup>1)</sup>			2					
CE marking (see declaration of conformity) <sup>3)</sup>			To EU EMC Directive <sup>2</sup> )	-				
			To EU RoHS Directive	-				
UKCA marking (see declaration of conformity) <sup>3)</sup>			To UK EMC regulations	-				
			To UK RoHS regulations	-				
Certification			c UL us - Recognized (OL)	c UL us - Recognized (OL)				
			RCM	-				
Cleanroom class			Class 6 to ISO 14644-1					
Shock resistance	Shock resistance			Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27				
Vibration resistant	Vibration resistant			Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6				

1) More information www.festo.com/x/topic/crc

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/mh2 → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

3) More information www.festo.com/catalogue/...  $\rightarrow$  Support/Downloads.

#### Electrical data

		With fast-switching electronics	Without fast-switching electronics
Electrical connection		Plug, 2-pin or cable	
Operating voltage	[V DC]	24	
Permissible voltage fluctuations	[%]	±10	
Power consumption	[W]	8.5 (high-current phase)	5.6
	[W]	2.125 (low-current phase)	-
Reverse polarity protection		Bipolar	-
Duty cycle	[%]	100	100
Additional functions		Spark arresting	-
		Holding current reduction	-
		Protective circuit	-
Degree of protection to EN 60529		IP65	IP65

#### Switching times and frequencies

			With fast-switching electronics	Without fast-switching electronics
Switching time	On	[ms]	3.5	10.5
	Off	[ms]	3.5	5
Tolerance for switching time	On	[%]	+1030	-
	Off	[%]	+1040	-
Switching time variation from 1 Hz upwards		[ms]	0.3	-
Maximum switching frequency		[Hz]	210	120

Materials

Housing	Die-cast zinc, coated
Cable sheath	PUR
Seals	HNBR, NBR
Screws	Galvanised steel
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

1

### Current curve for valves with fast-switching electronics (MHA4-MS1H)



---- Internal current in the coil

- External current in the supply line

### Dimensions

Valve with plug vanes or moulded-in cable, MHA4-...-3/2...



- [1] Capacitor charging
   [2] Controlled coil current 1 A
- [3] Holding current reduction
- [4] Controlled holding current 0.5 A

#### Download CAD data → <u>www.festo.com</u>

### Dimensions

Download CAD data  $\rightarrow$  <u>www.festo.com</u>



<sup>[1]</sup> Hole for coding pin, 2.5mm deep [2] Mounting thread, 13 mm deep

Туре	D1	D2 Ø	D3 Ø	H1	H2	H3	H4	H5	L1	L2
Hole pattern	6	5.2	M4	43.3	34	8.8	10	7.7	22.5	5

#### Dimensions

Download CAD data → <u>www.festo.com</u>



### Dimensions

Download CAD data → <u>www.festo.com</u>



### Solenoid valves MHA4, fast-switching valves

# Datasheet – Sub-base valve

Ordering data			1	Part no.	Туре
Valves					.,,,,
	Electrical connection: plug, 2-pin	With fast-switching electronics,     Normally closes       switching time 3.5 ms		525175	MHA4-MS1H-3/2G-4
		Without fast-switching electronics, switching time 10.5 ms	Normally closed	525174	MHA4-M1H-3/2G-4
	Electrical connection: cable	With fast-switching electronics, switching time 3.5 ms	Normally closed	525177	MHA4-MS1H-3/2G-4-K
		Without fast-switching electronics,	Normally open	525196	MHA4-M1H-3/20-4-K
₹ <b>₩</b>		switching time 10.5 ms	Normally closed	525176	MHA4-M1H-3/2G-4-K
		Individual sub-base Pneumatic connection: thread G1/4			MHA4-AS-3-1/4
	Manifold block		2 valve positions	525234	MHA4-PR2-3-1/4
	Pneumatic connection 1, 11, 3		4 valve positions	525235 525236	MHA4-PR4-3-1/4
	Pheumatic connection 2: threa	Pneumatic connection 2: thread G1/4 6 V			MHA4-PR6-3-1/4
			8 valve positions	525237	MHA4-PR8-3-1/4
			10 valve positions	525238	MHA4-PR10-3-1/4
Cover plate					
	Vacant valve positions must be sealed with a cover plate.			525239	MHAP4-BP-3

- 🌡 - Note

Valve types 3/2G and 3/20 must not be mixed on one manifold block.

				Part no.	Туре
Plug socket with cat	ole (for valves with 2-pin plug)				
R	3-pin socket,	PVC cable, degree of protection		151688	KMEB-1-24-2.5-LED
	Open cable end 3-wire	IP65	Length 5 m	151689	KMEB-1-24-5-LED
$\checkmark$	Signal status indication with LED		Length 10 m	193457	KMEB-1-24-10-LED
	4-pin socket,	PUR cable, degree of protection	Length 2.5 m	174844	KMEB-2-24-2.5-LED
A Start	Open cable end 3-wire Signal status indication with LED	IP65	Length 5 m	174845	KMEB-2-24-5-LED
	5-pin socket, plug M12 5-pin Signal status indication with LED	Cable sheath TPE-U (PU), degree of protection IP65	Length 0.5 m	177677	KMEB-2-24-M12-0.5-LED
Plug socket (for valv	es with 2-pin plug)				
$\mathbf{P}$	Angled socket, Without signal status indication	Screw terminal Degree of protection IP65	3-pin	151687	MSSD-EB
		Insulation displacement technology Degree of protection IP67	4-pin	192745	MSSD-EB-S-M14
Illuminating seal					
	For mounting between plug socket (without signal status indication) and valve			151717	MEB-LD-12-24DC
DIN rail mounting				·	
	For manifold block	162556	CPV10/14-VI-BG-NRH-35		
DIN rail					
Jel .	To EN 60715		2 m	35430	NRH-35-2000

### Solenoid valves MHA4, fast-switching valves

# Datasheet – Sub-base valve

Ordering data						
					Part no.	Туре
Silencer						Datasheets → Internet: u
	Push-in sleeve	Screwed plug PE	8 mm	Pack of 1	175611	UC-QS-8H
	Threaded connection, polymer design	Screwed plug PE	G1/4	1 piece	165004	UC-1/4
				20 pieces	534220	UC-1/4-20
		Housing	G3/8	1 piece	2309	U-3/8
		POM		20 pieces	534224	U-3/8-20
Push-in fitting						Datasheets → Internet: q
	Male thread with external hex	G1/4	8 mm	Pack of 10	186099	QS-G1/4-8
				50 pieces	132040	QS-G1/4-8-50
			10 mm	Pack of 10	186101	QS-G1/4-10
				50 pieces	132041	QS-G1/4-10-50
		G3/8	10 mm	Pack of 10	186102	QS-G3/8-10
				50 pieces	132044	QS-G3/8-10-50
			12 mm	Pack of 10	186103	QS-G3/8-12
				20 pieces	132045	QS-G3/8-12-20
	Push-in L-fitting, rotatable through 360°, male thread with external hex		8 mm	Pack of 10	186120	QSL-G1/4-8
				50 pieces	132052	QSL-G1/4-8-50
			10 mm	Pack of 10	186122	QSL-G1/4-10
				50 pieces	132053	QSL-G1/4-10-50
		G3/8	10 mm 12 mm	Pack of 10	186123	QSL-G3/8-10
				20 pieces	132056	QSL-G3/8-10-20
				Pack of 10	186124	QSL-G3/8-12
				20 pieces	132057	QSL-G3/8-12-20
Blanking plug						
	For G1/4 thread			Pack of 10	3569	B-1/4
$\bigcirc)$	For G3/8 thread		Pack of 10	3570	B-3/8	
Inscription label						
	For colonaid up ha			00	107250	
	For solenoid valve			80 piece	197259	MH-BZ-80X