

Mini slide DGSS

FESTO



Characteristics

At a glance

[Link dgss](#)


- Compact drive
- Optimum price/performance ratio
- Slide and yoke plate as a single component
- Excellent positioning accuracy
- Precise and resilient rolling bearing guide
- Operation possible without additional cushioning elements.
- Optional: stroke adjustment and external cushioning using accessories
- Very flexible thanks to wide choice of mounting and attachment options
- Simple design thanks to symmetrical mounting interface

Diagrams

[Link dgss](#)


The diagrams shown in this document are also available online. These can be used to display precise values.

Overview



External cushioning via accessories:

- [1] Shock absorber DYEF/DYSS
- [2] Stop kit DADP-...-F
- [3] Stop kit DADP-...-R (stop kit DADP-...-F included in the scope of delivery)

Cushioning

End-position cushioning has the following functions:

- Reduces kinetic energy in the end positions
- Avoids vibrations
- Reduces noise generation

Operation possible without additional cushioning elements.

Can be operated with external cushioning components:

- Higher permissible energy (effective load and speed)
- Reduced cycle times
- Easy stroke reduction possible from one side
- Precision end-position adjustment

[E1] Elastomer cushioning, double-sided, stroke not adjustable

- Standard design
- Internal cushioning, without stroke adjustment
- Elastic cushioning
- For lower cushioning energy
- Without metal fixed stop

[P] Elastic cushioning rings/plates on both sides

- External cushioning via shock absorber DYEF-G8-...-Y1, with stroke adjustment
- Elastic cushioning
- For medium cushioning energy
- Stroke reduction to the next smaller stroke is possible
- Without metal fixed stop
- Available from stroke 10 mm

Characteristics


[P1]	Elastomer cushioning, adjustable on both sides, with fixed stop	[E]	Elastomer cushioning, short, on both sides
• External cushioning via shock absorber DYEF-G8-...-Y1F, with stroke adjustment • Elastic cushioning • For low to mid-range cushioning energies • Stroke reduction to the next smaller stroke is possible • With metal fixed stop for a very precise end position • Available from stroke 10 mm		• External cushioning via shock absorber DYEF-G8-S-...-Y1, with stroke adjustment • Elastic cushioning • For medium cushioning energy • Stroke reduction, space-saving • Without metal fixed stop • Available from stroke 10 mm	
[Y12]	Shock absorber, self-adjusting, linear at both ends, external		
• External cushioning via shock absorber DYSS-G8-...-Y1F, with stroke adjustment • Hydraulic cushioning • For high cushioning energy • Stroke reduction to the next smaller stroke is possible • With metal fixed stop for a very precise end position • Available from stroke 10 mm			

Position sensing

[A] For proximity sensor

By using proximity switches, any position can be detected.

Application example



With the centring sleeves ABAZ, several mini slides can be easily mounted next to each, thus saving space. That is also how the required distance to the proximity switches is maintained and trouble-free function is guaranteed.

Type code

001	Series	
DGSS	Mini slide	
002	Size [mm]	
6	6	
10	10	
16	16	
20	20	

003	Stroke [mm]	
5	5	
10	10	
15	15	
20	20	
25	25	
30	30	
40	40	
50	50	
60	60	

004	Cushioning	
E1	Elastomer cushioning, double-sided, stroke not adjustable	

005	Position sensing	
A	For proximity sensor	

Datasheet

General technical data				
Size [mm]	6	10	16	20
Piston diameter	6 mm	10 mm	16 mm	20 mm
Stroke	5 mm, 10 mm, 15 mm, 20 mm, 25 mm, 30 mm, 40 mm, 50 mm, 60 mm			
Design	Yoke Piston rod Slide			
Guide	Recirculating ball bearing guide			
Mode of operation	Double-acting			
Type of mounting	With through-hole With female thread			
Pneumatic connection	M3	M5		
Cushioning	Elastomer cushioning, double-sided, stroke not adjustable			
Cushioning length	0.9 mm	1.5 mm	0.65 mm	1 mm
Position detection	Via proximity switch			
Mounting position	Any			
Max. speed ¹⁾	0.5 m/s			
Repetition accuracy ²⁾	<= 0.3 mm			

- 1) DGSS-6 with cushioning -P/-E/-Y12: 0.5 m/s
 DGSS-6 with cushioning -P1: 0.45 m/s
 DGSS-10 ... 20 with cushioning -P/-E/-Y12: 0.8 m/s
 DGSS-10 ... 20 with cushioning -P1: 0.5 m/s
- 2) DGSS-6 ... 20 with cushioning -P/-E: ≤ 0.3 mm
 DGSS-6 ... 20 with cushioning -P1/-Y12: ≤ 0.01 mm

Operating and ambient conditions				
Size [mm]	6	10	16	20
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure ¹⁾	0.15 ... 0.8 MPa	0.1 ... 0.8 MPa		
Operating pressure ²⁾	1.5 ... 8 bar	1 ... 8 bar		
Operating pressure ³⁾	21.75 ... 116 psi	14.5 ... 116 psi		
Ambient temperature	-10 ... 60°C			
Corrosion resistance class CRC ⁴⁾	1 - Low corrosion stress			

- 1) DGSS-6/10: The min. operating pressure may increase slightly after an idle period > 24 h.
 2) DGSS-6/10: The min. operating pressure may increase slightly after an idle period > 24 h.
 3) DGSS-6/10: The min. operating pressure may increase slightly after an idle period > 24 h.
 4) More information www.festo.com/x/topic/kbk

Forces				
Size [mm]	6	10	16	20
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	17 N	47 N	121 N	188 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	13 N	39 N	104 N	158 N

Impact energy				
Size [mm]	6	10	16	20
Impact energy in end positions ¹⁾	0.01 J	0.018 J	0.03 J	0.05 J

- 1) DGSS-6 with cushioning -P/-E: 0.014 J
 DGSS-6 with cushioning -P1: 0.005 J
 DGSS-6 with cushioning -Y12: 0.06 J (energy per stroke)
 DGSS-10 with cushioning -P/-E: 0.06 J
 DGSS-10 with cushioning -P1: 0.02 J
 DGSS-10 with cushioning -Y12: 0.3 J (energy per stroke)
 DGSS-16 with cushioning -P/-E: 0.11 J
 DGSS-16 with cushioning -P1: 0.03 J
 DGSS-16 with cushioning -Y12: 0.58 J (energy per stroke)
 DGSS-20 with cushioning -P/-E: 0.21 J
 DGSS-20 with cushioning -P1: 0.04 J
 DGSS-20 with cushioning -Y12: 1.15 J (energy per stroke)

Datasheet

Impact energy for cushioning -P/-P1/-E/-E1 – Formula

$$V = \sqrt{\frac{2 \cdot E}{m_1 + m_2}}$$

$$m_2 = \frac{2 \cdot E}{v^2} - m_1$$

The specifications represent the maximum values that can be achieved. The maximum permissible impact energy must be observed.

V = permissible impact velocity

E = max. impact energy

m1 = moving mass (drive)

m2 = moving payload

Impact energy for cushioning -Y12 – formula

$$V = \sqrt{\frac{2 \cdot (E - (F + (m_1 + m_2) \cdot g \cdot \sin(\alpha)) \cdot s)}{m_1 + m_2}}$$

$$m_2 = \frac{E - F \cdot s}{\frac{1}{2} \cdot v^2 + g \cdot s \cdot \sin(\alpha)} - m_1$$

The specifications represent the maximum values that can be achieved. The maximum permissible impact energy must be observed.

V = permissible impact velocity

E = kinetic impact energy

F = cylinder force minus friction force

m1 = moving mass (drive)

m2 = moving payload

g = acceleration due to gravity

s = shock absorber stroke (values → DYSS catalogue)

a = angle of impact

v = impact velocity

Weight for DGSS-6

Size [mm]	6								
Stroke	5 mm	10 mm	15 mm	20 mm	25 mm	30 mm	40 mm	50 mm	60 mm
Product weight	64 g	68 g	75 g	80 g	89 g	95 g	107 g	120 g	134 g
Moving mass	27 g	28 g	31 g	32 g	36 g	37 g	41 g	46 g	51 g

Weight for DGSS-10

Size [mm]	10								
Stroke	5 mm	10 mm	15 mm	20 mm	25 mm	30 mm	40 mm	50 mm	60 mm
Product weight	117 g	124 g	134 g	144 g	154 g	164 g	183 g	202 g	222 g
Moving mass	52 g	56 g	59 g	63 g	67 g	71 g	77 g	84 g	92 g

Weights for DGSS-16

Size [mm]	16								
Stroke	5 mm	10 mm	15 mm	20 mm	25 mm	30 mm	40 mm	50 mm	60 mm
Product weight	191 g	202 g	214 g	227 g	241 g	253 g	279 g	306 g	330 g
Moving mass	86 g	92 g	97 g	103 g	109 g	114 g	125 g	137 g	147 g

Weights for DGSS-20


Size [mm]	20								
Stroke	5 mm	10 mm	15 mm	20 mm	25 mm	30 mm	40 mm	50 mm	60 mm
Product weight	379 g	389 g	407 g	432 g	450 g	477 g	513 g	564 g	600 g
Moving mass	156 g	161 g	166 g	179 g	184 g	199 g	209 g	235 g	246 g

Datasheet

Materials

Material cover	Wrought aluminium alloy
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel
Material guide	NBR PA High-alloy steel
Material seals	NBR PU
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)

Dynamic load values



The indicated forces and torques refer to the centre of the guide. They must not be exceeded in dynamic operation. Special attention must be paid to the deceleration process.

The values for the position of the guide centre (H17, L17) can be found in the chapter Dimensions.

Dynamic load values – formula

$$f_v = \frac{|F_{y1}|}{F_{y2}} + \frac{|F_{z1}|}{F_{z2}} + \frac{|M_{x1}|}{M_{x2}} + \frac{|M_{y1}|}{M_{y2}} + \frac{|M_{z1}|}{M_{z2}} \leq 1$$

If the drive is simultaneously subjected to several of the indicated forces and torques, the following equation must be satisfied in addition to the indicated maximum loads.

f_v = load comparison factor

$F1$ = dynamic value

$F2$ = maximum value

Dynamic load values for DGSS-6

Size [mm]	6								
Stroke	5 mm	10 mm	15 mm	20 mm	25 mm	30 mm	40 mm	50 mm	60 mm
Max. force F_y	296 N				274 N	258 N	235 N	218 N	205 N
Max. force F_z	296 N				274 N	258 N	235 N	218 N	205 N
Max. moment M_x	0.8 Nm				0.7 Nm		0.6 Nm		
Max. moment M_y	0.7 Nm				0.6 Nm			0.5 Nm	
Max. moment M_z	0.7 Nm				0.6 Nm			0.5 Nm	

Dynamic load values for DGSS-10


Size [mm]	10								
Stroke	5 mm	10 mm	15 mm	20 mm	25 mm	30 mm	40 mm	50 mm	60 mm
Max. force F_y	826 N				766 N	721 N	655 N	608 N	572 N
Max. force F_z	826 N				766 N	721 N	655 N	608 N	572 N
Max. moment M_x	3 Nm				2.8 Nm	2.7 Nm	2.4 Nm	2.2 Nm	2.1 Nm
Max. moment M_y	2.6 Nm				2.4 Nm	2.3 Nm	2.1 Nm	1.9 Nm	1.8 Nm
Max. moment M_z	2.6 Nm				2.4 Nm	2.3 Nm	2.1 Nm	1.9 Nm	1.8 Nm

Datasheet



Dynamic load values for DGSS-16									
Size [mm]	16								
Stroke	5 mm	10 mm	15 mm	20 mm	25 mm	30 mm	40 mm	50 mm	60 mm
Max. force Fy	925 N				859 N	808 N	734 N	682 N	641 N
Max. force Fz	925 N				859 N	808 N	734 N	682 N	641 N
Max. moment Mx	4.4 Nm				4 Nm	3.8 Nm	3.5 Nm	3.2 Nm	3 Nm
Max. moment My	2.6 Nm				2.4 Nm	2.3 Nm	2.1 Nm	1.9 Nm	1.8 Nm
Max. moment Mz	2.6 Nm				2.4 Nm	2.3 Nm	2.1 Nm	1.9 Nm	1.8 Nm

Dynamic load values for DGSS-20									
Size [mm]	20								
Stroke	5 mm	10 mm	15 mm	20 mm	25 mm	30 mm	40 mm	50 mm	60 mm
Max. force Fy	1,560 N				1,448 N	1,363 N	1,238 N	1,149 N	1,082 N
Max. force Fz	1,560 N				1,448 N	1,363 N	1,238 N	1,149 N	1,082 N
Max. moment Mx	10.1 Nm				9.4 Nm	8.9 Nm	8 Nm	7.5 Nm	7 Nm
Max. moment My	5.1 Nm				4.7 Nm	4.4 Nm	4 Nm	3.7 Nm	3.5 Nm
Max. moment Mz	5.1 Nm				4.7 Nm	4.4 Nm	4 Nm	3.7 Nm	3.5 Nm




Payload m as a function of impact velocity v and cushioning -P/-P1/-E/-E1 for DGSS-6





Datasheet


Payload m as a function of impact velocity v and cushioning -P/-P1/-E/-E1 for DGSS-10Payload m as a function of impact velocity v and cushioning -P/-P1/-E/-E1 for DGSS-16

Datasheet

Payload m as a function of impact velocity v and cushioning -P/-P1/-E/-E1 for DGSS-20Payload m as a function of impact velocity v and cushioning -Y12 for DGSS-6Payload m as a function of impact velocity v and cushioning -Y12 for DGSS-10

Datasheet

Payload m as a function of impact velocity v and cushioning -Y12 for DGSS-16Payload m as a function of impact velocity v and cushioning -Y12 for DGSS-20




Dimensions

	B1 ±0,2	B2 ±0,1	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	B15	D1 Ø H7	D2 Ø H7	D3 Ø H7	D4 Ø H7
DGSS-6-5-E1A	16	15,3	10	3	10	3	–	–	9	3,2	7,7	10	3	8	9	5	5	5	6
DGSS-6-10-E1A							9,9	2,7											
DGSS-6-15-E1A																			
DGSS-6-20-E1A																			
DGSS-6-25-E1A																			
DGSS-6-30-E1A																			
DGSS-6-40-E1A																			
DGSS-6-50-E1A																			
DGSS-6-60-E1A																			
DGSS-10-5-E1A	20	19,3	12,5	3,8	12,5	3,8	–	–	11	4,2	9,7	13	3,5	10	11	7	5	5	7,5
DGSS-10-10-E1A							12	3,7											
DGSS-10-15-E1A																			
DGSS-10-20-E1A																			
DGSS-10-25-E1A																			
DGSS-10-30-E1A																			
DGSS-10-40-E1A																			
DGSS-10-50-E1A																			
DGSS-10-60-E1A																			

	D5 Ø H7	D6	D7	D8	D9	D10	D11	D12	D13	D15	H1	H2	H3	H4	H5	H6	H7 ±0,2	H8	H9	
DGSS-6-5-E1A	5	M3	M3	M2	M4	–	M3	–	M3	M3	39	19,5	2,5	–	5	19	38	15	7	
DGSS-6-10-E1A						M2		–												
DGSS-6-15-E1A														M4						
DGSS-6-20-E1A																				
DGSS-6-25-E1A																				
DGSS-6-30-E1A																				
DGSS-6-40-E1A																				
DGSS-6-50-E1A																				
DGSS-6-60-E1A																				
DGSS-10-5-E1A	–	M5	M5	M2,5	M5	–	M4	–	M4	M4	47	20,8	3,7		5	23	46	18	7,5	
DGSS-10-10-E1A	7					M2,5		M4						–						M5
DGSS-10-15-E1A																				
DGSS-10-20-E1A																				
DGSS-10-25-E1A																				
DGSS-10-30-E1A																				
DGSS-10-40-E1A																				
DGSS-10-50-E1A																				
DGSS-10-60-E1A																				

Dimensions

Dimensions – DGSS-6 ... 10-E1 (page 2 of 4)

Download CAD data www.festo.com

[1] Compressed air ports


Dimensions

	H10	H11	H12	H13	H14	H15	H16	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11	
DGSS-6-5-E1A	18	15,5	11,2	6,6	28,2	5	10,5	42,5	34,5	6	4	12	-	3,5	20	10	10	8	
DGSS-6-10-E1A								47,5	39,5							15			
DGSS-6-15-E1A								52,5	44,5							20			
DGSS-6-20-E1A								57,5	49,5							25			
DGSS-6-25-E1A								62,5	54,5							30			30
DGSS-6-30-E1A								67,5	59,5							35			
DGSS-6-40-E1A								77,5	69,5				42,5		45				
DGSS-6-50-E1A								87,5	79,5				52,5		55				
DGSS-6-60-E1A								97,5	89,5				62,5		65				
DGSS-10-5-E1A		21,5	13	7	33	11,5	51	41	8	5	19,5	-	19,5	15,5	10	12	11		
DGSS-10-10-E1A							56	46							15				
DGSS-10-15-E1A							61	51							20				
DGSS-10-20-E1A							66	56							25				
DGSS-10-25-E1A							71	61							30				
DGSS-10-30-E1A							76	66							35				
DGSS-10-40-E1A							86	76				42,5		45					
DGSS-10-50-E1A							96	86				52,5		55					
DGSS-10-60-E1A							106	96				62,5		65					

	L12	L13	L14	L15	L16	L18	T1	T2	T3	T4	T5	T6	T7	T8	T9	T10	T11	T13	
							max.	±1	max.	±0,05				±0,05	max.	max.	max.	max.	
DGSS-6-5-E1A	–	10,5	15	8	10	–	4,5	5	6	3,3	1,4	1,4	1,4	1,4	–	5,5	5	4,5	
DGSS-6-10-E1A	37				20														
DGSS-6-15-E1A	41																		
DGSS-6-20-E1A	43				30														
DGSS-6-25-E1A																			
DGSS-6-30-E1A					28										20				20
DGSS-6-40-E1A					43										25				25
DGSS-6-50-E1A	30					30													
DGSS-6-60-E1A																			
DGSS-10-5-E1A	–	11	16	10	10	–	6	8,5	4	4,4	1,7	1,4	1,4	–	–	6,2	7	6	
DGSS-10-10-E1A	46				20														
DGSS-10-15-E1A	51																		
DGSS-10-20-E1A	53				30														
DGSS-10-25-E1A																			
DGSS-10-30-E1A					20									20					
DGSS-10-40-E1A					53									46	25				25
DGSS-10-50-E1A	30					30													
DGSS-10-60-E1A																			

Dimensions

Dimensions – DGSS-16 ... 20-E1 (page 3 of 4)

Download CAD data www.festo.com


[1] Compressed air ports

Dimensions

	B1 ±0,2	B2 ±0,1	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	B15	D1 Ø H7	D2 Ø H7	D3 Ø H7	D4 Ø H7
DGSS-16-5-E1A	24	23,3	14	5	12	6	—	—	16	3,7	11,7	17	3,5	12	16	7	5	5	7,5
DGSS-16-10-E1A																			
DGSS-16-15-E1A																			
DGSS-16-20-E1A																			
DGSS-16-25-E1A																			
DGSS-16-30-E1A																			
DGSS-16-40-E1A																			
DGSS-16-50-E1A																			
DGSS-16-60-E1A																			
DGSS-20-5-E1A	32	31,3	21,6	5,2	21,6	5,2	—	—	20	5,7	15,7	20	6	16	20	9	7	7	9,3
DGSS-20-10-E1A																			
DGSS-20-15-E1A																			
DGSS-20-20-E1A																			
DGSS-20-25-E1A																			
DGSS-20-30-E1A																			
DGSS-20-40-E1A																			
DGSS-20-50-E1A																			
DGSS-20-60-E1A																			

	D5 Ø H7	D6	D7	D8	D9	D10	D11	D12	D13	D15	H1	H2	H3	H4	H5	H6	H7 ±0,2	H8	H9										
DGSS-16-5-E1A	7	M5	M5	M3	M5	—	M4	—	M4	M4	53,5	25,3	3,7	—	5,5	27	52,5	26	6										
DGSS-16-10-E1A						M3		—						4,1															
DGSS-16-15-E1A																													
DGSS-16-20-E1A																													
DGSS-16-25-E1A																													
DGSS-16-30-E1A																													
DGSS-16-40-E1A																													
DGSS-16-50-E1A																													
DGSS-16-60-E1A																													
DGSS-20-5-E1A	9	M5	M5	M4	M6	—	M4	—	M5	M5	64,5	26,7	5	—	6	34	63,5	34	6										
DGSS-20-10-E1A						M4		—						4,8															
DGSS-20-15-E1A																													
DGSS-20-20-E1A																													
DGSS-20-25-E1A																													
DGSS-20-30-E1A																													
DGSS-20-40-E1A																													
DGSS-20-50-E1A																													
DGSS-20-60-E1A																													

Dimensions



[1] Compressed air ports

Dimensions


	H10	H11	H12	H13	H14	H15	H16	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11
DGSS-16-5-E1A	25	19	12	14	37,6	6	13	60,6	48,6	10	5	19,9	-	5	32	15	12	14
DGSS-16-10-E1A								65,6	53,6							20		
DGSS-16-15-E1A								70,6	58,6							25		
DGSS-16-20-E1A								75,6	63,6							30		
DGSS-16-25-E1A								80,6	68,6						37	35		
DGSS-16-30-E1A								85,6	73,6				40					
DGSS-16-40-E1A								95,6	83,6				60		50			
DGSS-16-50-E1A								105,6	93,6						60			
DGSS-16-60-E1A								115,6	103,6						70			
DGSS-20-5-E1A	34	22	17	10	46,3	7	16	73	60,5	10	6	37	-	6,5	31	15	15	
DGSS-20-10-E1A								78	65,5							20		
DGSS-20-15-E1A								83	70,5							25		
DGSS-20-20-E1A								88	75,5							30		
DGSS-20-25-E1A								93	80,5						50	35		
DGSS-20-30-E1A								98	85,5				45					
DGSS-20-40-E1A								108	95,5				70		55			
DGSS-20-50-E1A								118	105,5						65			
DGSS-20-60-E1A								128	115,5						70			

	L12	L13	L14	L15	L16	L18	T1	T2	T3	T4	T5	T6	T7	T8	T9	T10	T11	T13
							max.	±1	max.	±0,05				±0,05	max.	max.	max.	max.
DGSS-16-5-E1A	-	55,8	19	12	10	-	5	8,5	5,5	4,4	1,7	1,4	1,4	1,7	-	6,6	6	6
DGSS-16-10-E1A	20				-													
DGSS-16-15-E1A	20																	
DGSS-16-20-E1A	30																	
DGSS-16-25-E1A	30																	
DGSS-16-30-E1A	20					20												
DGSS-16-40-E1A	65				34	20									20	7		
DGSS-16-50-E1A	75				49	25									25			
DGSS-16-60-E1A	65				30	30												
DGSS-20-5-E1A	-	14	23	12,5	10	-	5	8,5	6,5	8	2,1	1,7	1,7	2,1	-	7,5	8	6
DGSS-20-10-E1A	67				20										-			
DGSS-20-15-E1A	69				30													
DGSS-20-20-E1A					20													
DGSS-20-25-E1A					20													
DGSS-20-30-E1A					25	25												
DGSS-20-40-E1A					73	30									30			
DGSS-20-50-E1A	82				30	30												

Dimensions

Dimensions – DGSS-...-E1 perpendicularity


Download CAD data www.festo.com



[1] The term perpendicularity refers to the alignment accuracy between the slide surface and the yoke plate.

Dimensions

Dimensions – DGSS-...-E1 parallelism

[Download CAD data](#) www.festo.com



[1] The term parallelism refers to the alignment accuracy between the mounting surface and the slide surface in the longitudinal direction.

	1)
DGSS-6-5 ... 30-E1A	0,08
DGSS-6-40 ... 60-E1A	0,1
DGSS-10-5 ... 30-E1A	0,08
DGSS-10-40 ... 60-E1A	0,1
DGSS-16-5 ... 30-E1A	0,08
DGSS-16-40 ... 60-E1A	0,1
DGSS-20-5 ... 30-E1A	0,1
DGSS-20-40 ... 60-E1A	0,15

1) Parallelism

Dimensions

Dimensions – DGSS-...-E1 linearity Download CAD data www.festo.com



- [1] l = stroke
[2] The term linearity refers to the alignment accuracy between the mounting surface and the slide surface in relation to the stroke.


	1)
DGSS-6-5 ... 30-E1A	0,035
DGSS-6-40 ... 60-E1A	0,05
DGSS-10-5 ... 30-E1A	0,035
DGSS-10-40 ... 60-E1A	0,05
DGSS-16-5 ... 30-E1A	0,035
DGSS-16-40 ... 60-E1A	0,05
DGSS-20-5 ... 30-E1A	0,035
DGSS-20-40 ... 60-E1A	0,05

1) Linearity

Dimensions

Dimensions – DGSS-...-E1 guide centre and additional stroke/cushioning stroke

Download CAD data www.festo.com



	H17	L17
DGSS-6-...-E1A	7,9	20
DGSS-10-...-E1A	9,6	28,1
DGSS-16-...-E1A	10,4	31,9
DGSS-20-...-E1A	10,8	35,9


	1)	2)	3)	4)
DGSS-6-...-E1A	1,85	0,7	0,9	0,25
DGSS-10-...-E1A	2,15	0,4	1,5	
DGSS-16-...-E1A	1,9	0,65	0,65	0,6
DGSS-20-...-E1A		0,4	1	0,5

- 1) Max. additional stroke = additional stroke without cushioning + max. cushioning stroke for the retracted/extended end position.
- 2) Additional stroke without cushioning. Without pressurisation and with cushioning.
- 3) Max. cushioning stroke for the retracted end position.
- 4) Max. cushioning stroke for the extended end position.

Dimensions

Dimensions – DGSS-...-E1 with stop kit DADP and shock absorber DYEF-G8-...-Y1 (cushioning -P)

Download CAD data www.festo.com




	D14 $\varnothing$	L19	LD1			LD2			T12	$\varnothing 1$	$\varnothing 2$
			1)	min.	max.	1)	min.	max.			
DGSS-16-10-E1A	10	36	22,4	12,4	34,7	10	12,4	22,4	4	6	2,5
DGSS-16-15-E1A							17,4	27,4			
DGSS-16-20-E1A							22,4	32,4			
DGSS-16-25-E1A							27,4	37,4			
DGSS-16-30-E1A							32,4	42,4			
DGSS-16-40-E1A							42,4	52,4			
DGSS-16-50-E1A							52,4	62,4			
DGSS-16-60-E1A							62,4	72,4			
DGSS-20-10-E1A	13	39	20,7	12,8	33,5	10	12,8	22,8	5	8	3
DGSS-20-15-E1A						15	27,8				
DGSS-20-20-E1A						19,1	13,7	32,8			
DGSS-20-25-E1A							18,7	37,8			
DGSS-20-30-E1A							32,8	42,8			
DGSS-20-40-E1A							33,7	52,8			
DGSS-20-50-E1A							43,7	62,8			
DGSS-20-60-E1A							53,7	72,8			

1) Setting range

Dimensions

Dimensions – DGSS-...-E1 with stop kit DADP and shock absorber DYE-F-G8-...-Y1F (cushioning -P1)

Download CAD data www.festo.com



Dimensions


	D14 Ø	L19	LD1			LD2			T12	≙E1	≙E2
			1)	min.	max.	1)	min.	max.			
DGSS-6-10-E1A	6	22	11,2	8,8	20	10	8,8	18,8	2	3	2,5
DGSS-6-15-E1A						10,3	13,5	23,8			
DGSS-6-20-E1A							18,5	28,8			
DGSS-6-25-E1A							23,5	33,8			
DGSS-6-30-E1A							28,5	38,8			
DGSS-6-40-E1A							38,5	48,8			
DGSS-6-50-E1A							48,5	58,8			
DGSS-6-60-E1A							58,5	68,8			
DGSS-10-10-E1A	8	31	13	11,5	24,5	10	11,5	21,5	3	5	4
DGSS-10-15-E1A						15		26,5			
DGSS-10-20-E1A						17,5	14	31,5			
DGSS-10-25-E1A							19	36,5			
DGSS-10-30-E1A							24	41,5			
DGSS-10-40-E1A							34	51,5			
DGSS-10-50-E1A							44	61,5			
DGSS-10-60-E1A							54	71,5			
DGSS-16-10-E1A	10	36	21,2	12,9	34	10	12,9	22,9	4	6	5
DGSS-16-15-E1A						15		27,9			
DGSS-16-20-E1A						20		32,9			
DGSS-16-25-E1A						20,4	17,5	37,9			
DGSS-16-30-E1A							22,5	42,9			
DGSS-16-40-E1A							32,5	52,9			
DGSS-16-50-E1A							42,5	62,9			
DGSS-16-60-E1A							52,5	72,9			
DGSS-20-10-E1A	13	39	19,4	13,3	32,7	10	13,3	23,3	5	8	6
DGSS-20-15-E1A						15		28,3			
DGSS-20-20-E1A						18,8	14,5	33,3			
DGSS-20-25-E1A							19,5	38,3			
DGSS-20-30-E1A							24,5	43,3			
DGSS-20-40-E1A							34,5	53,3			
DGSS-20-50-E1A							44,5	63,3			
DGSS-20-60-E1A							54,5	73,3			

1) Setting range

Dimensions

Dimensions – DGSS-...-E1 with stop kit DADP and shock absorber DYEF-G8-S-...-Y1 (cushioning -E)

Download CAD data www.festo.com



[1] Restricted nominal stroke with shock absorbers DYEF-G8-S-...-Y1 (cushioning -E).

[2] Example for DGSS-16-25: Nominal stroke = LD2max. – LD1min. = 36,3 – 15,3 = 21 mm


	D14 ø	H18	L19	L20	LD1			LD2			1)	2)
					1)	min.	max.	1)	min.	max.		
DGSS-16-10-E1A	10	2,6	20,1	2,5	8,1	15,3	23,4	8,1	15,3	21,3	6	2,5
DGSS-16-15-E1A									18,2	26,3		
DGSS-16-20-E1A									23,2	31,3		
DGSS-16-25-E1A									28,2	36,3		
DGSS-16-30-E1A									33,2	41,3		
DGSS-16-40-E1A									43,2	51,3		
DGSS-16-50-E1A									53,2	61,3		
DGSS-16-60-E1A	13	3,1	21,4	3	6,9	15,1	21,9	7,4	63,2	71,3	8	3
DGSS-20-10-E1A									15,3	22,7		
DGSS-20-15-E1A									20,3	27,7		
DGSS-20-20-E1A									25,3	32,7		
DGSS-20-25-E1A									30,3	37,7		
DGSS-20-30-E1A									35,3	42,7		
DGSS-20-40-E1A									45,3	52,7		
DGSS-20-50-E1A									55,3	62,7		
DGSS-20-60-E1A									65,3	72,7		

1) Setting range

Dimensions

Dimensions – DGSS-...-E1 with stop kit DADP and shock absorber DYSS-G8-...-Y1F (cushioning -Y12)

Download CAD data www.festo.com




	D14 ø	L19	LD1			LD2			T12	Ø1	Ø2
			1)	min.	max.	1)	min.	max.			
DGSS-16-10-E1A	10	36	15,8	12,9	28,6	10	12,9	22,9	4	6	2,5
DGSS-16-15-E1A							17,9	27,9			
DGSS-16-20-E1A							22,9	32,9			
DGSS-16-25-E1A							27,9	37,9			
DGSS-16-30-E1A							32,9	42,9			
DGSS-16-40-E1A							42,9	52,9			
DGSS-16-50-E1A							52,9	62,9			
DGSS-16-60-E1A							62,9	72,9			
DGSS-20-10-E1A	13	39	13,6	13,3	26,9	5	13,3	18,9	5	8	3
DGSS-20-15-E1A						10		23,3			
DGSS-20-20-E1A						13	15,3	28,3			
DGSS-20-25-E1A							20,3	33,3			
DGSS-20-30-E1A							25,3	38,3			
DGSS-20-40-E1A							30,3	43,3			
DGSS-20-50-E1A							40,3	53,3			
DGSS-20-60-E1A							50,3	63,3			

1) Setting range

Dimensions

Dimensions – Stop kit DADP-SP-G9-...-F

[Download CAD data](#) www.festo.com


[1] DADP-SP-G9-6-F: M2x6 screw / DADP-SP-G9-10-F: M2.5x8 screw / DADP-SP-G9-16-F: M2.5x8 screw / DADP-SP-G9-20-F: M3x12 screw


[2] DADP-SP-G9-6-F: M2x8 screw / DADP-SP-G9-10-F: M2.5x10 screw / DADP-SP-G9-16-F: M3x10 screw / DADP-SP-G9-20-F: M4x10 screw

	B1	B2	B3	B4	B5	B6	B7	B8	D1	H1	H2
	-0,1						-0,05				
DADP-SP-G9-16-F	23,1	8,7	10,7	1,7	6,7	15,1	12	3,6	M8x1	20,4	8,9
DADP-SP-G9-20-F	31,1	13	13,4	2,8	9,5	21,7	15		M10x1	27,1	13,2

	H3	H4	H5	H6	H7	L1	L2	L3	L4	L5
				-0,1	-0,1					
DADP-SP-G9-16-F	3,9	15,1	15,4	8,5	4,4	15	6	18	4,7	4,8
DADP-SP-G9-20-F	4,6	17,4	20,4	13	7,4	20,5	9	22	9	6

Dimensions

Dimensions – Stop kit DADP-SP-G9-....-R Download CAD data www.festo.com




[1] DADP-SP-G9-6-R: M2x14 screw / DADP-SP-G9-10-R: M2.5x18 screw / DADP-SP-G9-16-R: M3x16 screw / DADP-SP-G9-20-R: M4x22 screw

	B1	B2	B3	B4	B5	B6	B7	B8	D1	D2	D3
	-0,1	-0,1									
DADP-SP-G9-16-R	23,1	10	5,6	12	4,6	14	12	5	M4	M5	M8x1
DADP-SP-G9-20-R	31	14,1	7	17	4,7	21,6	17	7,3	M5		M10x1

	H1	H2	H3	H4	H5	H6	H7	H8	H11	L1	L2
	-0,1										
DADP-SP-G9-16-R	52,9	21	15,5	12	5,8	13	3,4	25,3	42,4	15	7
DADP-SP-G9-20-R	63,9	27,9	16	16	6,7	16	4,7	26,7	52	20,5	9,8

Dimensions

Dimensions – Centring sleeve ABAZ-G9-HD

[Download CAD data](#) www.festo.com



	D1 ø	D2 ø g8	D3 ø	L1	L2
ABAZ-G9-HD-10	9,3	7,5	4,8	18	15
ABAZ-G9-HD-20	11,3	9,3	5,8		

Ordering data

Mini slide DGSS					
	Size	Stroke	Cushioning	Part no.	Type
	6	5 mm	Elastomer cushioning, double-sided, stroke not adjustable	8164050	DGSS-6-5-E1A
		10 mm		8164051	DGSS-6-10-E1A
		15 mm		8164052	DGSS-6-15-E1A
		20 mm		8164053	DGSS-6-20-E1A
		25 mm		8164054	DGSS-6-25-E1A
		30 mm		8164055	DGSS-6-30-E1A
		40 mm		8164056	DGSS-6-40-E1A
		50 mm		8164057	DGSS-6-50-E1A
		60 mm		8164058	DGSS-6-60-E1A
	10	5 mm		8164059	DGSS-10-5-E1A
		10 mm		8164060	DGSS-10-10-E1A
		15 mm		8164061	DGSS-10-15-E1A
		20 mm		8164062	DGSS-10-20-E1A
		25 mm		8164063	DGSS-10-25-E1A
		30 mm		8164064	DGSS-10-30-E1A
		40 mm		8164065	DGSS-10-40-E1A
		50 mm		8164066	DGSS-10-50-E1A
		60 mm		8164067	DGSS-10-60-E1A
	16	5 mm		8164068	DGSS-16-5-E1A
		10 mm		8164069	DGSS-16-10-E1A
		15 mm		8164070	DGSS-16-15-E1A
		20 mm		8164071	DGSS-16-20-E1A
		25 mm		8164072	DGSS-16-25-E1A
		30 mm		8164073	DGSS-16-30-E1A
		40 mm		8164074	DGSS-16-40-E1A
		50 mm		8164075	DGSS-16-50-E1A
		60 mm		8164076	DGSS-16-60-E1A
	20	5 mm		8164077	DGSS-20-5-E1A
		10 mm		8164078	DGSS-20-10-E1A
		15 mm		8164079	DGSS-20-15-E1A
		20 mm		8164080	DGSS-20-20-E1A
		25 mm		8164081	DGSS-20-25-E1A
		30 mm		8164082	DGSS-20-30-E1A
		40 mm		8164083	DGSS-20-40-E1A
		50 mm		8164084	DGSS-20-50-E1A
		60 mm		8164085	DGSS-20-60-E1A

Peripherals

Peripherals overview



Accessories			→ Link
Type/order code	Description		
[1] Mini slide DGSS	Compact version		dgss
[2] Centring sleeve ZBH	- For centring loads and attachments - Centring sleeves are not in the scope of delivery of the mini slide		38
[3] Centring sleeve ABAZ	For mounting several mini slides next to each other		38
[4] Proximity switch SMT-10M	- For round slot - For position sensing		35
[4] Proximity switch SMT-10G	- For round slot - For position sensing		36
[5] Stop kit DADP-...-R	- For mounting shock absorbers - For cushioning the extended and retracted end position - Stop kit DADP-...-F included in the scope of delivery		36
[6] Push-in fitting QSM	For connecting tubing with standard O.D		35
[6] One-way flow control valve GRLA	For regulating speed		35
[7] Shock absorber DYE-F-G8-...-Y1	- Cushioning -P - For cushioning the end positions - Elastic cushioning rings/pads at both ends without metal fixed stop - Threaded sleeve included in the scope of delivery		37
[7] Shock absorber DYE-F-G8-S-...-Y1	- Cushioning -E - For cushioning the end positions - Elastic cushioning rings/pads at both ends without metal fixed stop - Short design - Threaded sleeve included in the scope of delivery		37
[7] Shock absorber DYSS-G8-...-Y1F	- Cushioning -Y12 - For cushioning the end positions - Self-adjusting, hydraulic - Threaded sleeve included in the scope of delivery		37

Peripherals


Accessories		→ Link
Type/order code	Description	
[7] Shock absorber DYE-F-G8-...-Y1F	• Cushioning P1 • For cushioning the end positions • Elastic cushioning rings/pads at both ends with metal fixed stop • Threaded sleeve included in the scope of delivery	37
[8] Stop kit DADP-...-F	• For mounting shock absorbers • For cushioning the extended end position	36
[9] Distance sensor SOIA	To monitor the condition of the cushioning components	38

Accessories

Push-in fitting QSM						
	Pneumatic connection 1	Pneumatic connection, port 2	Note on materials	Product weight	Part no.	Type
	Male thread M3	For tubing outer diameter of 3 mm	RoHS compliant	1.1 g	153301	QSM-M3-3
	Male thread M5	For tubing outside diameter of 4 mm		3.4 g	153302	QSM-M5-3
		For tubing outside diameter of 4 mm		3.2 g	153304	QSM-M5-4
		For tubing outside diameter of 6 mm		4.5 g	153306	QSM-M5-6

Push-in fitting QSM-...-I						
	Pneumatic connection 1	Pneumatic connection, port 2	Note on materials	Product weight	Part no.	Type
	Male thread M3	For tubing outer diameter of 3 mm	RoHS compliant	2.3 g	133001	QSM-M3-3-I-R
		For tubing outside diameter of 4 mm		2.2 g	133002	QSM-M3-4-I-R
	Male thread M5	For tubing outer diameter of 3 mm		3.2 g	153313	QSM-M5-3-I
		For tubing outside diameter of 4 mm		3 g	153315	QSM-M5-4-I
		For tubing outside diameter of 6 mm		4.4 g	153317	QSM-M5-6-I


One-way flow control valve GRLA						
	Pneumatic connection, port 2	Pneumatic connection 1	Note on materials	Product weight	Part no.	Type
	M3	Push-in connector 3 mm	RoHS compliant	7 g	175041	GRLA-M3-QS-3
	M5	Push-in connector 3 mm		13 g	193137	GRLA-M5-QS-3-D
		Push-in connector 4 mm			193138	GRLA-M5-QS-4-D
		Push-in connector 6 mm			193139	GRLA-M5-QS-6-D

Proximity switch SMT-10M for round slot, magneto-resistive						Link smt
	Type of mounting	Switching output	Electrical connection	Cable length	Part no.	Type
	Screw-clamped, Insertable in the slot from above	3-wire NPN N/O contact	Open end	2.5 m	551377	SMT-10M-NS-24V-E-2,5-L-OE
			Plug M8, A-coded	0.3 m	551379	SMT-10M-NS-24V-E-0,3-L-M8D
		3-wire PNP N/O contact	Open end	2.5 m	551373	SMT-10M-PS-24V-E-2,5-L-OE
			Plug M8, A-coded	0.3 m	551375	SMT-10M-PS-24V-E-0,3-L-M8D
		2-wire N/O contact	Open end	2.5 m	551382	SMT-10M-ZS-24V-E-2,5-L-OE


Accessories

Proximity switch SMT-10G for round slot, magneto-resistive


Link [smt](#)

	Type of mounting	Switching output	Electrical connection	Cable length	Part no.	Type
	Clamped in C-slot, Inserted into the slot lengthwise	3-wire NPN N/O contact	Open end	2.5 m	8065030	SMT-10G-NS-24V-E-2,5Q-OE
			Plug M8, A-coded	0.3 m	8065029	SMT-10G-NS-24V-E-0,3Q-M8D
		3-wire PNP N/O contact	Open end	2.5 m	547862	SMT-10G-PS-24V-E-2,5Q-OE
			Plug M8, A-coded	0.3 m	547863	SMT-10G-PS-24V-E-0,3Q-M8D


Connecting cables NEBA, straight

	Electrical connection 1, connector system	Electrical connection 2, connector system	Electrical connection 2, number of connections/cores	Cable length	Part no.	Type
	M8x1, A-coded, to EN 61076-2-104	Open end	3	2.5 m	8078223	NEBA-M8G3-U-2.5-N-LE3
				5 m	8078224	NEBA-M8G3-U-5-N-LE3


Connecting cables NEBA, angled

	Electrical connection 1, connector system	Electrical connection 2, connector system	Electrical connection 2, number of connections/cores	Cable length	Part no.	Type
	M8x1, A-coded, to EN 61076-2-104	Open end	3	2.5 m	8078230	NEBA-M8W3-U-2.5-N-LE3
				5 m	8078231	NEBA-M8W3-U-5-N-LE3

Stop kit DADP-...-F


	Size	Material stops	Note on materials	Product weight	Part no.	Type
	6	High-alloy steel	RoHS compliant	12 g	8173536	DADP-SP-G9-6-F
	10			27 g	8173537	DADP-SP-G9-10-F
	16			36 g	8173538	DADP-SP-G9-16-F
	20			87 g	8173539	DADP-SP-G9-20-F

Stop kit DADP-...-R

	Size ¹⁾	Material plate	Note on materials	Product weight	Part no.	Type
	6	Anodised wrought aluminium alloy	RoHS compliant	24 g	8173532	DADP-SP-G9-6-R
	10			52 g	8173533	DADP-SP-G9-10-R
	16			68 g	8173534	DADP-SP-G9-16-R
	20			160 g	8173535	DADP-SP-G9-20-R


1) Scope of delivery: DADP-...-R and DADP-...-F stop kits

Accessories


Shock absorber DYE-F-G8-...-Y1 (cushioning -P)						
	Description ¹⁾	Cushioning	Material housing	Product weight	Part no.	Type
	For size 6	Elastic cushioning rings/pads at both ends without metal fixed stop	High-alloy steel	5 g	8073902	DYEF-G8-M4-Y1
					8131070	DYEF-G8-M4-Y1-F1A
	For size 10			11.7 g	8073904	DYEF-G8-M6-Y1
					8131072	DYEF-G8-M6-Y1-F1A
	For size 16			23 g	8073905	DYEF-G8-M8-Y1
					8131073	DYEF-G8-M8-Y1-F1A
	For size 20			41 g	8073906	DYEF-G8-M10-Y1
					8131074	DYEF-G8-M10-Y1-F1A

1) Scope of delivery: 1 cushioning component and 1 threaded sleeve


DYEF-...-F1A: Recommended for production facilities for manufacturing lithium-ion batteries. More information: www.festo.com/x/topic/bat

Shock absorber DYE-F-G8-...-Y1F (cushioning -P1)						
	Description ¹⁾	Cushioning	Material housing	Product weight	Part no.	Type
	For size 6	Elastic cushioning rings/pads at both ends with metal fixed stop	High-alloy steel	4.5 g	8160234	DYEF-G8-M4-Y1F
	For size 10			10.8 g	8160236	DYEF-G8-M6-Y1F
	For size 16			20.9 g	8160237	DYEF-G8-M8-Y1F
	For size 20			37.6 g	8160238	DYEF-G8-M10-Y1F

1) Scope of delivery: 1 cushioning component and 1 threaded sleeve

Shock absorber DYE-F-G8-S-...-Y1 (cushioning -E)						
	Description ¹⁾	Cushioning	Material housing	Product weight	Part no.	Type
	For size 6	Elastic cushioning rings/pads at both ends without metal fixed stop	High-alloy steel	3.5 g	8159470	DYEF-G8-S-M4-Y1
	For size 10			6.9 g	8159472	DYEF-G8-S-M6-Y1
	For size 16			14.6 g	8159473	DYEF-G8-S-M8-Y1
	For size 20			26 g	8159474	DYEF-G8-S-M10-Y1

1) Scope of delivery: 1 cushioning component and 1 threaded sleeve

Shock absorber DYSS-G8-...-Y1F (cushioning -Y12)						
	Description ¹⁾	Cushioning	Material housing	Product weight	Part no.	Type
	For size 6	Self-adjusting	High-alloy steel	3.9 g	8073911	DYSS-G8-2-4-Y1F
					8119980	DYSS-G8-2-4-Y1F-F1A
	For size 10			10.2 g	8111384	DYSS-G8-4-4-Y1F-G2
					8119982	DYSS-G8-4-4-Y1F-F1A-G2
	For size 16			16 g	8073914	DYSS-G8-5-5-Y1F
					8119983	DYSS-G8-5-5-Y1F-F1A
	For size 20			33 g	8073915	DYSS-G8-7-5-Y1F
					8119984	DYSS-G8-7-5-Y1F-F1A

1) Scope of delivery: 1 cushioning and 1 threaded sleeve

DYSS-...-F1A: recommended for production plants for manufacturing lithium-ion batteries. More information www.festo.com/x/topic/bat


Monitoring with distance sensor SOIA


For monitoring the application and condition of the cushioning components. Enables predictive maintenance and increases reliability and precision.

The following parameters can be monitored:

- Impact velocity
- End position
- Energy absorption
- Residual energy
- Cushioning reserve

Accessories

Distance sensor SOIA, inductive Link soia						
	Mounting type	Displacement measuring range	Switching output	Electrical connection	Part no.	Type
	Flush	0 ... 2 mm	PNP/NPN, switchable, Push-pull	Open end	8161194	SOIA-M8PB-PNLK-LE
		0 ... 4 mm			8161198	SOIA-M12PB-PNLK-LE
	Not flush	0 ... 7 mm			8161196	SOIA-M8PNB-PNLK-LE
					8161200	SOIA-M12PNB-PNLK-LE

Centring sleeve ABAZ						
	Description	Material sleeve	Note on materials	Product weight	Part no.	Type
	For size 6	High-alloy stainless steel	RoHS compliant	2.4 g	8183326	ABAZ-G9-HD-6
	For sizes 10, 16			6.5 g	8183327	ABAZ-G9-HD-10
	For size 20			7.9 g	8183328	ABAZ-G9-HD-20

Centring sleeve ZBH-5						
	Description	Material sleeve	Size of pack	Product weight	Part no.	Type
	For sizes 6, 10, 16	Steel	10	1 g	8146543	ZBH-5-B

Centring sleeve ZBH-7						
	Description	Material sleeve	Size of pack	Product weight	Part no.	Type
	For sizes 10, 16, 20	Steel	10	1 g	8146544	ZBH-7-B

Centring sleeve ZBH-9						
	Description	Material sleeve	Size of pack	Product weight	Part no.	Type
	For size 20	Steel	10	2 g	8137184	ZBH-9-B